

### 1.6X1.25mm BI-COLOR SMD CHIP LED LAMP



**ATTENTION** 

OBSERVE PRECAUTIONS
FOR HANDLING
ELECTROSTATIC
DISCHARGE
SENSITIVE
DEVICES

Part Number: KPTB-1612QBDSEKC

Blue

Super Bright Orange

#### **Features**

- 1.6mmx1.25mm SMT LED, 0.65mm thickness.
- Bi-color,low power consumption.
- Wide viewing angle.
- Ideal for backlight and indicator.
- Various colors and lens types available.
- Package: 2000pcs / reel.
- Moisture sensitivity level : level 3.
- RoHS compliant.

### Description

The Blue source color devices are made with InGaN Light Emitting Diode.


The Super Bright Orange device is made with AlGalnP (on GaAs substrate) light emitting diode chip.

Static electricity and surge damage the LEDS.


It is recommended to use a wrist band or anti-electrostatic glove when handling the LEDs.


All devices, equipment and machinery must be electrically grounded.

### **Package Dimensions**



1.2(.047)









#### Notes:

- 1. All dimensions are in millimeters (inches).
- 2. Tolerance is ±0.2(0.008") unless otherwise noted.
- 3. The specifications, characteristics and technical data described in the datasheet are subject to change without prior notice.

4. The device has a single mounting surface. The device must be mounted according to the specifications.

 SPEC NO: DSAJ9051
 REV NO: V.5A
 DATE: MAR/26/2013
 PAGE: 1 OF 6

 APPROVED: WYNEC
 CHECKED: Allen Liu
 DRAWN: Y.Liu
 ERP: 1203007668

### **Selection Guide**

Part No.	Dice	Lens Type	lv (mcd) [2] @ 20mA		Viewing Angle [1]
			Min.	Тур.	201/2
KPTB-1612QBDSEKC	Blue (InGaN)	Water Clear	40	80	120°
			*40	*80	
	Super Bright Orange (AlGaInP)		120	250	
			*80	*150	

#### Notes:

- θ1/2 is the angle from optical centerline where the luminous intensity is 1/2 of the optical peak value.
   Luminous intensity/ luminous Flux: +/-15%.
   \*Luminous intensity value is traceable to the CIE127-2007 compliant national standards.

### Electrical / Optical Characteristics at TA=25°C

Symbol	Parameter	Device	Тур.	Max.	Units	Test Conditions	
λpeak	Peak Wavelength	Blue Super Bright Orange	460 610		nm	IF=20mA	
λD [1]	Dominant Wavelength	Blue Super Bright Orange	465 601		nm	Ir=20mA	
Δλ1/2	Spectral Line Half-width	Blue Super Bright Orange	25 29		nm	IF=20mA	
С	Capacitance	Blue Super Bright Orange	100 15		pF	VF=0V;f=1MHz	
VF [2]	Forward Voltage	Blue Super Bright Orange	3.3 2.1	4 2.5	V	IF=20mA	
lR	Reverse Current	Blue Super Bright Orange		50 10	uA	V <sub>R</sub> = 5V	

- 1.Wavelength: +/-1nm.
  2. Forward Voltage: +/-0.1V.
  3.Wavelength value is traceable to the CIE127-2007 compliant national standards.


### Absolute Maximum Ratings at TA=25°C

Parameter	Blue	Super Bright Orange	Units		
Power dissipation	120	75	mW		
DC Forward Current	30	30	mA		
Peak Forward Current [1]	150	195	mA		
Reverse Voltage	,	V			
Operating Temperature	-40°C To +85°C				
Storage Temperature	-40°C To +85°C				


#### Note:

1. 1/10 Duty Cycle, 0.1ms Pulse Width.

SPEC NO: DSAJ9051 **REV NO: V.5A** DATE: MAR/26/2013 PAGE: 2 OF 6 **APPROVED: WYNEC CHECKED: Allen Liu** DRAWN: Y.Liu ERP: 1203007668




### KPTB-1612QBDSEKC Blue





 SPEC NO: DSAJ9051
 REV NO: V.5A
 DATE: MAR/26/2013
 PAGE: 3 OF 6


 APPROVED: WYNEC
 CHECKED: Allen Liu
 DRAWN: Y.Liu
 ERP: 1203007668

### **Super Bright Orange**














SPATIAL DISTRIBUTION


 SPEC NO: DSAJ9051
 REV NO: V.5A
 DATE: MAR/26/2013
 PAGE: 4 OF 6

 APPROVED: WYNEC
 CHECKED: Allen Liu
 DRAWN: Y.Liu
 ERP: 1203007668

### **KPTB-1612QBDSEKC**

Reflow soldering is recommended and the soldering profile is shown below. Other soldering methods are not recommended as they might cause damage to the product.

Reflow Soldering Profile For Lead-free SMT Process.




- NOTES:

  1.We recommend the reflow temperature 245°C(+/-5°C). The maximum soldering temperature should be limited to 260°C.


  2.Don't cause stress to the epoxy resin while it is exposed to high temperature.

  3.Number of reflow process shall be 2 times or less.


**Recommended Soldering Pattern** (Units: mm; Tolerance: ± 0.1)



### **Reel Dimension**




**Tape Dimensions** (Units: mm)





SPEC NO: DSAJ9051 **REV NO: V.5A** DATE: MAR/26/2013 PAGE: 5 OF 6 APPROVED: WYNEC **CHECKED: Allen Liu** DRAWN: Y.Liu ERP: 1203007668

### **PACKING & LABEL SPECIFICATIONS**

### KPTB-1612QBDSEKC







Detailed application notes are listed on our website. http://www.kingbright.com/application\_notes

SPEC NO: DSAJ9051 APPROVED: WYNEC REV NO: V.5A CHECKED: Allen Liu DATE: MAR/26/2013 DRAWN: Y.Liu PAGE: 6 OF 6 ERP: 1203007668