



SEAMLESS KNIT POLYKOR™ BLENDED GLOVE WITH DOUBLE-DIPPED NITRILE COATED MICROSURFACE GRIP ON FULL HAND - 13 GAUGE

- Seamless construction offers increased comfort and breathability
- PolyKor® blended shell technology offers high cut resistance and durability with ultra-thin liners
- Nitrile MicroSurface coatings are impermeable providing an elevated grip in dry and oily conditions, infused with thousands of tiny suction cup pockets that create a vacuum effect that dispenses fluids away on contact
- Microsurface nitrile palm provides excellent grip in dry, wet & oily conditions
- Double-Dipped nitrile coating on the full hand helps keep hands dry, extends the life of the glove and provides excellent abrasion resistance
- Knit Wrist helps prevent dirt and debris from entering the glove

APPLICATIONS

- Secure Dry Grip and Oil Resistant
- Handling and Assembly of Medium to Large Parts and Materials
- Metal Fabrication
- Mechanical Equipment Maintenance and Repair
- Heavy to Medium Fastening and Anchoring

CARE INSTRUCTIONS

Recommend washing gloves in slightly warm water not exceeding 40°C. A mild non-ionic detergent should be used. A 5-10 minute cycle time should be employed. Tumble dry on low - maximum temperature 140°F (60°C).

TECHNICAL DATA

MATERIAL	Support PolyKor™ with Nitrile Micro-Surface coating				
CONSTRUCTION	Seamless knit				
COLOR	Support: ■ Gray / Coating: ■ Black/Blue				
WRIST STYLE	Knit wrist				
SIZES	7 -11				
PACKAGING	1 pair per bag, 12 pairs per dozen, 72 pairs per case				
CASE DIMENSIONS	14.2" x 11.8" x 12.6" / 36cm x 30cm x 32cm				
CASE WEIGHT	7	8	9	10	11
	11.7 lbs 5.4 kgs	12.3 lbs 5.6 kgs	13.5 lbs 6.1 kgs	14 lbs 6.4 kgs	15 lbs 6.9 kgs
COO	China				

PERFORMANCE PROPERTIES

EN388: 4X43D	ASTM F2992-15 ANSI Cut Level A4 (Adopted by ANSI/ISEA 02/16)					
ABRASION	0	1	2	3	4	-
CUT (2003)	X	1	2	3	4	5
TEAR	0	1	2	3	4	-
PUNCTURE	0	1	2	3	4	-
CUT (ISO 13997)	A	B	C	D	E	F



DIMENSIONS (IN/CM)

	7	8	9	10	11
A	9.3 / 23.7	9.7 / 24.7	10.1 / 25.7	10.5 / 26.6	10.7 / 27.2
B	3.6 / 9.2	3.9 / 9.9	4.1 / 10.4	4.2 / 10.6	4.4 / 11.2
H	■ Red	■ Yellow	■ Brown	■ Black	■ Blue

