

2-178496-1 ✓ ACTIVE

AMP Universal Power


TE Internal #: 2-178496-1

PCB Mount Header, Right Angle, Wire-to-Board, 3 Position, 7.92 mm [.311 in] Centerline, Fully Shrouded, Tin (Sn), AMP Universal Power

[View on TE.com >](#)



Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: **PCB Mount Header**

PCB Mount Orientation: **Right Angle**

Connector System: **Wire-to-Board**

Number of Positions: **3**

Centerline (Pitch): **7.92 mm [.311 in]**

Features

Product Type Features

Mixed & Hybrid Header	No
Connector Shape	Rectangular
PCB Connector Type	PCB Mount Header
Connector System	Wire-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

Number of Columns	3
Number of Loaded Positions	2
Connector Contact Load Condition	Selectively Loaded
PCB Mount Orientation	Right Angle
Number of Positions	3



Number of Rows	1
----------------	---

Number of Power Positions	2
---------------------------	---

Electrical Characteristics

Operating Voltage	300 VAC
-------------------	---------

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

Contact Underplating Material	Nickel
-------------------------------	--------

Contact Underplating Material Thickness	.8 – 1.8 μm [31.49 – 70.86 μin]
---	--

PCB Contact Termination Area Plating Material Finish	Bright
--	--------

Contact Size	1.2mm
--------------	-------

Mating Tab Width	1.2 mm[.047 in]
------------------	-----------------

PCB Contact Termination Area Plating Material Thickness	1 μm [39.37 μin]
---	---

Contact Shape & Form	Rectangular
----------------------	-------------

Contact Layout	Inline
----------------	--------

Contact Base Material	Brass
-----------------------	-------

Mating Tab Thickness	.64 mm[.025 in]
----------------------	-----------------

Contact Mating Area Plating Material	Tin (Sn)
--------------------------------------	----------

Contact Mating Area Plating Material Finish	Bright
---	--------

Contact Mating Area Plating Material Thickness	1 μm [39.37 μin]
--	---

Contact Type	Tab
--------------	-----

Contact Current Rating (Max)	12 A
------------------------------	------

PCB Contact Termination Area Plating Material	Tin
---	-----

Termination Features

Rectangular Termination Post & Tail Width	1.1 mm[.043 in]
---	-----------------

Rectangular Termination Post & Tail Thickness	.64 mm[.025 in]
---	-----------------

Termination Post & Tail Length	3.8 mm[.15 in]
--------------------------------	----------------

Termination Method to PCB	Through Hole - Solder
---------------------------	-----------------------

Mechanical Attachment

Panel Mount Feature	Without
---------------------	---------

Mating Retention Type	Locking Latch
-----------------------	---------------

PCB Mount Retention Type	Boardlock
--------------------------	-----------



PCB Mount Alignment	Without
---------------------	---------

Mating Retention	With
------------------	------

PCB Mount Retention	With
---------------------	------

Connector Mounting Type	Board Mount
-------------------------	-------------

Mating Alignment	Without
------------------	---------

Housing Features

Mating Entry Location	Side
-----------------------	------

Centerline (Pitch)	7.92 mm [.311 in]
--------------------	-------------------

Housing Material	Nylon 6/6 GF
------------------	--------------

Dimensions

Connector Width	14 mm [.551 in]
-----------------	-----------------

PCB Thickness (Recommended)	1.6 mm [.063 in]
-----------------------------	------------------

Connector Height	9.55 mm [.376 in]
------------------	-------------------

Connector Length	13.02 mm [.513 in]
------------------	--------------------

Usage Conditions

Operating Temperature (Max)	105 °C [221 °F]
-----------------------------	-----------------

Operating Temperature Range	-30 – 105 °C [-22 – 221 °F]
-----------------------------	-----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

Glow Wire Rating	Standard Part - Not Glow Wire
------------------	-------------------------------

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	250
--------------------	-----

Packaging Method	Bag
------------------	-----

Other

Position Locations Omitted	2
----------------------------	---

Number of Blocked Positions	1
-----------------------------	---

Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com)>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 178125-6
U/POWER PLUG HSG 2P 7.29




TE Part # 178125-2
UNIVERSAL POWER PLUG HSG 2P



TE Part # 178125-1
U/POWER PLUG HSG 2P 7.92M/M



TE Part # 178125-9
UNIVERSAL POWER PLUG HSG 2P



TE Part # 178125-4
U/POWER PLUG HSG 2P 7.29MM


Also in the Series | **AMP Universal Power**



Connector Contacts(22)



Insertion & Extraction Tools(1)



PCB Headers & Receptacles(51)



Power Contacts(21)



Rectangular Power Connectors(163)



Wire-to-Board Connector Assemblies & Housings(13)




Wire-to-Board Headers & Receptacles (51)


Customers Also Bought



TE Part #5053042067
RNF-100-3/16-0-STK




TE Part #172335-1
MINI UMNL PLUG HOUSING 1P



TE Part #175156-2
U/P REC CONT L/P



TE Part #179518-1
CT CRIMP-2 REC CONT. L/P



TE Part #292161-4
CT P/HDR ASSY V 4P W/KINK NAT




TE Part #316224-1
2.5 S.D.L HI-PRO V 5P ON/TAPE



TE Part #1-794374-1
SINGLE CIRCUIT MINI UMNL ASSY



TE Part #917745-1
AMP POWER D/L TAB HDR ASY 2P V



TE Part #6318369-1
SMARTEC CONN. V HDR ASSY ON TA



TE Part #172040-1
MIC CAP 5P H

Documents



Product Drawings

UNIV. POWER HDR H ASSY 2P NAT.

Japanese

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_2-178496-1_F.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-178496-1_F.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-178496-1_F.3d_stp.zip](#)

English

3D PDF

English

Customer View Model

[ENG_CVM_2-178496-1_C.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_2-178496-1_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_2-178496-1_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Crimping of Universal Power Contact

English

Power Cord Connector

English

Product Specification

English

Product Specification

Japanese

AMP Universal Power Connector

Japanese

Instruction Sheets

AMP UNIVERSAL POWER CONNECTOR SERIES

English

Instruction Sheet (non U.S.)



English

[Agency Approvals](#)

[UL Report](#)

English