


Piloted check valve HGL-1/2-NPT

Part number: 34880

FESTO



Data sheet

 General operating condition

Feature	Value
Valve function	Piloted non-return function
Pneumatic connection, port 1	1/2 NPT
Pneumatic connection, port 2	1/2 NPT
Type of mounting	Screw-in
Standard nominal flow rate (standardised to DIN 1343)	0 l/min ... 1600 l/min
Operating pressure	0.02 MPa ... 1 MPa
Operating pressure	0.2 bar ... 10 bar
Pilot pressure	0.1 MPa ... 1 MPa
Pilot pressure	1 bar ... 10 bar
Pilot pressure	14.5 psi ... 145 psi
Ambient temperature	-20 °C ... 80 °C
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Symbol	00991456
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Media temperature	-20 °C ... 80 °C
Note on materials	RoHS-compliant