



CARLIT - FLEX S3

Réf. : 16131



Suitable for :	Outside
Type :	Boots
Activity :	Construction / Extreme cold / Oil and Gas
Upper :	Supple full leather water resistant for 4 hours
Lining :	Synthetic fur grey colour
Tongue :	
Ankle protection :	
Fastening :	
Toe cap :	Ultralight and extra wide Composite toe cap 200 joules LIGHT SYSTEM®
Midsole :	Composite FLEX SYSTEM®, anti-magnetic and thermal insulated
Insole :	Foamed PU, anatomical, antistatic and anti bacterial
Sole :	PU/TPU multi-hardness EXTREM 4 outsole, oil resistant FO, antistatic, HI-CI
Sole pattern :	Deep cleated sole pattern for better slip resistance on wet or icy grounds
Weight (Kg/pair) :	1.400
Colors :	Brown upper, outsole black/grey/silver cleats
Sizes :	38-48 (5-13)
Standard :	EN ISO 20345:2011 SRC
CE certificate of conformity N° :	0075/020/161/06/18/1168 EXT 19/06/18
Special features :	Two loops for easy and fast boot pull-on
Special features 2 :	Available in small sizes: 35 -36 -37
Special features 3 :	

SPECIAL FEATURES

 Integral 100% composite
(Air System + Light System + Flex System)

 Metal free, non magnetic

 4-hour water absorption and
penetration resistance test (WR)

 EXTREM 4

G GENERAL FEATURES

	Antistatic properties (A)	YES	YES
	Heel energy absorption (E)	YES	YES
	Abrasion resistance	YES	YES
	Crampon sole	YES	YES
	Heat-insulated sole (HI)	YES	YES
	Cold-insulated sole (CI)	YES	YES
	200 joule extra-wide toecap	YES	YES
	Hyper-ventilated lining	YES	YES
	Perforation-resistance 1100 N (P)	YES	