




Terminals & Splices > Magnet Wire Terminals



Magnet Wire Terminal Type: **Tab**
Mating Tab Width: **3 mm [.118 in]**
Mating Tab Thickness: **.64 mm [.025 in]**
Magnet Wire Size: **.16 – 1.02 mm**

Features

Product Type Features

Compatible With Discrete Wire Type	Magnet Wire, Solid
------------------------------------	--------------------

Contact Features

Magnet Wire Terminal Type	Tab
Mating Tab Width	3 mm[.118 in]
Mating Tab Thickness	.64 mm[.025 in]
Terminal Plating Material	Tin
Contact Underplating Material	Copper
Terminal Orientation	Straight

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
------------------------------------	-------------------------------

Mechanical Attachment

Mating Retention Type	Barbs
-----------------------	-------

Dimensions

Terminal Height	7.7 mm[.303 in]
Magnet Wire Size	.16 – 1.02 mm
Stock Thickness (Magnet Wire Side)	.5 mm[.02 in]
Product Length	24.18 mm[.951 in]

Usage Conditions

--	--



Insulation Option	Uninsulated
-------------------	-------------

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Packaging Features

Packaging Method	Reel
------------------	------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # 2-1601197-2
[.118X.025 MULTI-BARB STD SMZ](#)



TE Part # 5-1601008-2
[.118 X .025 TAB STD SIAMEZE](#)



TE Part # 2-1601149-2
[159-020-014=REC,250X020,MMDSMZ](#)



TE Part # 4-1601197-2
[.118X.025 MULTI-BARB STD SMZ](#)



TE Part # 1601104-2
[131-175-021=TAB,071X025,STD SMZ](#)



TE Part # 1601112-2
[131-187-014=TAB,110X032,STD SMZ](#)



TE Part # 1601149-2
[159-019-014=REC,250X020,MMDSMZ](#)



TE Part # 2-1601243-2
[TAB,.118 X .020,STD,SMZ](#)



TE Part # 3-1601008-2
[.118 X .025 TAB STD SIAMEZE](#)



TE Part # 1601008-2
[131-017-014=TAB,118X025,STD SMZ](#)



TE Part # 1601033-3
[STD SMZ 187X020 BARB TAB TERM](#)



TE Part # 1601119-2
[118X 025 TAB FINE WIRE SIAMEZE](#)



TE Part # 1601193-2
[.025 SQ OFFSET PIN STD SMZ](#)



TE Part # 1601051-2
[131-113-014=TAB,118X032,STD SMZ](#)



TE Part # 2-1601104-2
[131-176-021=TAB,071X025,STD SMZ](#)




TE Part # 2-1601119-2
[118X025 TAB FINE WIRE SIAMEZE](#)

Also in the Series | **SIAMEZE**



[Insertion & Extraction Tools\(1\)](#)



[Magnet Wire Terminals\(191\)](#)

Customers Also Bought



TE Part #964339-1
[MAG MATE KONT. MKII](#)

TE Part #7-1393238-2
[RTD14110](#)

TE Part #2-1393243-4
[RTE25524](#)

TE Part #1825142-2
[AE101MD1AG04](#)

TE Part #9-1879256-5
[RP 2B 237R 0.1% 15PPM 1K RL](#)

TE Part #1623187-1
[CRG0805 1% 300K](#)

TE Part #9-2176374-8
[RQ 0805 1K1 0.1% 10PPM 1K RL](#)

TE Part #5822138-4
[80 ME .050 L/P AU M/L PB-FREE](#)

TE Part #1-1546111-0
[EUROSTYLE TB,HEADER,GREY,10POS](#)

Documents

Product Drawings

[131-177-014=TAB,118X025,STDSMZ](#)

English

[131-177-014=TAB,118X025,STDSMZ](#)

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1601106-2_C.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1601106-2_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1601106-2_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Datasheets & Catalog Pages
Magnet Wire Terminals & Splices

English

Product Specifications
Application Specification

English