




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **634 – 1782 CMA**

Mating Tab Width: **6.35 mm [.25 in]**

Features

Product Type Features

Insertion Force	Low
-----------------	-----

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Open

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Hole



Dimensions

Compatible Insulation Diameter Range	2.4 – 2.8 mm[.094 – .11 in]
Terminal Material Thickness	.33 mm[.013 in]
Wire Size	634 – 1782 CMA

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

Compatible With Agency/Standards Products	UL
---	----

Packaging Features

Packaging Quantity	12000
Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts



KIT

REPRESENTATION ONLY

TE Part # 7-2150663-7

[OC-090F100O-CRIMPTOOLINGKIT](#)



TE


TE Part # 1742109-1

[250 MINI FASTON, FLAG, REC., 18-14 AWG, BR](#)

Also in the Series | FASTON 250



[Compression Connectors\(4\)](#)




[Crimp Terminal Housings\(116\)](#)



[Insertion & Extraction Tools\(6\)](#)



[Insulation Boots & Sleeves\(16\)](#)



[Magnet Wire Terminals\(1\)](#)



[PCB Terminals\(133\)](#)



[Quick Disconnects\(421\)](#)



[Splices\(4\)](#)

Customers Also Bought



TE

TE Part #T1927030120-000

[H3APR-MTGSW-M20](#)



TE

TE Part #T2030002025-000

[CEF-2.5](#)



TE

TE Part #T2080052101-000

[HQ-005-M](#)



TE

TE Part #T2080052201-000

[HQ-005-F](#)



TE Part #T2030002015-000
CEF-1.5

TE Part #T1937030000-000
H3APR-MAGSW

TE Part #T1910240140-009
H24BPR-TSH-M40-EMC-C

TE Part #T2050462201-000
HEE-046-F

TE Part #T2050462101-000
HEE-046-M

TE Part #T2030001015-000
CEM-1.5

Documents

Product Drawings

250 FASTON,REC.,22-18 AWG,TPBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2238045-2_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2238045-2_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2238045-2_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

250_Series_Mini_FASTON_Rec

English

Product Specifications

Application Specification

English

Agency Approvals

UL

2238045-2

Quick Disconnect Receptacle, 22 – 18 AWG, .32 – .82 mm² Wire, 634 – 1782 CMA, 6.35 mm [.25 in] Tab Width, Straight, Brass, Tin Plating, FASTON 250



English