

passive filter - 316 A - 400 V - 50 Hz - for variable speed drive

VW3A46116

Passive filter

EAN Code: 3606480640070

Main

Product or component type

3,	1 doored litter
Product specific application	Reduction of current harmonics
Complementary	
Range compatibility	Altivar 61 Altivar Process ATV600 Altivar 71 Altivar Process ATV900
[Us] rated supply voltage	400 V +/- 10 %
power supply frequency	50 Hz +/- 2 %
Quantity per drive	2 filters per drive for variable speed drive ATV61H motor: 280 kW/450 hp 2 filters per drive for variable speed drive ATV61Q motor: 280 kW/450 hp 1 filter per drive for variable speed drive ATV61H motor: 160 kW/250 hp 2 filters per drive for variable speed drive ATV61H motor: 355 kW 1 filter per drive for variable speed drive ATV71H motor: 160 kW/250 hp 2 filters per drive for variable speed drive ATV71H motor: 315 kW/500 hp 2 filters per drive for variable speed drive ATV71H motor: 355 kW 1 filter per drive for variable speed drive ATV61Q motor: 355 kW 1 filter per drive for variable speed drive ATV61Q motor: 355 kW 1 filter per drive for variable speed drive ATV71Q motor: 355 kW 1 filter per drive for variable speed drive ATV71Q motor: 315 kW/500 hp 2 filters per drive for variable speed drive ATV71Q motor: 355 kW 1 filter per drive for variable speed drive ATV71Q motor: 356 kW 1 filter per drive for variable speed drive ATV71Q motor: 315 kW/500 hp 2 filters per drive for variable speed drive ATV630 wall mount, motor: 160 kW/250 hp 2 filters per drive for variable speed drive ATV930 wall mount, motor: 315 kW/500 hp 2 filters per drive for variable speed drive ATV930 wall mount, motor: 315 kW/500 hp
[In] rated current	304 A for input 316 A for output
Network number of phases	3 phases
THDI	10 % for variable speed drive ATV61H motor: 280 kW/450 hp 10 % for variable speed drive ATV61Q motor: 280 kW/450 hp 10 % for variable speed drive ATV61H motor: 160 kW/250 hp 10 % for variable speed drive ATV61H motor: 355 kW 10 % for variable speed drive ATV71H motor: 160 kW/250 hp 10 % for variable speed drive ATV71H motor: 315 kW/500 hp 10 % for variable speed drive ATV71H motor: 355 kW 10 % for variable speed drive ATV61Q motor: 160 kW/250 hp 10 % for variable speed drive ATV61Q motor: 355 kW 10 % for variable speed drive ATV61Q motor: 355 kW 10 % for variable speed drive ATV71Q motor: 315 kW/500 hp 10 % for variable speed drive ATV71Q motor: 315 kW/500 hp 10 % for variable speed drive ATV71Q motor: 355 kW 10 % for variable speed drive ATV71Q motor: 315 kW/500 hp 10 % for variable speed drive ATV630 motor: 160 kW/250 hp 10 % for variable speed drive ATV930 motor: 160 kW/250 hp 10 % for variable speed drive ATV630 motor: 315 kW/500 hp
Max current	1.5 x nominal current (duration = 60 s)
Efficiency	98 %
Thermal losses	925 W

Cos phi	1 (150 % of line current) 0.85 (75 % of line current) 0.99 (100 % of line current)				
Electrical connection	A, B terminal, connection capacity: 2.5 mm² X1-1X2-3 terminal, connection capacity: 25300 mm²				
Electrical insulation class	Class F				
Net weight	142 kg				

Environment

ID dames of medaction	ID00
IP degree of protection	IP20
	IP55 (enclosure mounting)
Vibration resistance	2 mm peak to peak (f= 513.2 Hz) conforming to IEC 60068-2-6
	0.7 gn (f= 13.2150 Hz) conforming to IEC 60068-2-6
Relative humidity	585 % without condensation
Ambient air temperature for	4560 °C (with current derating 3 % per °C)
operation	545 °C (without current derating)
Ambient air temperature for	-2555 °C storage in original packaging
storage	-2565 °C during transport
Operating altitude	<= 1000 m without current derating
	> 10004000 m with current derating 5 % per 1000 m
Standards	IEC 61000-2-2
	IEC 61000-2-4
	IEC 61000-3-12
	IEC 61000-3-4
	G5/4 engineering recommendation
	IEC 61000-3-2

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	71.000 cm
Package 1 Width	80.000 cm
Package 1 Length	120.000 cm
Package 1 Weight	163.441 kg

Logistical informations

Country of origin

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Use Better


Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration

Use Again

○ Repack and remanufacture		
Take-back	No	

Dimensions Drawings

Dimensions



- (1) Front view
- (2) Right side view
- (3) Top view

Dimensions in mm

Α	В	С	D	E1	E2	E3	F	G	Н
448.5	420	800	900.06	240	300	240	443	468	713


Dimensions in in.


Differisions in in.									
Α	В	С	D	E1	E2	E3	F	G	Н
17.66	16.54	31.50	35.43	9.45	11.81	9.45	17.44	18.43	28.07

Mounting and Clearance

Mounting Recommendations

Vertical Mounting Only






(1) Filter

Connections and Schema

Recommended Schema



- (1) Drive
- (2) Filter
- (3) Optional