

Product data sheet

Automation technology - Voltage and Power Supply



Product description	M12 Connecting cable male cable connector - female cable connector, Contacts: 4, unshielded, moulded on the cable, IP68, UL 2238, PUR, black, 4 x 1.50 mm², 5 m
Area	M12-T
Coding	T-coded
Series	813
Part no.	77 0630 0629 50704-0500

Country of Origin	DE
-------------------	----

Electrical parameters

Rated voltage	63 V
Rated impulse voltage	1500 V
Rated current	12.0 A
Pollution degree	3
Overvoltage category	III
Insulating material group	II
EMC compliance	unshielded

Material

Housing material	PA (UL94 V-0)
Contact body material	PA (UL94 V-0)
Contact material	CuZn (brass) / CuSn (bronze)
Contact plating	Au (gold)
REACH SVHC	CAS 7439-92-1 (Lead)
SCIP number	9528f550-37bf-4e14-8072-525c048663f8

Cable data - Structure of the cable

Cable diameter	8.0 mm
Cross section	4 x 1.50 mm ²
Sheath material	PUR
Single-lead insulation	PP
Single-lead structure	84 x 0.15 mm
Cable color	black

Cable data - Electrical properties

Conductor resistance	13.3 Ω/Km (20°C)
----------------------	------------------

Cable data - Mechanical properties

Bending radius, fixed cable	≥ 7.5 x Ø
Bending radius, moving cable	≥ 10 x Ø
Bending cycles	5 million
Permitted acceleration	5 m/s ²
Travel distance, horizontal	20 m
Travel speed	≤ 300 m/min

Cable data - Thermal properties

Temperature range cable in move from/to	-30 °C / 80 °C
Temperature range cable fixed from/to	-50 °C / 80 °C

Product data sheet

Automation technology - Voltage and Power Supply



Product description	M12 Connecting cable male cable connector - female cable connector, Contacts: 4, unshielded, moulded on the cable, IP68, UL 2238, PUR, black, 4 x 1.50 mm², 5 m
Area	M12-T
Coding	T-coded
Series	813
Part no.	77 0630 0629 50704-0500

Cable data - Other features

Halogen free	yes
--------------	-----

Authorization/approvals

Approvals	UL 2238
-----------	---------


Classifications

eCl@ss 11.1	27-06-03-11
ETIM 9.0	EC002638

Declarations of conformity

Low Voltage Directive	2014/35/EU (EN 60529:1991;EN 60204-1:2018)
RoHS Directive	2011/65/EU (EN 50581:2012)

Derating curve



Product description	M12 Connecting cable male cable connector - female cable connector, Contacts: 4, unshielded, moulded on the cable, IP68, UL 2238, PUR, black, 4 x 1.50 mm², 5 m
Area	M12-T
Coding	T-coded
Series	813
Part no.	77 0630 0629 50704-0500

General Disclaim Notice

The connector must not be plugged or unplugged under load. Non-observance and improper use can result in personal injury.

The connectors have been developed for applications in plant engineering, control and electrical equipment construction. The user is responsible for checking whether the connectors can also be used in other areas of application.

To protect against unintentional opening of the connector, the thread between the housing and the connector head must be secured with a suitable cyanoacrylate adhesive when used in circuits with voltages dangerous to the touch. This does not apply to connectors used in SELV and PELV circuits according to IEC 61140 (EN 61140, VDE 0140-1).

Connectors which are used in circuits with voltages dangerous to the touch may only be installed and used by, or under the supervision of, persons with electrical engineering training, taking into account the applicable regulations and standards.

The user must take suitable safety precautions to ensure that the connector cannot be accidentally disconnected.

Plug connectors with enclosure protection IP67 and IP68 are not suitable for use under water. When used outdoors, the plug connectors must be protected separately against corrosion. For further information on the IP protection classes, please refer to the "Technical Information" download centre.

Please observe the pollution degree and the overvoltage category. For further information, please refer to the download center "Technical Information".

To lock the cable connector with the device connector, the threaded ring is tightened "hand-tight" (approx. 60 cNm).