



| 20 | 10-10-1203 | AE-3002-20C | 3.800 ±.012 | 4.000 +0.12/-0.16 | 96.52 ±0.3 | 101.60 ±.3 |
|----------------|------------|-------------|-------------|-------------------|-------------|------------|
| 19 | -1193 | -19C | 3.600 ±.012 | 3.800 +0.12/-0.16 | 91.44 ±0.3 | 96.52 ±.3 |
| 18 | -1183 | -18C | 3.400 ±.012 | 3.600 +0.12/-0.16 | 86.36 ±0.3 | 91.44 ±.3 |
| 17 | -1173 | -17C | 3.200 ±.012 | 3.400 +0.12/-0.16 | 81.28 ±0.3 | 86.36 ±.3 |
| 16 | -1163 | -16C | 3.000 ±.010 | 3.200 +0.12/-0.16 | 76.20 ±0.25 | 81.28 ±.3 |
| 15 | -1153 | -15C | 2.800 ±.010 | 3.000 +0.12/-0.16 | 71.12 ±0.25 | 76.20 ±.3 |
| 14 | -1143 | -14C | 2.600 ±.010 | 2.800 +0.12/-0.16 | 66.04 ±0.25 | 71.12 ±.3 |
| 13 | -1133 | -13C | 2.400 ±.010 | 2.600 +0.12/-0.16 | 60.96 ±0.25 | 66.04 ±.3 |
| 12 | -1123 | -12C | 2.200 ±.010 | 2.400 +0.08/-0.12 | 55.88 ±0.25 | 60.96 ±.3 |
| 11 | -1113 | -11C | 2.000 ±.008 | 2.200 +0.08/-0.12 | 50.80 ±0.20 | 55.88 ±.3 |
| 10 | -1103 | -10C | 1.800 ±.008 | 2.000 +0.08/-0.12 | 45.72 ±0.20 | 50.80 ±.3 |
| 9 | -1093 | -9C | 1.600 ±.008 | 1.800 +0.08/-0.12 | 40.64 ±0.20 | 45.72 ±.3 |
| 8 | -1083 | -8C | 1.400 ±.008 | 1.600 +0.08/-0.12 | 35.56 ±0.20 | 40.64 ±.3 |
| 7 | -1073 | -7C | 1.200 ±.008 | 1.400 +0.08/-0.12 | 30.48 ±0.20 | 35.56 ±.3 |
| 6 | -1063 | -6C | 1.000 ±.004 | 1.200 +0.08/-0.12 | 25.40 ±0.10 | 30.48 ±.3 |
| 5 | -1053 | -5C | .800 ±.004 | 1.000 +0.08/-0.12 | 20.32 ±0.10 | 25.40 ±.3 |
| 4 | -1043 | -4C | .600 ±.004 | .800 +0.08/-0.12 | 15.24 ±0.10 | 20.32 ±.3 |
| 3 | -1033 | -3C | .400 ±.004 | .600 +0.08/-0.12 | 10.16 ±0.10 | 15.24 ±.3 |
| 2 | 10-10-1023 | AE-3002-2C | .200 ±.004 | .400 +0.08/-0.12 | 5.08 ±0.10 | 10.16 ±.3 |
| No OF CIRCUITS | PART No. | ENG. No. | ENGLISH | | METRIC | |

NOTE :
 1. DIMENSIONS SHOWN (MILLIMETERS) INCHES
 2. HOOKS AVAILABLE ON ENDS ONLY
 3. THIS PART CONFORMS TO MOLEX PROD.SPEC.99020-0087

| REVISION UPDATE | DESCRIPTION |
|-------------------|-------------|
| EC NO: E2005-0200 | |
| 2004/10/05 | |
| 2004/10/05 | |
| 2004/10/05 | |
| 2004/10/08 | |

| GENERAL TOLERANCES (UNLESS SPECIFIED) | |
|---------------------------------------|---------------|
| 4 PLACES | ± --- ± --- |
| 3 PLACES | ± 0.25 ± .010 |
| 2 PLACES | ± 0.35 ± .014 |
| 1 PLACE | ± --- ± --- |
| ANGULAR ±1/2° | |

| DIMENSION STYLE | |
|-----------------|------------|
| MM/IN | |
| DRAWN BY | DATE |
| P MOORE | 1998/09/14 |
| CHECKED BY | DATE |
| MGOONEY | 1999/03/08 |
| APPROVED BY | DATE |
| MWILHITE | 1999/03/08 |
| MATERIAL NO. | |

| SCALE | DESIGN UNITS | THIRD ANGLE PROJECTION |
|---|--------------|------------------------|
| 5:1 | METRIC | |
| TITLE | | |
| KONEKTCON & P.C. TAIL TERMINAL ASSEMBLY | | |
| MOLEX MOLEX INCORPORATED | | |
| DOCUMENT NO. | | SHEET NO. |
| SDAE-3002-NC-* | | 1 OF 2 |
| DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS | | |
| THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION | | |