

TB 16 I BU - Feed-through terminal block



3076659

<https://www.phoenixcontact.com/gb/products/3076659>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Feed-through terminal block, nom. voltage: 1000 V, nominal current: 76 A, number of connections: 2, connection method: Screw connection, Rated cross section: 16 mm², cross section: 6 mm² - 16 mm², mounting type: NS 35/7,5, NS 35/15, NS 32, color: blue

Commercial data

Item number	3076659
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BEK211
Product key	BEK211
GTIN	4046356662130
Weight per piece (including packing)	25.66 g
Weight per piece (excluding packing)	25.66 g
Customs tariff number	85369010
Country of origin	IN

TB 16 I BU - Feed-through terminal block



3076659

<https://www.phoenixcontact.com/gb/products/3076659>

Technical data

Notes

General

Note	For a reliable contact of multi stranded conductors it is recommended to untwist multi stranded conductors.
------	---

Product properties

Product type	Feed-through terminal block
Product family	TB
Number of connections	2
Number of rows	1
Potentials	1

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	8 kV
Maximum power dissipation for nominal condition	2.43 W

Connection data

Number of connections per level	2
Nominal cross section	16 mm ²
Connection method	Screw connection
Screw thread	M5
Tightening torque	2 ... 3 Nm
Stripping length	12 mm
Connection in acc. with standard	IEC 60947-7-1
Conductor cross-section rigid	6 mm ² ... 16 mm ²
Cross section AWG	8 ... 6 (converted acc. to IEC)
Conductor cross-section flexible	6 mm ² ... 16 mm ²
Conductor cross-section, flexible [AWG]	8 ... 6 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	6 mm ² ... 16 mm ²
Flexible conductor cross-section (ferrule with plastic sleeve)	6 mm ² ... 16 mm ²
2 conductors with same cross section, solid	4 mm ² ... 6 mm ²
2 conductors with same cross section, flexible	4 mm ² ... 6 mm ²
2 conductors with same cross section, flexible, with ferrule without plastic sleeve	4 mm ² ... 6 mm ²
Nominal current	76 A
Maximum load current	76 A
Nominal voltage	1000 V
Nominal cross section	16 mm ²

TB 16 I BU - Feed-through terminal block



3076659

<https://www.phoenixcontact.com/gb/products/3076659>

Dimensions

Width	12.2 mm
Height	51 mm
Depth on NS 35/7,5	50.5 mm
Depth on NS 35/15	58 mm

Material specifications

Color	blue (RAL 5015)
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA
Static insulating material application in cold	-60 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Electrical tests

Surge voltage test

Test voltage setpoint	9.8 kV
Result	Test passed

Temperature-rise test

Requirement temperature-rise test	Increase in temperature ≤ 45 K
Result	Test passed
Short-time withstand current 16 mm ²	1.92 kA
Result	Test passed

Power-frequency withstand voltage

Test voltage setpoint	2.2 kV
Result	Test passed

Mechanical properties

Mechanical data

Open side panel	Yes
-----------------	-----

Mechanical tests

Mechanical strength

Result	Test passed
--------	-------------

TB 16 I BU - Feed-through terminal block



3076659

<https://www.phoenixcontact.com/gb/products/3076659>

Attachment on the carrier

DIN rail/fixing support	NS 35
Test force setpoint	5 N
Result	Test passed

Test for conductor damage and slackening

Rotation speed	10 rpm
Revolutions	135
Conductor cross-section/weight	6 mm ² / 1.4 kg 16 mm ² / 2.9 kg
Result	Test passed

Environmental and real-life conditions

Needle-flame test

Time of exposure	30 s
Result	Test passed

Oscillation/broadband noise

Specification	DIN EN 50155 (VDE 0115-200):2022-06
Spectrum	Long life test category 2, bogie-mounted
Frequency	$f_1 = 5 \text{ Hz}$ to $f_2 = 250 \text{ Hz}$
ASD level	6.12 (m/s ²) ² /Hz
Acceleration	3.12g
Test duration per axis	5 h
Test directions	X-, Y- and Z-axis
Result	Test passed

Shocks

Pulse shape	Half-sine
Acceleration	30g
Shock duration	18 ms
Number of shocks per direction	3
Test directions	X-, Y- and Z-axis (pos. and neg.)
Result	Test passed

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Standards and regulations

TB 16 I BU - Feed-through terminal block



3076659

<https://www.phoenixcontact.com/gb/products/3076659>

Connection in acc. with standard	IEC 60947-7-1
----------------------------------	---------------

Mounting

Mounting type	NS 35/7,5
	NS 35/15
	NS 32

TB 16 I BU - Feed-through terminal block


3076659

<https://www.phoenixcontact.com/gb/products/3076659>



Drawings

Circuit diagram



TB 16 I BU - Feed-through terminal block



3076659

<https://www.phoenixcontact.com/gb/products/3076659>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/3076659>

 UL Recognized Approval ID: E60425				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
B				
	600 V	76 A	10 - 4	-
C				
	600 V	76 A	10 - 4	-

 cULus Recognized Approval ID: E60425				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
B				
	600 V	76 A	10 - 4	-
C				
	600 V	76 A	10 - 4	-

 EAC Approval ID: KZ7500651131219505	
---	--

TB 16 I BU - Feed-through terminal block



3076659

<https://www.phoenixcontact.com/gb/products/3076659>

Classifications

ECLASS

ECLASS-13.0	27250101
ECLASS-15.0	27250101

ETIM

ETIM 9.0	EC000897
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

TB 16 I BU - Feed-through terminal block



3076659

<https://www.phoenixcontact.com/gb/products/3076659>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk