

TF-K25

Torque wrench TORCOFIX TF-K

20-850 Nm / 15-630 lbf·ft

Code	ETIM
3288234	EC002132
EAN	UNSPSC
4010886965566	27-11-17-15
Country of origin	eCl@ss
Germany	21-04-02-22
Customs tariff number	
82041100	



Article description

- Use:
- Controlled screw tightening in the range of 5 - 25 Nm / 3,7 - 18 lbf·ft
- Adjustable, releasing and sturdy tubular torque wrench with integrated ratchet and with square drive for industry and the trades
- Features:
- Classified as per DIN EN ISO 6789-2:2017 Type II Class A; adjusted to a maximum permissible +/-3 % deviation and thus with a greater precision than the standard-stipulated +/-4 %
- Incl. traceable test certificate (DIN EN ISO 6789-2:2017)
- For controlled right- and left-hand tightening (square socket for direction change)
- 1/4" mushroom head socket square with ball lock
- Robust, matt powder-coated tubular steel construction, with galvanized ratchet and high-quality plastic parts
- New ergonomic handle, shaped according to the natural grip position of the hand
- clearly recognisable and tactile hand centring aid and calibration aid in the middle of the handle
- Double scale Nm / lbf·ft and vernier are protected from abrasion and contamination by an enlarged viewing window
- With vernier scale for Nm main scale for setting intermediate scale values; lbf·ft setting only via main scale
- Vertical alignment of the scale, torque adjustment therefore suitable for left and right handers
- Scale line positioned directly above the scale prevents reading errors (parallax errors)
- Unit labeling integrated in the scale frame and also protected by viewing windows
- The precise release mechanism generates a distinct tactile and audible release signal when the set torque value is reached
- incl. roll away protection, prevents rolling away when the tool is put down

Article information

Contents (Qty of pieces)	1	Torque range (min./max.) [Nm]	5 Nm - 25 Nm
Net weight [kg]	0,38 kg	Torque range (min./max.) [lbf·ft]	3,7 lbf·ft - 18 lbf·ft
Total length [mm]	273 mm	Trigger mechanism	Short path triggering
Total width [mm]	39 mm	Precision +/-	+/- 3 %
Total height [mm]	39,8 mm	Direction of tightening	Left and right
Material	Tubular steel construction, top-grade plastic parts	Fixed setting	no
Standard	ISO 1174 DIN 3120	Test certificate	DIN EN ISO 6789-2:2017
Drive connector square (male)	1/4"	Graduation	1
Drive connector square (male)	6,3 mm	Head height 1 [mm]	25,3 mm
Return angle	10°	Width of head 1 [mm]	35,0 mm
Number of teeth	36	Calibration length	200,5 mm
Drive type/drive	Mushroom head	Graduation [lbf·ft]	1 lbf·ft
Torque (min.) [N·m]	5 Nm	Graduation [n·m]	1 Nm
Torque (max.) [N·m]	25 Nm	vernier Nm	0,1 Nm
Torque (min.) [lbf·ft]	3,7 lbf·ft	Distance housing - square drive	17,5 mm
Torque (max.) [lbf·ft]	18 lbf·ft	Storage/Content	Plastic box