

Product datasheet

Specifications



servo motor SH3 040 0,21Nm,no
key,single,no brake,90°conn,IP54/
IP65,9k RPM

SH30401P06A2000

EAN Code: 3606485467405

Main

Range compatibility	PacDrive 3
Device short name	SH3
Product or component type	Servo motor

Complementary

Maximum mechanical speed	9000 rpm
[Us] rated supply voltage	115...480 V
Network number of phases	Three phase
Continuous stall current	1.12 A
Continuous stall torque	0.21 N.m at 115...480 V three phase
Continuous power	170 W
Peak stall torque	0.75 N.m at 480 V three phase
Nominal output power	77 W at 115 V single phase 77 W at 230 V single phase 166 W at 400 V three phase 166 W at 480 V three phase
Nominal torque	0.176 N.m at 115 V single phase 0.176 N.m at 230 V single phase 0.184 N.m at 400 V three phase 0.184 N.m at 480 V three phase
Nominal speed	4000 rpm at 115 V single phase 4000 rpm at 230 V single phase 9000 rpm at 400 V three phase 9000 rpm at 480 V three phase
Maximum current Irms	4.5 A
Shaft end	Smooth shaft
Shaft diameter	8 mm
Shaft length	25 mm
IP degree of protection	IP54 shaft bushing without shaft seal ring: conforming to IEC 60034-5 IP65 motor: conforming to IEC 60034-5
Encoder type	Absolute single turn SinCos Hiperface
Speed feedback resolution	16 periods
Holding brake	Without
Holding torque	0.4 N.m
Mounting support	International standard flange
Motor flange size	40 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Electrical connection	Rotatable right angled connector
Torque constant	0.19 N.m/A at 120 °C
Back emf constant	13.6 V/krpm at 20 °C
Number of motor poles	5.0
Rotor inertia	0.0232 kg.cm ²
Stator resistance	17.2 Ohm
Stator inductance	7.3 mH
Type of cooling	Natural convection
Length	73.4 mm
Centring collar diameter	30 mm
Centring collar depth	2.5 mm
Number of mounting holes	4
Mounting holes diameter	4.5 mm
Circle diameter of the mounting holes	46 mm
Net weight	0.4 kg
Sizing reference	SH32053P
Network number of phases	3
Temperature copper hot	130 °C
Electrical connection	rotatable right angled connector
Output current 3s peak	4.5 A
Inertia	0.0 kg.cm ² of brake 0.023 kg.cm ² of motor

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.900 cm
Package 1 Width	17.100 cm
Package 1 Length	24.600 cm
Package 1 Weight	698.000 g

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Total lifecycle Carbon footprint 408

Environmental Disclosure [Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard Yes

Packaging without single use plastic No

[EU RoHS Directive](#) Pro-active compliance (Product out of EU RoHS legal scope)

SCIP Number Ead0850d-370a-47c5-8cf7-1d93c2c974a4

REACH Regulation [REACH Declaration](#)

PVC free Yes

Use Longer

Lifetime extension

Repair No

Use Again

Repack and remanufacture

End of life manual availability No need of specific recycling operations

Take-back No