



Connectors > Connector Accessories > Connector Hardware



Connector Hardware Accessory Type: **Holder**

Primary Product Color: **Black**

Number of Positions: **8**

Operating Temperature (Max): **105 °C [221 °F]**

Operating Temperature Range: **-40 – 105 °C [-40 – 221 °F]**

Features

Product Type Features

Connector Hardware Accessory Type	Holder
Hardware Accessory Function	Mounting

Configuration Features

Number of Positions	8
---------------------	---

Body Features

Primary Product Color	Black
-----------------------	-------

Mechanical Attachment

Product Mount Type	Board Mount
--------------------	-------------

Housing Features

Centerline (Pitch)	2.5 mm[.098 in]
--------------------	-----------------

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

Industry Standards

--	--



UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Carton
Packaging Quantity	4000

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


TE Part # 7-964575-5
DUOPLUG2,5RAHMEN 5P

TE Part # 9-1534796-8
AMP DUOPLUG MK2 CONNECTOR 8P


TE Part # 3-2311500-8
DUOPLUG MKI STD,KEYED 2/3,8 POS, BROWN

TE Part # 2304525-8
AMP DUOPLUG MK II CONNECTOR 8P





TE Part # 2-1534796-8
AMP DUOPLUG MK2 CONNECTOR 8P




TE Part # 1534796-8
AMP DUOPLUG MK2 CONNECTOR 8P

Customers Also Bought




TE Part #1879334-5
CPF 0603 2R21 1% 50PPM 1K RL



TE Part #140723-2
SPLICE 22-16 AWG .02 TPBR



TE Part #1622820-5
3520 120R 5%



TE Part #282081-1
RUBBER PLUG



TE Part #41969-2
250 FASTON REC 22-18 AWG BR



TE Part #1-964575-5
PCB RAHMEN 5P



TE Part #3-2176364-3
RQ 0402 10K 0.1% 10PPM 5K RL



TE Part #HPP845E034R4
I.C 20D RH/T DIGITAL B400



TE Part #3-1825910-5
FSM18JH=6MM TACT SWITCH, HIGH TEMP



TE Part #3-643817-5
05P MTA156 CONN ASSY 18AWG ORA

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-964575-8_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-964575-8_C.3d_igs.zip

English



Customer View Model
[ENG_CVM_CVM_1-964575-8_C.3d_stp.zip](#)
English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages
[RAST Connector System Catalog](#)
English

Product Specifications
[Product Specification](#)
English

Agency Approvals
[Agency Approval Document](#)
English