



Part Number : [1200705208](#)

Product Description : Micro-Change (M12)
Receptacle, 8 Poles, PG9 Mounting Threads, Female
(Straight) to 0.25mm² PVC Leads, 0.30m (11.81")
Length

Series Number : 120070

Status : Active

Product Category : Circular Industrial Connectors

Engineering Number : 8R8J20E02C3003



Documents & Resources

Drawings

[1200705208_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead; Triphenyl-phosphate per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	120070
Description	Micro-Change (M12) Receptacle, 8 Poles, PG9 Mounting Threads, Female (Straight) to 0.25mm ² PVC Leads, 0.30m (11.81") Length
IP Rating	IP67
NEMA Rating	NEMA 6
Product Name	Micro-Change (M12)
Type	Single Ended (pigtail)
UPC	884982224759

Agency

CSA	LR6837
UL	E152210

Electrical

Current - Maximum per Contact	2.0A
Voltage - Maximum	30V AC / 36V DC

Physical

Coupling Type	Internal Thread
Gender	Female

Keyway	Single
Length	0.30m
Material - Component	Nickel-plated Brass
Mounting Thread Size	PG9
Net Weight	22.549/g
Orientation	Straight
Panel Mount	Front
Poles	8
Temperature Range - Operating	-25° to +90°C
Wire/Cable Type	Leads, UL 1061
Wire Size (AWG)	24