

DCS781X2-QW

54V XR FLEXVOLT 305mm Mitre Saw - 2 x 9Ah



5054905310646



Product Description :

The DCS781 is the ultimate cordless Mitre Saw for first and second fix applications on the jobsite and can deliver up to 675 cuts in 83mm skirting board with one 9Ah XR FLEXVOLT® battery. The powerful 54V brushless motor offers a cutting capacity of 310 x 90mm, with a 165mm height capacity at the fence and the Regenerative Braking Technology extends runtime by redirecting lost energy back into the battery. Engineered for repeatable accuracy with dual horizontal rails and a stainless steel detent plate with common angles at 0, 15, 22.5, 31.6, 35.3 and 45 degrees. Other features include Wireless Tool Control to enable automatic stop start dust extraction when used with the DCV586M, XPS crosscut positioning system for the ultimate in accuracy and visibility with no calibration needed and 100mm extendable side handles for material support and increased portability on site.

Product Features and Benefits :

- **EXTREME RUNTIME:** 675 cuts in 82mm skirting board, on a single 9Ah FLEXVOLT battery
- **AIRLOCK DUST PORT:** AirLock compatible dust extraction for simple connection
- **WTC DUST EXTRACTION:** Wireless Tool Control allows direct connection to a compatible vac with auto stop/start
- **CAM LOCK MITRE CONTROL:** Makes mitre setting faster and easier, allowing to quickly adjust angles between 0° - 50° left and 0° - 60° right
- **DOUBLE BEVEL:** Intuitive bevel lock with machined stops provides accurate and simple setting of bevel angles up to 49° left and right
- **DEPTH STOP:** Allows the adjustment of the cutting depth for grooving and rebating applications
- **MACHINED BASE & FENCE:** Designed, machined and checked to the highest standards of accuracy to deliver 0.1° accuracy
- **3 YEAR GUARANTEE:** Tool and battery covered by extended warranty, subject to registration
- **PART OF THE CORDLESS 54V XR FLEXVOLT SYSTEM:** Power Of Corded. Freedom Of Cordless
- **54V XR BRUSHLESS MOTOR:** Enhanced efficiency and durability
- **IMPRESSIVE CROSS CUT CAPACITY:** 90mm x 310mm at 90°
- **HIGH DEPTH OF CUT:** Up to 165mm x 19mm skirting board cut upright at the fence
- **EXCEPTIONAL RUNTIME PERFORMANCE:** Achieved through a combination of blade, brushless motor design and regenerative braking technology
- **LARGE DUAL SLIDING FENCE:** Provides maximum support in large material cuts at any angle or combination of angles
- **COMPACT & LIGHTWEIGHT:** Application focussed cut capacities, with a lightweight compact design for easy transport around the jobsite
- **XPS SHADOWLINE:** Provides fast accurate alignment of the blade with no adjustment required
- **STAINLESS STEEL DETENT PLATE:** Robust and easy to recalibrate, with common angles at 0, 15, 22.5, 31.6, 35.3 and 45 degrees

Technical specifications :

- Battery Capacity : 9.0 Ah
- Voltage : 54 V
- Weight (Including Battery) [Metric] : 24.7 Kg
- Max. Depth of Cut [Metric] : 165 x 19 mm
- Blade Bore [Metric] : 30 mm
- Blade Diameter [Metric] : 305 mm

Product Warranty :

1 Year Limited Warranty, 3 Year Limited Warranty When Registered

Included items :

- 54V XR FLEXVOLT 305mm Mitre Saw (x1)
- Stabilizer Bar (x1)
- 60 Tooth Blade (x1)
- Base Extensions (x2)
- Material Clamp (x1)
- DCB547 9Ah/3Ah Battery (x2)
- DCB118 Charger (x1)

- Max. Cutting Capacity (90°/90°) [Metric] :
310 x 90 mm
- Max. Cutting Capacity (45°/90°) [Metric] :
219 x 90 mm
- Saw Blade Thickness [Metric] : 2.16 mm
- Max. Cutting Capacity (90°/45°) [Metric] :
310 x 54 mm
- Blade Speed : 3800 rpm
- Max. Cutting Capacity (45°/45°) [Metric] :
219 x 54 mm

DCS781X2-QW

54V XR FLEXVOLT 305mm Mitre Saw - 2 x 9Ah



5054905310646

Product from the series DCS781X2

Ref	◆	Titre	◆
DCS781X2-QW		54V XR FLEXVOLT 305mm Mitre Saw - 2 x 9Ah	

DCS781X2-QW

54V XR FLEXVOLT 305mm Mitre Saw - 2 x 9Ah



5054905310646

Product included in the kit/set DCS781X2

Ref	◆	Titre	◆
DCB118-EU		XR 8A Charger	
DCB547-EC		XR FLEXVOLT 9.0AH BATTERY	