


FO patch cable - FOC-LC:PA-LC:PA-OM4:D01/1 - 1115625

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Multi-mode OM4 duplex jumper, LC-LC, UPC polishing, length 1 m

Your advantages

- ✓ Glass fiber optical, 8-shaped FO cable jumper
- ✓ Indoor use, suitable for fiber optics distribution and termination devices
- ✓ Made of halogen-free flame retardant material, RoHS compliant



Key Commercial Data

Packing unit	1 pc
GTIN	 4 063151 040611
GTIN	4063151040611
Weight per Piece (excluding packing)	13.000 g
Custom tariff number	85447000
Country of origin	China
Sales Key	ABNACF

Technical data

Dimensions

Length of cable	1.00 m
-----------------	--------

Ambient conditions

Ambient temperature (assembly)	-20 °C ... 60 °C
Ambient temperature (storage/transport)	-20 °C ... 60 °C
Ambient temperature (operation)	-20 °C ... 60 °C

General

Number of positions	2
Transmission characteristics (category)	OM4

FO patch cable - FOC-LC:PA-LC:PA-OM4:D01/1 - 1115625

Technical data

General

Halogen-free	complying with IEC 60754-1/2
Resistance to oil	Not resistant to oil, gasoline, acids, and lyes
Flame resistance	yes

Material

Flammability rating according to UL 94	V0
--	----

Cable

Cable abbreviation	I-V(ZN)H
Cable structure	Figure 8 cable
Smallest bending radius, fixed installation	30 mm
Smallest bending radius, movable installation	7.5 mm
Cable weight	5.30 kg/km
External sheath, color	Violet
Outer sheath, material	LSZH
Transmission speed	10 bps
Flame resistance	yes
Halogen-free	complying with IEC 60754-1/2
Resistance to oil	Not resistant to oil, gasoline, acids, and lyes
Concentration of fumes	in accordance with IEC 61034

Standards and Regulations

Concentration of fumes	in accordance with IEC 61034
Flame resistance	yes
Resistance to oil	Not resistant to oil, gasoline, acids, and lyes
Halogen-free	complying with IEC 60754-1/2
Behavior in fire	No corrosive or toxic fumes

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 10.0.1	27061003
eCl@ss 11.0	27061003
eCl@ss 9.0	27061003

UNSPSC

UNSPSC 18.0	26121604
UNSPSC 19.0	26121604

FO patch cable - FOC-LC:PA-LC:PA-OM4:D01/1 - 1115625

Classifications

UNSPSC

UNSPSC 20.0	26121604
UNSPSC 21.0	26121604

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		B.01687
-----	---	---------
