

Eaton 129591

Catalog Number: 129591

Eaton SPX Variable frequency drive, 600 V AC, 3-phase, 30 kW, IP54, Radio interference suppression filter, Brake chopper, OLED display, FR7



General specifications

Product Name	Catalog Number
Eaton SPX variable frequency drive	129591
EAN	Product Length/Depth
4015081269181	640 mm
Product Height	Product Width
257 mm	237 mm
Product Weight	Certifications
35 kg	IEC/EN 61800-3
	UL 508C
	UL Category Control No.: NMMS, NMMS2, NMMS7, NMMS8
	IEC/EN61800-3
	RCM
	RoHS, ISO 9001
	Safety: EN 61800-5-1: 2003
	DNV
	CE
	CSA-C22.2 No. 14
	IEC/EN61800-5
	Specification for general requirements:
	IEC/EN 61800-2
	UL File No.: E134360
	CSA Class No.: 3211-06
	UL report applies to both US and Canada
	Certified by UL for use in Canada
	CUL
	UL

General

Degree of protection

IP54

NEMA Other

Electromagnetic compatibility

1st and 2nd environments (according to EN 61800-3)

Fitted with:

OLED display

Internal DC link

Brake chopper

Radio interference suppression filter

DC link choke

IGBT inverter

Frame size

FR7

Mounting position

Vertical

Product Category

Variable frequency drives

Protection

Finger and back-of-hand proof, Protection against direct contact (BGV A3, VBG4)

Radio interference class

C2, C3: depending on the motor cable length, the connected load, and ambient conditions. External radio interference suppression filters (optional) may be necessary.

Suitable for

Branch circuits, (UL/CSA)

Climatic environmental conditions

Altitude

Above 1000 m with 1 % performance reduction per 100 m

Max. 3000 m

Max. 1000 m

Ambient operating temperature - min

-10 °C

Ambient operating temperature - max

50 °C

Ambient operating temperature at 150% overload - min

-10 °C

Ambient operating temperature at 150% overload - max

50 °C

Ambient storage temperature - min

-40 °C

Climatic proofing

< 95 % relative humidity, no condensation, no corrosion, no dripping water

Main circuit

Mains voltage - min

525 V

Mains voltage - max

690 V

Operating mode

Sensorless vector control (SLV)

Optional: Vector control with feedback (CLV)

U/f control

Output frequency - min

0 Hz

Output frequency - max

320 Hz

Output voltage (U₂)

600 V AC, 3-phase

690 V AC, 3-phase

Rated control supply voltage

10 V DC (Us, max. 10 mA)

Rated frequency - min

45 Hz

Rated frequency - max

66 Hz

Rated operational current (I_e) at 110% overload

41 A

Rated operational current (I_e) at 150% overload

34 A

Rated operational power at 690 V, 50 Hz

30 kW

Rated operational power at 690 V, 50 Hz, 110% overload

37 kW

Rated operational voltage

690 V AC, 3-phase

600 V AC, 3-phase

Resolution

0.01 Hz (Frequency resolution, setpoint value)

Supply frequency

50/60 Hz

Switching frequency

1.5 kHz, 1 - 6 kHz adjustable, fPWM, Power section, Main circuit

System configuration type

AC supply systems with earthed center point

Voltage rating - max

690 VAC

Communication

Communication interface

CANopen®, optional

BACnet/IP, optional

PROFIBUS-DP

LonWorks, optional

Modbus-TCP, optional

Motor rating

Assigned motor current I_M at 690 V, 50 Hz, 110% overload

39 A

Assigned motor current I_M at 690 V, 50 Hz, 150% overload

32 A

Assigned motor current I_M at 690 V, 60 Hz, 110% overload

36 A

Assigned motor current I_M at 690 V, 60 Hz, 150% overload

28 A

Assigned motor power at 690 V, 60 Hz

30 HP

Assigned motor power at 690 V, 60 Hz, 110% overload

40 HP

Control circuit

Number of inputs (analog)

2 (parameterizable, 0 - 10 V DC, 0/4 - 20 mA)

Number of inputs (digital)

6 (parameterizable, max. 30 V DC)

Number of outputs (analog)

1

Number of outputs (digital)

1 (parameterizable, 48 V DC/50 mA)

Number of relay outputs

2 (parameterizable, N/O, 8 A (24 V DC) / 8 A (250 V AC) / 0,4 A (125 V DC))

Rated control voltage (U_c)

24 V DC (external, max. 250 mA)

Design verification

Equipment heat dissipation, current-dependent P_{vid}

750 W

Heat dissipation capacity P_{diss}

0 W

Heat dissipation per pole, current-dependent P_{vid}

DeviceNet, optional	0 W
BACnet MS/TP, optional	Rated operational current for specified heat dissipation (In)
EtherCAT, optional	34 A
Ethernet IP, optional	Static heat dissipation, non-current-dependent Pvs
Modbus-RTU, optional	0 W
PROFINET, optional	
Connection to SmartWire-DT	Heat dissipation details
No	Operation (with 150 % overload)
	10.2.2 Corrosion resistance
	Meets the product standard's requirements.
	10.2.3.1 Verification of thermal stability of enclosures
	Meets the product standard's requirements.
	10.2.3.2 Verification of resistance of insulating materials to normal heat
	Meets the product standard's requirements.
	10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects
	Meets the product standard's requirements.
	10.2.4 Resistance to ultra-violet (UV) radiation
	Meets the product standard's requirements.
	10.2.5 Lifting
	Does not apply, since the entire switchgear needs to be evaluated.
	10.2.6 Mechanical impact
	Does not apply, since the entire switchgear needs to be evaluated.
	10.2.7 Inscriptions
	Meets the product standard's requirements.
	10.3 Degree of protection of assemblies
	Does not apply, since the entire switchgear needs to be evaluated.
	10.4 Clearances and creepage distances
	Meets the product standard's requirements.
	10.6 Incorporation of switching devices and components
	Does not apply, since the entire switchgear needs to be evaluated.
	10.7 Internal electrical circuits and connections
	Is the panel builder's responsibility.
	10.8 Connections for external conductors
	Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Resources

Application notes

[Electromagnetic compatibility \(EMC\)](#)

[Connecting drives to generator supplies](#)

[SPI - Variable frequency drives with a common DC bus](#)

Catalogs

[Product Range Catalog Drives Engineering](#)

Declarations of conformity

[DA-DC-00004868.pdf](#)

[DA-DC-00004869.pdf](#)

Drawings

[eaton-frequency-inverter-dimensions-006.eps](#)

Installation instructions

[IL04020008Z](#)

Multimedia

[How does a VFD work to save energy and money?](#)

[Eaton variable frequency drives - Demand more than good enough](#)

[Eaton variable frequency drives - Demand more innovation](#)

[Eaton variable frequency drives - Demand more expertise](#)

Product notifications

[eaton-drives-ecodesign-directive-mz040046en-en.pdf](#)