



 PRODUCT-DETAILS

OT400DLRR6AZ

OT400DLRR6AZ Safety switch



General Information

Extended Product Type	OT400DLRR6AZ
Product ID	1SCA022512R9430
EAN	6417019166438
Catalog Description	OT400DLRR6AZ Safety switch

Long Description	<p>Safety switch, 6-p. 415V AC23 400A, 220kW. Mounted auxiliary contact: 4NO2NC. Steel sheet enclosure. IP65. RedYellow Pistol handle. Interlocked cover. Defeatable interlocking.</p> <p>The enclosed switch is using a galvanised steel enclosure, with polyester coating. It is suitable for outdoor use with respect to UV light and ingress protection. The enclosure have inbuilt gas pressure relief function to protect the user in case of an internal arc. The door is earthed via the hinges. The enclosure is prepared for single and parallel cables. Cable entry types can be blank , ring-flange or C-flange type (FL21), with different cable configuration, like top/bottom or bottom/bottom. The handle is padlockable for 3 padlocks, cover is interlocked, and interlock function can be bypassed for thermography.</p>
------------------	---

Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	1SCC340076D0201
RoHS Declaration	1SCC340075D0201
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

SCIP

Simplified SCIP

52bbc85d-5df1-4528-b900-22661755922 Finland
bd56a85d-c4a0-4480-a59a-8500b114d70c Germany
83b6ab9c-b551-4ecb-bf3c-382ac6b99577 Portugal
d5fdd1c4-885d-481b-8d40-1f1d9eb34014 Belgium
a0c5d01f-5be3-4e89-8859-575eaa0f8a9f Poland
67826512-bbf0-4dc8-a372-4bff5a762b38 Poland
ed554303-75df-4b07-ab28-67969db7a353 Czech Republic
f9039801-b1f2-45ac-9957-8564e30a6f7e Sweden
9c4509b8-506b-41a1-9267-668e926b271e Bulgaria
612e58c4-27fa-4639-882e-57e205728e3a Croatia
573006cc-044b-4319-b167-18464eb6e641 Netherlands
03c1c533-0e42-45b6-97d0-7413381153df Belgium
4f0ad57f-e15f-465d-9082-0af57bec962c Germany
4a769999-0966-4182-a8cf-ba70d2f71b90 Spain
226d2473-62a9-4d42-9893-d93a15e82174 Denmark
a0c5d01f-5be3-4e89-8859-575eaa0f8a9f Poland
ed554303-75df-4b07-ab28-67969db7a353 Czech Republic
573006cc-044b-4319-b167-18464eb6e641 Netherlands
91a2d51e-8f27-441e-821e-9d326d0c6291 Germany
4a1fc6de-4f82-4c23-a2ba-901efbbaf631 Hungary
b74f86ea-d9fe-4d21-b662-7bac540b5afa Germany
226d2473-62a9-4d42-9893-d93a15e82174 Denmark
c61c12a6-96b2-470e-9f7c-674d414f7a2e Italy
03c1c533-0e42-45b6-97d0-7413381153df Belgium
83b6ab9c-b551-4ecb-bf3c-382ac6b99577 Portugal
d71990de-ab40-4b0c-a1cb-53dbc3c33505 Greece
cf9c677c-b9e7-4d71-9316-62aa581b27d9 Estonia
91a2d51e-8f27-441e-821e-9d326d0c6291 Germany
68d9f5d7-4ea0-4008-81d4-99aada3ea670 Germany
b74f86ea-d9fe-4d21-b662-7bac540b5afa Germany
c10be0ca-6d28-42e7-863e-0f5030de9e16 Poland
d5fdd1c4-885d-481b-8d40-1f1d9eb34014 Belgium
3d18f225-c351-4c58-be1e-5ad34a7c4fab Sweden
e8d3b45e-f6dc-4252-8faf-c284b89e93bf Norway
9c4509b8-506b-41a1-9267-668e926b271e Bulgaria
f9039801-b1f2-45ac-9957-8564e30a6f7e Sweden
612e58c4-27fa-4639-882e-57e205728e3a Croatia
ad703129-dbaa-4f2b-8b85-bb06986e6597 France
d71990de-ab40-4b0c-a1cb-53dbc3c33505 Greece
cf9c677c-b9e7-4d71-9316-62aa581b27d9 Estonia
4a769999-0966-4182-a8cf-ba70d2f71b90 Spain
30e668a0-8551-4520-90f8-d0313a787822 France
67826512-bbf0-4dc8-a372-4bff5a762b38 Poland
ad703129-dbaa-4f2b-8b85-bb06986e6597 France
460df353-a7ca-4c15-9ed4-52bfcf90bc8c Hungary
e8d3b45e-f6dc-4252-8faf-c284b89e93bf Norway
68d9f5d7-4ea0-4008-81d4-99aada3ea670 Germany
460df353-a7ca-4c15-9ed4-52bfcf90bc8c Hungary
c61c12a6-96b2-470e-9f7c-674d414f7a2e Italy
3d18f225-c351-4c58-be1e-5ad34a7c4fab Sweden
30e668a0-8551-4520-90f8-d0313a787822 France
4f0ad57f-e15f-465d-9082-0af57bec962c Germany
c10be0ca-6d28-42e7-863e-0f5030de9e16 Poland
4a1fc6de-4f82-4c23-a2ba-901efbbaf631 Hungary
2ab31eca-7f04-4fe3-b31e-e95fcd237e75 Hungary
b68b565c-ef1c-4d3c-801c-5e7c4969a4e2 Spain
28cb5825-3849-4971-ac65-4f0a5c0a89eb Belgium
d4d6309f-388c-4aa7-9ad9-5fd89d80a5d8 Germany
e3488172-177c-41d6-a9d4-f24fb917089b Poland
93c7b758-2e78-4566-b503-e2a059c7669f Norway
247c33d7-dfed-4903-8204-0d0849b618b4 Belgium
65581128-92c8-49cf-9568-63efade959a8 Denmark
f5c4daf9-bf95-405b-92ed-7ed0cd4cb172 Sweden
0ebb245e-6902-4e17-a8d3-12b18ea41427 Germany
2d5e9267-cec0-41cc-aff6-5de1b607568f Germany
26ed99d7-836e-4a9b-a425-d1ef70135a2b Croatia
0af09030-538d-4609-9164-b45302dc4803 Czech Republic
d37ad0df-8e59-4efa-8911-07887bf23366 Poland
f88f40c2-09c3-40ca-91c7-26172d7edbbe Netherlands
1b1d349d-8f0c-47ec-a744-a8a77cbbccaa Bulgaria
965b8e3f-2177-4c7b-9435-50ea96c95e6f Sweden
aff0f1e-ea7d-483b-8248-3d93a831e452 France
0f26c60d-2ef9-408f-b654-223622520e5b Greece
037bb332-2d2d-4897-b8c4-a39bdb1956a5 Portugal
2e0ad141-7e73-4045-ab34-b08206fb21d3 Poland
3975fe72-4d8e-4a2e-a567-88657c62b80b France
6f323ce7-61c8-459b-a094-6e51a60512ae Estonia
6998ec43-abbc-4691-9118-5644bc1245f5 Italy
9fd6670b-9289-411e-9c03-35bdf72d160b Germany
61ad3e8f-93b3-4237-8315-73e064da93c6 Hungary

Toxic Substances Control
Act - TSCA

1SCC340095D0201

Popular Downloads

Data Sheet, Technical Information	1SCC340015C0201
Instructions and Manuals	1SCC340016M0005
Mechanical Drawings	OTKM808023P8R.stp

Environmental

Degree of Protection	acc. to IEC 60529 IP65
Pollution Degree	3

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85363090
Country or Territory of Origin	Finland

Dimensions

Product Net Width	800 mm
Product Net Height	800 mm
Product Net Depth / Length	230 mm
Product Net Weight	35.74 kg

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	815 mm
Package Level 1 Depth / Length	910 mm
Package Level 1 Height	325 mm
Package Level 1 Gross Weight	39.6 kg
Package Level 1 EAN	6417019166438

Technical

Cable Entry Position	Top/Bottom
Cable Outlets Per Side	8xring-flange / 8xring-flange, Knock-outs: 3x10mm, 12.5mm, 20.5mm, 25.5mm, 32.5mm
Color	RAL7032
Connecting Capacity Main Circuit	Hole Diameter 10 mm Screw Clamp / PE Terminal 8pc,25 ... 120 mm²
Conventional Thermal Current (I_{the})	Fully Enclosed 400 A
Degree of Protection	acc. to IEC 60529 IP65
Enclosure Material	Steel sheet
Handle Color	Red / Yellow
Handle Type	Pistol handle
Impact Resistance Rating	Housing IK09
Maximum Mounted	4 NO, 2 NC

Auxiliary Contacts	
Mounted Auxiliary Contacts	4 NO, 2 NC
Neutral Type	No Neutral Terminal
Number of Auxiliary Contacts NC	2
Number of Auxiliary Contacts NO	4
Number of Poles	6P
Pollution Degree	3
Power Loss	at Rated Operating Conditions per Pole 10 W
Rated Conditional Short-Circuit Current (I_{nc})	61.5 kA
Rated Insulation Voltage (U_i)	750 V
Rated Operational Current AC-22A (I_e)	(380 ... 415 V) 400 A (500 V) 400 A (690 V) 400 A
Rated Operational Current AC-23A (I_e)	(380 ... 415 V) 400 A (500 V) 400 A (690 V) 400 A
Rated Operational Power AC-23A (P_e)	(380 ... 415 V) 220 kW (500 V) 280 kW (690 V) 355 kW
Rated Operational Voltage	Main Circuit 1000 V
Rated Short-Circuit Making Capacity (I_{cm})	(1000 V AC) 65 kA
Rated Short-time Withstand Current Low Voltage (I_{cw})	for 1 s 15 kA
Recommended Screw Driver	Main Circuit M10
Standards	IEC 60947-1, -3
Tightening Torque	Main Circuit 44 N·m

Technical UL/CSA

Recommended Screw Driver	Main Circuit M10
Tightening Torque	Main Circuit 44 N·m

Certificates and Declarations

Declaration of Conformity - CE	1SCC340025D2704
--------------------------------	-----------------

External Classifications and Standards

Object Classification Code	Q
ETIM 9	EC000216 - Switch disconnecter (low voltage)
ETIM 10	EC000216 - Switch disconnecter (AC)
UNSPSC	39122205
IDEA Granular Category Code (IGCC)	5166 >> Safety switch
eClass	V11.1 : 27371403
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

Categories

Low Voltage Products and Systems → Enclosed Switches → Enclosed Safety Switches → Enclosed Safety Switches

