


RAD-LDD Indust C0G HT200C, Ceramic, 470 pF, 5%, 200 VDC, C0G, High Temp, 200C, Radial Molded, Gold Termination, Industrial Grade, Lead Spacing = 5.08mm



Dimensions

L	4.83mm +/-0.25mm
H	5.97mm +/-0.25mm
T	2.29mm +/-0.25mm
S	5.08mm +/-0.38mm
LL	31.75mm MIN
F	0.635mm +0.102/-0.051mm
G	1.14mm MAX
K	4.83mm +/-0.25mm

Packaging Specifications

Weight:	493 mg
Packaging:	Bulk, Bag
Packaging Quantity:	100

General Information

Supplier:	KEMET
Series:	RAD-LDD Indust C0G HT200C
Style:	Radial
Description:	High Temp, 200C, Radial Molded, Gold Termination, Industrial Grade
Features:	Commercial
RoHS:	With Exemptions
REACH:	SVHC (Pb – CAS 7439-92-1)
Termination:	Gold
Halogen Free:	Yes

Specifications

Capacitance:	470 pF
Capacitance Tolerance:	5%
Voltage DC:	200 VDC
Dielectric Withstanding Voltage:	250 VDC
Temperature Range:	-55/+200C
Temperature Coefficient:	C0G
Dissipation Factor:	2.50%
Aging Rate:	0% Loss/Decade Hour
Insulation Resistance:	100 GOhms