



Part Number : [2317452234](#)

Product Description : Pre-Crimped Lead Mega-Fit
Tangless TPA-Capable Female-to-Pigtail, Gold (Au)
Plating, 450.00mm Length, 10 AWG, Black

Series Number : 231745

Status : Active

Product Category : Power and Signal Cable
Assemblies



Documents and Resources

Drawings

[2317452234 sd.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

[Industry Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	231745
Description	Pre-Crimped Lead Mega-Fit Tangless TPA-Capable Female-to-Pigtail, Gold (Au) Plating, 450.00mm Length, 10 AWG, Black
Application	Wire-to-Board, Wire-to-Wire
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Mega-Fit Crimp Terminals
Keyword	Pre-Crimped Leads
Product Name	Mega-Fit
UPC	198930861782

Electrical

Current - Maximum per Contact	30.0A
Voltage - Maximum	600V AC (RMS)/DC

Physical

Cable Length	450.00mm
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Black
Gender	Female-Pigtail
Material - Metal	Copper Alloy
Material - Plating Mating	Gold

Material - Plating Termination	Matte Tin
Net Weight	37.578/g
Packaging Type	Bag
Plating min - Mating	0.381µm
Plating min - Termination	1.524µm
Single Ended	Yes
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 11028
Wire Size (AWG)	10

Mates With / Use With

Use with Part(s)

Description	Part Number
Mega-Fit Tangless TPA-Capable Receptacle Housing, Dual Row, 2 Circuit, UL 94V-0, Glow-Wire Capable, Black	<u>1716920202</u>
Mega-Fit Tangless TPA-Capable Receptacle Housing, Dual Row, 4 Circuit, UL 94V-0, Glow-Wire Capable, Black	<u>1716920204</u>
Mega-Fit Tangless TPA-Capable Receptacle Housing, Dual Row, 6 Circuit, UL 94V-0, Glow-Wire Capable, Black	<u>1716920206</u>
Mega-Fit Tangless TPA-Capable Receptacle Housing, Dual Row, 8 Circuit, UL 94V-0, Glow-Wire Capable, Black	<u>1716920208</u>
Mega-Fit Tangless TPA-Capable Receptacle Housing, Dual Row, 10 Circuit, UL 94V-0, Glow-Wire Capable, Black	<u>1716920210</u>
Mega-Fit Tangless TPA-Capable Receptacle Housing, Dual Row, 12 Circuit, UL 94V-0, Glow-Wire Capable, Black	<u>1716920212</u>
Mega-Fit Tangless TPA-Capable Receptacle Housing, Single Row, 2	<u>2004561212</u>

Circuit, UL 94V-0, Glow-Wire Capable, Black	
Mega-Fit Tangless TPA-Capable Receptacle Housing, Single Row, 3 Circuit, UL 94V-0, Glow-Wire Capable, Black	<u>2004561213</u>
Mega-Fit Tangless TPA-Capable Receptacle Housing, Single Row, 4 Circuit, UL 94V-0, Glow-Wire Capable, Black	<u>2004561214</u>
Mega-Fit Tangless TPA-Capable Receptacle Housing, Single Row, 5 Circuit, UL 94V-0, Glow-Wire Capable, Black	<u>2004561215</u>
Mega-Fit Tangless TPA-Capable Receptacle Housing, Single Row, 6 Circuit, UL 94V-0, Glow-Wire Capable, Black	<u>2004561216</u>
Mega-Fit Tangless TPA-Capable Receptacle Housing, Single Row, 7 Circuit, UL 94V-0, Glow-Wire Capable, Black	<u>2004561217</u>
Mega-Fit Tangless TPA-Capable Receptacle Housing, Single Row, 8 Circuit, UL 94V-0, Glow-Wire Capable, Black	<u>2004561218</u>