



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
G	14						
			N1	REVISED PER ECO-19-007720	21MAY2020	KR	DR



STYLE A



STYLE B
INSULATION RESTRICTING

	100	LOOSE PIECE, BOX	16-14*	2.667[.105]-3.810[.150]	16-14	--	A				8-320564-1
	500	320564 ON TAPE	16-14*	2.667[.105]-3.810[.150]	16-14	--	A				2-320564-3
	500	LOOSE PIECE	14*	1.981[.078]-3.302[.130]	14	GREEN	B				2-320564-2
	500	LOOSE PIECE	16*	1.600[.063]-3.302[.130]	16	BLUE	B				2-320564-1
	500	LOOSE PIECE	16-14*	2.667[.105]-3.810[.150]	16-14	--	A				320564
	QTY	PACKAGE TYPE	 STAMPING	WIRE INSUL DIA	WIRE SIZE	STRIPE COLOR	STYLE	BODY	SLEEVE	PART NO	
								FINISH			

CUSTOMER SERVICE SYSTEMS			MAX. RECOMMENDED OPERATING TEMPERATURE: 105°C[221°F] MAX		THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN JR RUTH CHK T MICHIELUTTI APVD T MICHIELUTTI PRODUCT SPEC UL 486 A-B APPLICATION SPEC 114-2157 WEIGHT -		13JAN10 13JAN10 13JAN10		 TE Connectivity					
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: 300 VOLT MAX		DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:  0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127(.005) 4 PLC ± - ANGLES ± ±		NAME		TERMINAL, RING TONGUE, PIDG, WIRE SIZE: 16-14 AWG PIDG IR 16 & 14 AWG					
FOR APPLICATION		TOOLING ASSISTANCE CENTER		CIRCULAR MIL AREA: 1.04-2.62mm² [2,050-5,180] STRANDED OR SOLID		MATERIAL 		FINISH SEE TABLE INSULATION: COLOR-BLUE		SIZE A2		CAGE CODE 00779		DRAWING NO C-320564		RESTRICTED TO -	
FOR ORDER ENTRY		1-800-526-5142		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.						CUSTOMER DRAWING		SCALE 5:1		SHEET 1 OF 1		REV N1	

- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- STAMP "AMP - SEE TABLE" APPROX AS SHOWN.
- WIRE INSULATION DIA: SEE TABLE.
- BODY MATERIAL THK: 0.787[.031]±0.051[.002].
- BODY: TIN PLATE 0.00254[.000100] MIN EXT THK PER ASTM B545.
- SLEEVE: TIN PLATE 0.00254[.000100] MIN EXT THK PER ASTM B545.
- BODY & SLEEVE- CU PER ASTM B152 INSULATION - NYLON PER ASTM D4066
- APPLIES FROM EDGE OF METAL WIRE BARREL TO CENTER OF STUD HOLE.
- MEETS MS25036-110, CLASS 1 & 2.
- MEETS M7928/1-45, CLASS 1 & 2.
- MEETS M7928/1-54, CLASS 1 & 2.
- UL LISTED
- CSA CERTIFIED