



Article No. : 6SL4112-0DA17-0AF0

Client order no. :  
Order no. :  
Offer no. :  
Remarks :

Item no. :  
Consignment no. :  
Project :

Figure similar

### Rated data

#### Input

Number of phases	3 AC	
Line voltage	200...240V (-20+10 %)	
Line frequency	50/60 Hz (47 ... 63 Hz)	
<b>Voltage range (voltage class)</b>	200 ... 240 V (230V IEC)	200 ... 240 V (240V NEC)
Rated current	42.0 A	40.0 A

#### Output

Number of phases	3 AC	
<b>Voltage range (voltage class)</b>	200 ... 240 V (230V IEC)	200 ... 240 V (240V NEC)
Rated power (LO)	11.00 kW	15.00 hp
Rated power (HO)	7.50 kW	10.00 hp
Rated current (LO)	46.0 A	42.0 A
Rated current (HO)	40.0 A	28.0 A
Rated current (IN)	47.2 A	43.1 A
Max. output current	80.0 A	
Pulse frequency (factory setting)	4 kHz	
Output frequency for vector control	0 ... 480 Hz	
Output frequency for V/f control	0 ... 550 Hz	

#### Overload capability

Low Overload (LO)	150% rated current (LO) for 3 s, followed by 110% rated current (LO) for 57 s in a 300 s cycle time	
High Overload (HO)	200% rated current (HO) for 3 s, followed by 150% rated current (HO) for 57 s in a 300 s cycle time	

### Electronic power supply

Voltage	24 V (20.4 ... 28.8 V)	
Current demand, max.	2.00 A	

### General tech. specifications

Power factor $\lambda$ (typical)		
Displacement factor $\cos \varphi$ (typical)	0.98	
Efficiency $\eta$	0.97	
Sound pressure level (1m)	70 dB	
	with the control cabinet closed	
Filter class (integrated)	Unfiltered	

### Communication

Communication	PROFINET, Modbus TCP, EtherNet/IP
---------------	-----------------------------------

Article No. : 6SL4112-0DA17-0AF0

### Analog outputs

Number	1 (Non-isolated output)
<b>Operating mode</b>	
Voltage unipolar	0 ... 10 V
Current	0 ... 20 mA
Current monitored	4 ... 20 mA

### Motor temperature interface

1 input for motor temperature, connectable PTC, KTY 84, PT1000, and bimetal temperature switch
--

### PTC interface

Short-circuit monitoring < 200Ohm, overtemperature > 1650Ohm
--

### KTY84 interface

Short-circuit monitoring < 500Ohm; wire breakage > 2120Ohm; measurement current 2mA
---

### PTC1000 interface

Short-circuit monitoring < 603Ohm; wire breakage > 2120Ohm; measurement current 2mA
---

### Closed-loop control techniques

V/f linear / square-law / parameterizable	Yes
V/f with flux current control (FCC)	Yes
V/f ECO linear / square-law	Yes
Sensorless vector control	Yes
Vector control, with sensor	Yes
Encoderless torque control	Yes
Torque control, with encoder	Yes

### Ambient conditions

Cooling	Air cooling using an integrated fan
Cooling air requirement	0.050 m <sup>3</sup> /s (1.766 ft <sup>3</sup> /s)
Installation altitude (without derating)	1,000 m (3,281 ft)
Max. ambient temperature with derating	60 °C
Ambient temperature with high overload (without derating)	50 °C
Ambient temperature with low overload (without derating)	45 °C

### Relative humidity during

Max. operation	95 %
----------------	------

### Environmental conditions

#### Chemically active substances

Operation	Class 3C3, according to IEC 60721-3-3: 2002
Transport	Class 2C2 according to IEC 60721-3-2:1997 in marine- and weather-resistant transport packaging
Storage	Class 1C2 according to IEC 60721-3-1: 2002 in the transport packaging

#### Biologically active substances

Operation	Class 3B1 according to IEC 60721-3-3: 2002
Transport	Class 2B1 according to IEC 60721-3-2:1997 in the transport packaging
Storage	Class 1B1 according to IEC 60721-3-1:1997 in the transport packaging

#### Mechanically active substances

Operation	Class 3S1 according to IEC 60721-3-3: Ed. 2.2 2002 (Conductive dusts are not permitted.)
-----------	---

#### Climatic environmental conditions

Operation	Class 3K3 according to IEC 60721-3-3 Ed. 2.2: 2002
Transport	Class 2K4 according to IEC 60721-3-2:1997 in the transport packaging; temperature -40 ... +70 °C; relative atmospheric humidity 5...95% (without condensation)
Storage	Class 1K4 according to IEC 60721-3-1:1997 in the transport packaging; temperature -25 ... +55 °C; relative atmospheric humidity 5...95% (without condensation), storage altitude <=4000m; condensation, spray water, ice formation, salt mist not permissible


#### Mechanical environmental conditions

Operation	Class 3M1 according to IEC 60721-3-3 Ed. 2.2: 2002
Transport	Class 2M3 according to IEC 60721-3-2:1997 in the transport packaging
Storage	Class 1M2 according to IEC 60721-3-1:1997 in the transport packaging

### Integrated Safety functions

Safety function "Safe Torque Off"	Yes
Safe Stop 1 (SS1)	Yes
Safe Motor Temperature (SMT)	No
Extended software functions can be enabled with a license using an SD card.	

Connections		Certificates	
<b>Signal cable</b>		Certificate of suitability	CE, cULUs (UL 61800-5-1, CSA 22.2 No. 274), EAC, UKCA
Type	Push-in connection	CE marking	EMC directive 2014/30/EU; Low Voltage Directive 2014/35/EU; RoHS Directive 2011/65/EU; energy efficiency and eco design 2009/125/EU
Conductor cross-section	0.20 ... 2.50 mm <sup>2</sup> (24 ... 12 AWG)	Verification of suitability for fail-safety	SIL 3 according to IEC 61508 and IEC 61800-5-2, PL e according to ISO 13849-1, Category 4 according to ISO 13849-1
<b>Line side</b>		Environmental compatibility	RoHS II, REACH, Green Passport
Type	screw terminal	Explosion protection	-
<b>Conductor cross-section</b>		Shipbuilding approval	No
for single-core cables	10.00 ... 50.00 mm <sup>2</sup> (8 ... 1/0 AWG)	<b>Converter losses to IEC61800-9-2*</b>	
for multi-core cables	10.00 ... 50.00 mm <sup>2</sup> (8 ... 1/0 AWG)	Efficiency class	IE2
<b>Motor end</b>		In scope of Ecodesign Directive	No (in the valid range)
Type	screw terminal	Reason of exception	no exception
Conductor cross-section	10.00 ... 50.00 mm <sup>2</sup> (8 ... 1/0 AWG)	<b>IEC power loss data based on</b>	
<b>DC link</b>		Input	3 AC 230 V, 50 Hz
Type	screw terminal	Output	3 AC 0 - 230 V, 50 Hz, 4 kHz Space-vector modulation
Conductor cross-section	10.00 ... 50.00 mm <sup>2</sup> (8 ... 1/0 AWG)	Rated apparent power	18.8 kVA
<b>PE connection</b>		Power loss in standby	28.8 W (0.2%)
Type	M5, screw terminal		
Conductor cross-section	10.00 ... 50.00 mm <sup>2</sup> (8 ... 1/0 AWG)		
<b>Max. motor cable length</b>			
Shielded	200 m (656 ft)		
Unshielded	300 m (984 ft)		
<b>Mechanical data</b>			
Degree of protection	IP20 / UL open type		
Frame size	FSD2		
Net weight	22.5 kg (49.6 lb)		
<b>Dimensions</b>			
Width	200 mm (7.87 in)		
Height	442 mm (17.4 in)		
Depth	245 mm (9.65 in)		
<b>Memory card</b>			
1 slot for SD card	SINAMICS SD card, 8GByte		



**NEC power loss data based on**

Input	3 AC 240 V, 60 Hz
Output	3 AC 0 - 240 V, 60 Hz, 4 kHz Space-vector modulation
Rated apparent power	17.9 kVA
Power loss in standby	28.8 W (0.2%)

the absolute power losses for motor voltages according to NEC (AC 230 V, AC 460 V, AC 575 V) are approximately 2 % lower

The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current ( $I$ ) over the relative motor stator frequency ( $f$ ). The values are valid for the basic version of the converter without options/components.

\*calculated values

