



Main

Range of product	Mureva Styl
Range	Mureva Styl
Product or component type	Switch
Number of rocker	1
Switch function	2-pole 1-way
Colour tint	Grey (RAL 7016)

Complementary

Device presentation	Complete product
Technology type	Electromechanical
Device mounting	Surface
Actuator	Rocker
Load type	Load for energy saving lamps with ballast: 200 W
[Ue] rated operational voltage	250 V AC
Condition of use	Indoor/outdoor
Material	ABS (acrylonitrile butadiene-styrene) SEBS Brass
Rated current	16 AX
Wire stripping length	13 mm
Cable entry	Easy valve access diameter: 6...20 mm
Clamping connection capacity	1.5...2.5 mm ² for rigid cable(s) 1.5...2.5 mm ² for stranded cable(s) 1.5...2.5 mm ² for flexible cable(s)
Fixing mode	By screws
IP degree of protection	IP55
IK degree of protection	IK08
Width	76 mm
Height	76 mm
Chemical and detergent products resistance	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane
Depth	64 mm
Projecting depth	64 mm

Environment

Quality labels	EAC AENOR NF CE
Flame retardance	Self-extinguishing 650 °C conforming to IEC 60695-2-1
Standards	EN 60669-1
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-25...55 °C

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations