


FEATURES

- **Annealed Copper Conductor:** Offers superior conductivity and durability
- **Polyvinyl Chloride Jacket:** Provides protection against environmental factors
- **Plain Conductor Type:** Ensures consistent electrical performance
- **24/0.2 Core Strands:** Enhances flexibility and ease of installation
- **Operating Temperature Range -15 °C to 90 °C:** Suitable for a wide range of environments
- **Voltage Rating of 500 V:** Supports medium voltage applications
- **5 Cores:** Allows for complex wiring configurations
- **9.3 mm Outside Diameter:** Compact design for space-saving installations

RS PRO 0.75 mm² Flexible Cable, 50 m Length

RS Stock No: 606-123



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flexible cable is designed for reliable electrical connections in various industrial and commercial settings. With a conductor made from annealed copper, it ensures excellent conductivity and durability. The cable is ideal for installations requiring flexibility and resilience, providing a dependable solution for wiring applications.

General Specifications

Conductor Material	Annealed Copper
Conductor Type	Plain
Jacket Colour	White
Product Type	Flexible Cable

Mechanical Specifications

Cable CSA	0.75 mm ²
Cable Length	50 m
Core Strands	24/0.2
Jacket Material	Polyvinyl Chloride
Number of Cores	5
Outside Diameter	9.3 mm

Operation Environment Specifications

Maximum Operating Temperature	90 °C
Minimum Operating Temperature	-15 °C

Approvals

Standards/Approvals	ACI, BASEC ISO 9001 UKAS CS1-029, BS EN 50363-3, BS EN 50363-4-1, BS EN 50525-2-11, BS EN 60228
---------------------	---

Electrical Specifications

Voltage	500 V
---------	-------