

Eaton 259730

Catalog Number: 259730

Eaton Moeller series NZM - Molded Case Circuit Breaker. Shunt release, 480-525VAC/DC, +lateral terminal bracket

General specifications



Product Name

Eaton Moeller series NZM release

Catalog Number

259730

EAN

4015082597306

Product Length/Depth

37 mm

Product Height

66 mm

Product Width

32 mm

Product Weight

0.044 kg

Compliances

UL/CSA

IEC

RoHS conform

Product specifications

Used with

NZM1(-4), N(S)1(-4)

Type

Accessory

Shunt release

Special features

Switches are tripped by a voltage pulse or by the application of uninterrupted voltage.

If the shunt trip is live, contact with the circuit breaker's primary contacts is prevented when switched on.

Shunt releases cannot be installed simultaneously with NZM...-XHIV... early-make auxiliary contact or NZM...-XU... undervoltage release.

10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Resources

Brochures

[eaton-digital-nzm-brochure-br013003en-en-us.pdf](#)

[eaton-feerum-the-whole-grain-solution-success-story-en-us.pdf](#)

Catalogs

[eaton-digital-nzm-catalog-ca013003en-en-us.pdf](#)

Declarations of conformity

[DA-DC-03_NZM1](#)

eCAD model

[DA-CE-ETN.NZM1-XA480-525AC_DC](#)

Installation videos

[The new digital NZM Range](#)

[Introduction of the new digital circuit breaker NZM](#)

Technical data sheets

[eaton-nzm-technical-information-sheet](#)

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

10.4 Clearances and creepage distances

Meets the product standard's requirements.

10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

Electric connection type

Screw connection

Frame

NZM1

Number of contacts (normally open contacts)

0

Rated control supply voltage (Us) at AC, 50 Hz - max

525 V

Rated control supply voltage (Us) at AC, 50 Hz - min

480 V

Rated control supply voltage (Us) at AC, 60 Hz - max

525 V

Rated control supply voltage (Us) at AC, 60 Hz - min

480 V

Suitable for

Off-load switch

Voltage type

AC/DC

Rated control supply voltage (Us) at DC - max

525 V

Rated control supply voltage (Us) at DC - min

24 V

Number of contacts (normally closed contacts)

0

Number of contacts (change-over contacts)

0

Undelayed short-circuit release - min

0 A

Undelayed short-circuit release - max

0 A