
Parker Product Datasheet



Quick coupling system with nominal diameter 2.7 for pneumatic, liquids and gas applications up to 35 bar. Available in nickel-plated brass or stainless steel.

PART NUMBER: 20KBKS06MPX
COUPLING HALF: Coupler
CONNECTION TYPE: Tube
BODY MATERIAL: Brass
CONNECTION SIZE: 4x6 MM
FUNCTION: Double Shut-Off

PRODUCT OVERVIEW

Parker’s Series 20 is a mini-industrial coupling with European profile. Coupling system with single-hand operation. High flow rate despite small dimensions.

Markets:
- Industrial
- Life Sciences
- Medical technology
- Chemistry pharmacybr/>- Electronics and energy management
- Transportation
- Machinery construction
- Automotive
- Process

Features/Benefits:

- Mini Industrial coupling
- Single hand operation for easy and fast connection
- European profile is the most representative profile worldwide

TECH SPECIFICATIONS

HEX SIZE	12 mm (external)
VALVE INCLUDED	Yes
PRODUCT STYLE	Quick Connect
DIVISION	Low Pressure Connectors Europe Division
APPLICATION	Pharma
QUANTITY PER BOX	10.0
APPLICATION	Medical
PLATING TYPE	Without Surface Treatment
COUPLING HALF	Coupler
PRODUCT TYPE	Pneumatic Quick Couplings
SLEEVE MATERIAL	Brass
REGION OF ORIGIN	Germany
CONNECTION TYPE	Tube Panel monted, without spring guard
FUNCTION	Double Shut-Off
OPERATION TYPE	Sleeve
INDUSTRY	Healthcare & Life Sciences
MAXIMUM OPERATING PRESSURE	507 psi
LENGTH	45 mm
DIAMETER	2.7 mm (nominal)
MAXIMUM OPERATING PRESSURE	35 bar
PRODUCT SERIES	Series 20
BRAND	Parker

MAXIMUM OPERATING TEMPERATURE	100 °C
BRAND	Rectus
MINIMUM OPERATING TEMPERATURE	-4 °F
CONNECTION SIZE	4x6 mm
MINIMUM OPERATING TEMPERATURE	-20 °C
MAXIMUM OPERATING TEMPERATURE	212 °F
INTERCHANGE TYPE	European Profile
WEIGHT	0.018 kg
INDUSTRY	General Industrial
FLOW RATE	130 L/min (air)
VALVE TYPE	Standard Valve
APPLICATION	Food & Beverages
FOR FLUID TYPE	Air & Neutral Gases (Industrial compressed, lubricated air, inert gases)
SEAL MATERIAL	NBR
BODY MATERIAL	Brass
APPLICATION	Industrial Machinery
DIVISION	Low Pressure Connectors Europe Division
COMPATIBLE FITTING	Series 20 Plug
TECHNOLOGY	Pneumatics