

Product data sheet

Specifications



trip unit MicroLogic 4.3 for ComPact NSX 400/630 circuit breakers, electronic, rating 400A, 4 poles 4d

LV433932

Discontinued on: 30 September 2022

To be discontinued

Important message : This product has been switched to new ComPacT range and is no longer commercialized. It will continue to be available until Q4 2022 only limited to specific projects.

Main

Range	ComPact
Range of product	ComPact NSX400...630
Product or component type	Trip unit
Trip unit name	Micrologic 4.3
Trip unit technology	Electronic
Range compatibility	ComPact NSX400 ComPact NSX630
Device application	Distribution
Number of poles	4P
Protected poles description	3t 4t 3t + N/2
Neutral position	Left
Trip unit protection functions	LSolR
Protection type	L : for overload protection (long time) So : for short time short-circuit protection with fixed delay I : for instantaneous short-circuit protection R : for earth-leakage protection
Trip unit rated current	400 A at 40 °C
[Ue] rated operational voltage	440 V AC 50/60 Hz
Network type	AC
Network frequency	50/60 Hz

Complementary

Long-time pick-up adjustment type Ir (thermal protection)	Adjustable 9 settings
[Ir] long-time protection pick-up adjustment range	160...400 A
Long-time protection delay adjustment type tr	Fixed
[Tr] long-time protection delay adjustment range	11 s at 7.2 x Ir 16 s at 6 x Ir 400 s at 1.5 x Ir

Thermal memory	20 minutes before and after tripping
Short-time protection pick-up adjustment type Isd	Adjustable
[Isd] Short-time protection pick-up adjustment range	1.5...10 x Ir
Short-time protection delay adjustment type tsd	Fixed
[Tsd] Short-time protection delay adjustment range	0.02 s
Instantaneous protection pick-up adjustment type li	Fixed
[li] instantaneous protection pick-up adjustment range	4800 A
Earth-leakage protection	Integrated
Earth-leakage protection class	Class A
Earth-leakage protection sensitivity adjustment type IΔn	Adjustable
[IΔn] earth-leakage protection sensitivity adjustment range	1 A 500 mA 3 A 300 mA 10 A 5 A
Earth-leakage protection specific mode	OFF using the IΔn rotary switch
Earth-leakage protection time delay adjustment type Δt	Adjustable
[Δt] Earth-leakage protection time delay adjustment range	0 ms 150 ms 60 ms 500 ms 1 s
Neutral protection settings	0.5 x Ir (3t + N/2) 1 x Ir (4t) No protection (3t)
Zone selective interlocking ZSI	Without
Local signalling	Flashing LED (green) for ready to operate LED 105 % Ir (red) for overload LED 90 % Ir (orange) for overload Color indicator (yellow) for residual current

Environment

Standards	EN 60947-2 UL 508 IEC 60947-2 NEMA AB1
Product certifications	CB CCC EAC
Electrical shock protection class	Class II
Pollution degree	3 conforming to IEC 60947-1
IP degree of protection	IP40 conforming to IEC 60529
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	2.356 kg
Package 1 Height	17.0 cm
Package 1 width	21.4 cm
Package 1 Length	26.0 cm
Unit Type of Package 2	P06
Number of Units in Package 2	16
Package 2 Weight	48.44 kg
Package 2 Height	75.0 cm
Package 2 width	60.0 cm
Package 2 Length	80.0 cm
Unit Type of Package 3	S03
Number of Units in Package 3	2
Package 3 Weight	5.181 kg
Package 3 Height	30.0 cm
Package 3 width	30.0 cm
Package 3 Length	40.0 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
PVC free	Yes
California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)

LV433932 is replaced by:

1x



Trip unit MicroLogic Vigi 4.3, ComPacT NSX400/630, 4 poles, electronic basic and earth leakage protections, 400A rating

C4044V400
