

# Reflex iC60H Ti24 25 A 2P curve D integrated control MCB

Local distributor code: 399364266 A9C66225

EAN Code: 3606480455216

## Main

Device application	Control Distribution	
Range	Acti9	
product name	Reflex iC60	
Device short name	Reflex iC60H	
Product or component type	Integrated control circuit breaker	
Poles description	2P	
Number of protected poles	2	
Network type	AC	
Trip unit technology	Thermal-magnetic	
Curve code	D	

# Complementary

J		
[In] rated current	25 A	
Network frequency	50/60 Hz	
Breaking capacity code	н	
Breaking capacity	30 kA Icu at 220240 V AC 50/60 Hz conforming to EN/IEC 60947-2 15 kA Icu at 380415 V AC 50/60 Hz conforming to EN/IEC 60947-2	
[Ui] rated insulation voltage	500 V AC	
Contact position indicator	Yes	
Control type	Remote control by pulse ON/OFF button Remote control by continuous command Toggle	
Control signal type	Maintained Maintained very low voltage Impulse	
Local signalling	Flashing LED: device ready Green LED: device ON Red LED: fault Flashing LED: device tripped Flashing LED: device overheat	
[Uc] control circuit voltage	230 V AC 50/60 Hz 24 V AC 50/60 Hz 48 V AC 50/60 Hz 24 V DC 48 V DC	
[Us] rated supply voltage	230 V AC at 50/60 Hz	
Mounting mode	Fixed	

Mounting support	35 mm symmetrical DIN rail	
9 mm pitches	9	
Height	84 mm	
Width	81 mm	
Depth	77 mm	
Colour	White	
Mechanical durability	50000 cycles	
Electrical durability	AC-1: 50000 cycles AC 50 Hz	
Provision for padlocking	Padlockable	
Locking options description	Padlock in OFF position	
Earth-leakage protection	Separate block	
Product compatibility	With PLC	

## **Environment**

IP degree of protection	IP20 conforming to IEC 60529	
Pollution degree	3	
Tropicalisation	2	
Relative humidity	93 % at 40 °C	

# **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.000 cm
Package 1 Width	11.000 cm
Package 1 Length	16.800 cm
Package 1 Weight	569.900 g
Unit Type of Package 2	S03
Number of Units in Package 2	14
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	8.467 kg

# **Logistical informations**

Country of origin ES

# **Contractual warranty**

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

#### Environmental Data explained >

How we assess product sustainability >

## ☑ Environmental footprint

Environmental Disclosure

Product Environmental Profile

#### **Use Better**

<b>⊗</b> Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Compliant with Exemptions
SCIP Number	8e8587cb-1e8e-4934-ae0d-4f8ec8c2b050
REACh Regulation	REACh Declaration
PVC free	No

### **Use Again**

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins