

Dust Blower XGT®

AS001G

40Vmax • 200 m/s • 1,1 m³/min

Very compact and lightweight Dust Blower with XGT® Battery.

With a variety of tip nozzles, this model can meet a wide range of applications from professional use to home use, such as various blow-off works, filter cleaning, inflation and deflation of inflatable toys and more.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Max. Air Velocity	200 m/s
Blowing force	1,1 / 1,7 / 2,3 / 2,8 N
Air volume	0,6 / 0,8 / 1,0 / 1,1 m³/min
Max. sealed suction	103 mbar
Max Pressure	0,297 bar
Continuous use XGT® 40Vmax / 2.5 Ah	50 / 25 / 17 / 13 min
Sound Power Level (L _{WA})	90 dB(A)
Sound Pressure Level (L _{pA})	82 dB(A)
Product net weight	0,83 kg
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	1,5 - 2,9 kg

User benefits

- Filter for preventing foreign matter from being sucked in
- 4 stage air volume; selectable according to your application
- Battery protection circuit protects against overloading, over-discharging and over-heating

Link to product - www.makita.dk



Related products

Optional AC

191X11-1 Narrow Nozzle		191X13-7 Nozzle for cleaning filter	
191X15-3 Blower Nozzle		191X17-9 Nozzle for inflating	
191X19-5 Wide Nozzle		191X21-8 Flexible tube nozzle	
191X23-4 Air vent nozzle		191X25-0 Rubber Blow Nozzle Attachment	
191X27-6 Suction Nozzle Attachment 65 Set		191X29-2 Additional filter	

Other

User manual

Parts drawing