

7482-01

Torque wrench DREMOMETER SE A+S

with pre-set value locking and safety device (A+S)

Code ETIM
1427105 ECO02132EAN UNSPSC
4002805927304 27-11-17-15Country of origin eCI@ss
Germany 21-04-02-22Customs tariff number
82041100

Article description

- Technical advantage/Function:
- Pre-set value locking and safety device (A+S) eliminates the possibility of unintentional or manipulated adjustment, thereby representing more process reliability of the user
- Classified as per DIN EN ISO 6789-2:2017 Type II Class A; adjusted to a maximum permissible +/-3 % deviation and thus with a greater precision than the standard-stipulated +/-4 %
- Lightweight yet robust (as the housing is made of an aluminium alloy) and resilient, very workshop-friendly
- Drive offers extensive range of accessories
- Depending on the application, access is possible from the front (e.g. open-end fitting) or side (e.g. reversible ratchet and socket).
- Force to be applied in the middle of the handgrip only - do not use an extension tube as otherwise, inaccuracies can evolve
- Operation only with end fittings otherwise inaccuracies can arise. Keep the depth gauges on the certificate in mind. Only use original GEDORE accessories.
- Extremely low wear attributable to reduced forces in a lever mechanism
- Forged lever chain from our group own quality forge
- Maximum precision even when subjected to extreme continuous use
- Long life cycles and tool lives
- Easy operation - fast and safe torque tightening
- Easy adjustment thanks to attractive adjusting button secured against loss at the end of the handle
- With certificate acc. to DIN EN ISO 6789-2:2017, traceable via in-house DAkkS laboratory to national standards
- Pre-set DREMOMETER for serial production wherever the same value always needs to be applied • If fixed setting at the factory is desired is required, please state the Nm value when ordering (price on request)

Article information

Contents (Qty of pieces)	1	Precision +/-	+/- 3 %
Net weight [kg]	1,7 kg	Direction of tightening	Left and right
Total length [mm]	653 mm	Fixed setting	yes
Total width [mm]	35 mm	Test certificate	DIN EN ISO 6789-2:2017
Total height [mm]	30 mm	Graduation	5
Material	Aluminum alloy	Head height 1 [mm]	30 mm
Depth gauge [metric]	25,0 mm	Width of head 1 [mm]	35,0 mm
Drive type/drive	Rectangular cavity	Torque wrench type	C-SE A+S
Torque (min.) [N·m]	80 Nm	Calibration length	582 mm
Torque (max.) [N·m]	400 Nm	Graduation [lbf·ft]	5 lbf·ft
Torque (min.) [lbf·ft]	60 lbf·ft	Lever length drive side [mm]	53 mm
Torque (max.) [lbf·ft]	300 lbf·ft	Lever length handle side [mm]	600 mm
Torque range [min./max.] [N·m]	80 Nm - 400 Nm	Graduation [n·m]	5 Nm
Torque range (min./max.) [lbf·ft]	60 lbf·ft - 300 lbf·ft	Distance housing - square drive	53 mm
Drive connector rectangular	14 x 18 mm	Insertion depth 1	25,0 mm
Backup	Locking pin	Storage/Content	Box
Trigger mechanism	Short path triggering		