




**Part Number :** [734150965](#)

**Product Description :** MMCX Jack, Straight, PCB Receptacle, End Launch, Brass Body, Gold (Au) Plating, Tape and Reel, Leads Oriented Opposite Feed Holes, 50 Ohms

**Series Number :** 73414

**Status :** Active

**Product Category :** RF / Coaxial Connectors



---

## Documents & Resources

### Drawings

[734150965 sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### [Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

### [Industry Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	RF / Coaxial Connectors
Series	73414
Description	MMCX Jack, Straight, PCB Receptacle, End Launch, Brass Body, Gold (Au) Plating, Tape and Reel, Leads Oriented Opposite Feed Holes, 50 Ohms
Product Name	MMCX
Style	PCB
Type	Microminiature
UPC	800756718422

### Electrical

Frequency	6 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 170 Vrms@Sea Level

### Physical

Cable Attachment	N/A
Gender	Jack
Keying to Mating Part	N/A
Net Weight	0.377/g
Orientation	Straight
Packaging Type	Embossed Tape on Reel

Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	Edge Mount
PCB Thickness - Recommended	Various
Reverse Polar	No
Wire/Cable Type	N/A

### **Solder Process Data**

Max-Duration	10
Lead-Free Process Capability	REFLOW
Max-Cycle	2
Max-Temp	260