



Connectors > Connector Accessories > Connector Caps & Covers



Connector Cover Type: **Protective Cap**
Primary Product Material: **Zinc**
Operating Temperature (Max): **105 °C [221 °F]**
Operating Temperature Range: **-55 – 105 °C [-67 – 221 °F]**

Features

Product Type Features

Sealable	Yes
Connector Cover Type	Protective Cap

Body Features

Primary Product Plating Material	Nickel
Seal Material	Elastomer
Primary Product Material	Zinc

Mechanical Attachment

Component Retention Feature	Metal Bead Chain
-----------------------------	------------------

Housing Features

Compatible With Connector Shape	Circular
---------------------------------	----------

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Operation/Application

Compatible With Connector Shell Size	14
--------------------------------------	----

Packaging Features

Packaging Method	Carton
Packaging Quantity	10



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 208721-1
RECEPT ASSY,SZ 14,CMC



TE Part # 208715-1
RECEPT ASSY,SZ 14-7,CMC



TE Part # 208717-1
RECEPT ASSY,SZ 14,CMC



TE Part # 208719-1
RECEPT ASSY,SZ 14,CPC

Also in the Series | AMP Circular Plastic Connectors



Circular Connector Backshells & Clamps(1)



Circular Power Connectors(423)




Connector Contacts(6)



Connector Hardware(10)



Power Contacts(6)



Sealing Sleeves(2)

Customers Also Bought



TE Part #4-1423159-0
7012PKL=RLY,STD,ON,2P,125VDC,3



TE Part #3-1393766-5
R10-E1Y2-J5.0K=R10



TE Part #91550-1
CCII TYPE VI MLTIMATE PIN/SKT 18-14 ASSY



TE Part #1423161-5
7014PB=RLY,STD,ON,4P,125VDC,7



TE Part #1-1393117-9
KUP-11A15-120=KU



TE Part #33465
TERMINAL,SOLIS R 6 1/4



TE Part #66602-2
III+ PIN,18-14,30AU/FL,LP



TE Part #66601-2
III+ SKT,18-14,30AU/FL,LP



TE Part #208720-1
PLUG ASSY,SZ 14,CMC



TE Part #91539-1
CCII TYPE II SKT 22-14 2x18 ASSY

Documents



Product Drawings

CMC DUST CAP ASSM,SIZE 14

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_213823-2_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_213823-2_B.3d_igs.zip

English

Customer View Model

ENG_CVM_213823-2_B.3d_stp.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_213823-2_H.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_213823-2_H.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_213823-2_H.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMP Circular Connectors for Commercial Signal & Power Applications Continued

English

Product Specifications

Application Specification

English