




Timer Connector System

TE Internal #: 828801-6

Timer Connector System, PCB Mount Header, Horizontal, Wire-to-Board, 18 Position, .22 in [5.6 mm] Centerline, Fully Shrouded, Tin (Sn)

[View on TE.com >](#)

Connectors > PCB Connectors > PCB Headers & Receptacles > LOW & MEDIUM POWER HEADER



Connector System: **Wire-to-Board**
Number of Positions: **18**
Centerline (Pitch): **5.6 mm [.22 in]**
Sealable: **No**
PCB Mount Orientation: **Horizontal**

[All LOW & MEDIUM POWER HEADER \(158\)](#)

Features

Product Type Features

Hybrid Header	No
PCB Connector Assembly Type	PCB Mount Header
Header Type	Fully Shrouded
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Sections	1
Number of Positions	18
PCB Mount Orientation	Horizontal
Number of Rows	2

Body Features

--	--



Primary Product Color	Black
-----------------------	-------

Contact Features

Contact Type	Tab
Mating Tab Width	3 mm[.118 in]
Mating Tab Thickness	.8 mm[.031 in]
Contact Mating Area Plating Material	Tin (Sn)

Termination Features

Termination Method to Printed Circuit Board	Through Hole - Solder
---	-----------------------

Mechanical Attachment

Mounting Holes	With
Mating Retention	With
Mating Alignment	With
PCB Mount Alignment	Without
PCB Mount Retention	With
Mating Retention Type	Locking Interface

Housing Features

Centerline (Pitch)	5.6 mm[.22 in]
--------------------	----------------

Dimensions

Connector Length	61.1 mm[1.358 in]
Connector Width	25.9 mm[1.02 in]
Profile Height from PCB	19 mm[.748 in]

Operation/Application

Shielded	No
Circuit Application	Signal

Packaging Features

Packaging Quantity	245
--------------------	-----

Other

Interface Number	929504
------------------	--------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2022 (223) Candidate List Declared Against: JUL 2021 (219) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # CAT-T4827-CH8172
TIMER, CONNECTOR HOUSING

Also in the Series | Timer Connector System



Automotive Connector Caps & Covers (11)



Automotive Connector Locks & Position Assurance(16)



Automotive Housings(216)



Automotive Seals & Cavity Plugs(31)



Automotive Terminals(140)




Crimp Terminal Housings(13)




Insertion & Extraction Tools(20)



Other Automotive Connector Accessories(1)



PCB Headers & Receptacles(78)



Quick Disconnects(4)

Customers Also Bought




TE Part #5102160-4
A/L UNIV HDR 20P RA



TE Part #4-1601000-1
031-001-000=WIRE2WIRE,STD,SMZ




TE Part #2-825433-0
MOD 2 PINHDR 1X20P.




TE Part #2-2176398-2
3502 100K 1%




TE Part #3-2176372-8
RQ 0603 121K 0.1% 10PPM 5K RL



TE Part #828801-2
2X 3P MESSERLEI 3,0



TE Part #1-927770-1
JPT REC 2.8 Contact SWS Au



TE Part #166642-000
D-SCE-1K-6.4-50-6



Documents

Product Drawings

2X 9P MESSERLEI 3,0

English

CAD Files

Customer View Model

ENG_CVM_CVM_828801-6_E.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_828801-6_E.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_828801-6_E.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English