




Connectors > D-Shaped Connectors > Microminiature & Nanominiature D Connectors



Connector & Housing Type: **Plug**
Connector System: **Cable-to-Board**
Number of Positions: **15**
Mounting Hardware: **Jackpost Assembly**
Centerline (Pitch): **1.27 mm [.05 in]**

Features

Product Type Features

Connector & Housing Type	Plug
Connector System	Cable-to-Board
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	15
---------------------	----

Body Features

Shell Plating Material	Electroless Nickel
Flying Leads Length	2.77 mm[.109 in]

Contact Features

Contact Mating Area Plating Material	Gold (Au)
Contact Type	Pin
Contact Base Material	Beryllium Copper
Contact Options	Installed
Contact Current Rating (Max)	3 A

Termination Features

Termination Method to PCB	Through Hole - Solder
Termination Method to Wire & Cable	Preterminated Flying Leads

Mechanical Attachment



Mounting Hardware	Jackpost Assembly
Connector Mounting Type	Panel Mount

Housing Features

Centerline (Pitch)	1.27 mm[.05 in]
--------------------	-----------------

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2024 (240) SVHC > Threshold: Pb (.2% in component part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1532172-2
M83513/04-B02N, MCKS-N1-B-15S6G1-36.0



TE Part # 1-1532172-1
M83513/04-B15N, MCKS-N1-B-15S6Q1-72.0



TE Part # 1-1532172-2
M83513/04-B16N, MCKS-N1-B-15S6Q9-72.0



TE Part # 1532172-4
M83513/04-B04N, MCKS-N1-B-15S6G9-36.0



TE Part # 1532172-9
M83513/04-B13N, MCKS-N1-B-15S6G1-72.0



TE Part # 1-1532173-0
M83513/04-C14N, MCKS-N1-B-21S6G9-72.0



TE Part # 1532172-5
M83513/04-B09N, MCKS-N1-B-15S6Q1-18.0



TE Part # 1532173-1
M83513/04-C01N, MCKS-N1-B-21S6G1-18.0



TE Part # 1532172-8
M83513/04-B12N, MCKS-N1-B-15S6Q9-36.0



TE Part # 1532172-6
M83513/04-B10N, MCKS-N1-B-15S6Q1-36.0



TE Part # 1532172-7
M83513/04-B11N, MCKS-N1-B-15S6Q9-18.0


Customers Also Bought



TE Part #2-2013289-1
EMBOSS TAPE DDR3 204P 5.2H STD



TE Part #1825058-7
ADE04S04=DIP SWITCH,EXT,SMT-GW



TE Part #282104-1
AMP SUPERSEAL 1.5 SERIES 2P CA



TE Part #1761007-2
SFP 1X2 CAGE & LIGHT PIPE KIT



TE Part #5103309-6
A/L LOW PRO HDR 26P VERT BLACK

Documents



Product Drawings

M83513/10-B01NP = MCKS-N1-P-15PRT1

English