

Han PP Power 4/0 F Plastic Crimp PG13



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 09 35 231 0423 |
| Specification | Han PP Power 4/0 F Plastic Crimp PG13 |
| HARTING eCatalogue | https://harting.com/09352310423 |

Identification

| | |
|----------------|-----------------------------|
| Category | Connectors |
| Series | Han® PushPull (V14) |
| Identification | Power |
| Element | Connector sets |
| Features | Intuitive locking mechanism |

Version

| | |
|--------------------|---|
| Termination method | Crimp termination |
| Shielding | Unshielded |
| Number of contacts | 5 |
| Locking type | PushPull |
| Pack contents | incl. plastic housing and female insert Without contacts |

Technical characteristics

| | |
|-------------------------------|------------------------------|
| Conductor cross-section | 0.25 ... 2.5 mm ² |
| Conductor cross-section [AWG] | AWG 22 ... AWG 12 |
| Rated current | 16 A |
| Rated voltage | 690 V |
| Rated impulse voltage | 8 kV |
| Pollution degree | 3 |
| Rated voltage acc. to UL | 600 V |
| Limiting temperature | -40 ... +70 °C |



Pushing Performance
Since 1945

Technical characteristics

| | |
|--|--|
| Mating cycles | ≥500 |
| Degree of protection acc. to IEC 60529 | IP65 IP67 |
| Clamping range | 9 ... 13 mm |
| Vibration resistance | 5-150 Hz, 5 g, 0.35 mm, 2h/axis |
| Shock resistance | 5 g / 30 ms, 3 shocks / axis and direction |

Material properties

| | |
|---|----------------|
| Material (insert) | Thermoplastic |
| Surface (contacts) | Silver plated |
| Material (hood/housing) | Thermoplastic |
| Colour (hood/housing) | Black |
| Material (O-ring) | NBR |
| Material (cable seal) | TPE |
| Material flammability class acc. to UL 94 | V-0 |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Not contained |
| California Proposition 65 substances | Yes |
| California Proposition 65 substances | Lead Nickel |

Specifications and approvals

| | |
|----------------|--|
| Specifications | IEC 61076-3-118 |
| UL / CSA | UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076 |
| Approvals | DNV GL |

Commercial data

| | |
|-------------------|---------|
| Packaging size | 1 |
| Net weight | 29.8 g |
| Country of origin | Romania |



Pushing Performance
Since 1945

Commercial data

| | |
|--------------------------------|---|
| European customs tariff number | 85366990 |
| GTIN | 5713140054202 |
| eCl@ss | 27440114 Rectangular connector (for field assembly) |
| ETIM | EC002636 |
| UNSPSC 24.0 | 39121408 |

Mating face

