



Switches > Switch Knobs



Primary Product Material: **Phenolic**  
Knob Design: **Straight Knurl**  
Shaft Size: **6.35 mm [ .25 in ]**  
Product Diameter: **25.3 mm [ .996 in ]**  
Primary Product Color: **Black**

Features

Configuration Features

Spinner	Without
Skirt	Without
Spin Plate	Without
Knob Design	Straight Knurl

Body Features

Primary Product Material	Phenolic
Primary Product Color	Black

Dimensions

Shaft Size	6.35 mm[.25 in]
Product Diameter	25.3 mm[.996 in]

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247)



	Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1437624-9  
PK90B1/4=KNOB PLASTIC BLK 1/4

Customers Also Bought




TE Part #173977-6  
CT CONN MT REC ASSY 6P



TE Part #5104338-3  
A/L LOW PRO HDR 16P VERT HT



TE Part #2213929-5  
Z35 MINI LED HOLDER 16\*19  
PANHEAD



TE Part #1393771-9  
JWD-171-14=REED RELAYS



TE Part #1-794231-0  
MINI UMN2 SCKT 20-16AWG LP A



TE Part #2-1623773-5  
C10 470R 5% (LOOSE)



TE Part #1811957-1  
ASY,SCRLESS WIRE CONN,VERT,2P



TE Part #5227673-1  
BNC PCB VERTICAL JACK W/POST



TE Part #1623525-1  
CRG1206 1% 4K7



TE Part #T4162123005-002  
RPC-M12-5MS-1.0SH-M12-5FS-PUR

Documents

Product Drawings

PH15181/4=KNOB PLASTIC CONTROL

English

CAD Files

Customer View Model

ENG\_CVM\_CVM\_1437624-2\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_1437624-2\_A.3d\_stp.zip

English

Customer View Model

ENG\_CVM\_CVM\_1437624-2\_A.2d\_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.