


product type designation

product description

FO Standard Cable GP

Glass fiber-optic cable, preferred length, preassembled

FO Standard Cable GP 50/125, pre-assembled with 2x LC duplex connectors, length 10 m.



suitability for use

Cable for installation indoors and outdoors, UL approval

version of the assembled FO cable

Pre-assembled with 2x LC DUPLEX connectors

cable designation

AT-W(ZN)YY 2x1 G 50/125 OM2++

wire length

10 m

optical data

attenuation factor per length

- at 850 nm / maximum
- at 1300 nm / maximum

2.7 dB/km
0.7 dB/km

bandwidth length product

- at 850 nm
- at 1300 nm

600 GHz·m
1200 GHz·m

mechanical data

number of fibers / per FOC core

1

number of FO cores / per FOC cable

2

version of the FO conductor fiber

Multi-mode gradient fiber 50/125 µm, OM 2

design of the FOC core

Hollow core, filled, diameter 1400 µm

design of the fiber-optic cable

segmentable

outer diameter

- of the optical fibers
- of the optical fiber sheath
- of the FOC core sheath

50 µm
125 µm
2.9 mm

symmetrical deviation / of the outer diameter of the FOC core sheath

0.1 mm

width / of cable sheath

7.4 mm

thickness / of cable sheath

4.5 mm

material

- of the fiber-optic cable core
- of the optical fiber sheath
- of the FOC core sheath
- of the fiber-optic cable sheath
- of the strain relief

Quartz glass
Quartz glass
PVC
PVC
Aramid fibers

color

- of the FOC core sheath
- of cable sheath

orange/black
green

bending radius

- with single bend / minimum permissible
- with multiple bends / minimum permissible

45 mm
65 mm

tensile load

<ul style="list-style-type: none"> during installation / short-term 	1200 N
<ul style="list-style-type: none"> during operation / maximum 	500 N
short-term shear force per length	600 N/cm
continuous shear force per length	400 N/cm
weight per length	40 kg/km
ambient conditions	
ambient temperature	
<ul style="list-style-type: none"> during operation 	-25 ... +80 °C
<ul style="list-style-type: none"> during storage 	-25 ... +80 °C
<ul style="list-style-type: none"> during transport 	-25 ... +80 °C
<ul style="list-style-type: none"> during installation 	-5 ... +50 °C
fire behavior	flame-resistant acc. to IEC 60332-1-2 and IEC 60332-3-22 (Cat. A)
chemical resistance	
<ul style="list-style-type: none"> to mineral oil 	conditional resistance
<ul style="list-style-type: none"> to grease 	conditional resistance
radiological resistance / to UV radiation	resistant
protection class IP	IP20
product features, product functions, product components / general	
product feature	
<ul style="list-style-type: none"> halogen-free 	No
<ul style="list-style-type: none"> silicon-free 	Yes
product component / rodent protection	No
wire length	
<ul style="list-style-type: none"> for glass FOC / for 100BaseFX / for Industrial Ethernet / maximum 	5000 m
<ul style="list-style-type: none"> for glass FOC / for 1000BaseSX / for Industrial Ethernet / maximum 	750 m
<ul style="list-style-type: none"> for glass FOC / for 1000BaseLX / for Industrial Ethernet / maximum 	2000 m
<ul style="list-style-type: none"> for glass FOC / with PROFIBUS / maximum 	3000 m
standards, specifications, approvals	
certificate of suitability	
<ul style="list-style-type: none"> UL approval 	Yes; UL approval: cULus OFN (NEC Article 770, UL 1651) / CSA approval: OFN 90 FT4 (CSA standard C22.2 No. 232)
<ul style="list-style-type: none"> RoHS conformity 	Yes
reference code	
<ul style="list-style-type: none"> according to IEC 81346-2 	WH
<ul style="list-style-type: none"> according to IEC 81346-2:2019 	WHA
further information / internet links	
internet link	
<ul style="list-style-type: none"> to web page: selection aid TIA Selection Tool 	http://www.siemens.com/tia-selection-tool
<ul style="list-style-type: none"> to website: Industrial communication 	http://www.siemens.com/simatic-net
<ul style="list-style-type: none"> to website: Industry Mall 	https://mall.industry.siemens.com
<ul style="list-style-type: none"> to website: Information and Download Center 	http://www.siemens.com/industry/infocenter
<ul style="list-style-type: none"> to website: Selection guide for cables and connectors 	https://sie.ag/2QdlxcP
<ul style="list-style-type: none"> to website: Image database 	http://automation.siemens.com/bilddb
<ul style="list-style-type: none"> to website: CAX-Download-Manager 	http://www.siemens.com/cax
<ul style="list-style-type: none"> to website: Industry Online Support 	https://support.industry.siemens.com

last modified:

9/2/2023 