

**PRODUCT-DETAILS** 

# A43 212-100

# A43 212-100, Energy meter'Bronze', Modbus RS485, Three-phase, 80 A



General Information	
Extended Product Type	A43 212-100
Product ID	2CMA170522R1000
ABB Type Designation	A43 212-100
EAN	7392696705226
Catalog Description	A43 212-100, Energy meter Bronze', Modbus RS485, Three-phase, 80 A
Long Description	Advanced DIN-rail meter with a large and easy to read back lighted pixel-oriented display. The meter is intended for use in the industry, commercial buildings etc. The meter can be used in 3 or 4 wire systems with a wide voltage range. The meter has several instrumentation values, 25 possible alarms and event logs. Three phase direct connected for active and reactive energy. Import and export of energy in different registers and one total. One output for pulses or alarm etc. RS-485 communication over Modbus RTU or EQ Bus. Accuracy class 1.0 (or B for MID meters). The meters is IEC approved + MID approved and verified.

#### Eco Transparency

Environmental Product 9AKK108467A4138
Declaration - EPD

Technical	
Standards	IEC 62052-11
Function	Electricity meter
Sub-Function	Bronze
Rated Voltage (U <sub>r</sub> )	3x57.7-288 V

A43 212-100 2

5 Maximum 80	Rated Current (I <sub>n</sub> )
80	Current Rating
50 / 60 F	Rated Frequency (f)
0.807	
Modbus RS48	Communication Interface
Active Energy Class B MID (±19	Accuracy
Measurement Instrument Directive (MII	Measuring Instrument Conformity
One-Tar	Meter Tariff Rating
1-99999	Pulse Output Rate
	Number of Poles
Three-phas	Number of Phases
	Number of Counter Positions
1 D	Number of Digital In/Outputs
A43 212-10	ABB Type Designation
Direct connecte	Meter Type
DIN ra	Mounting Type
Electric	Pulse Output Type
Digit	Type of Indicator
Polycarbonate in transparent front glass. Glass reinforced polycarbonate i bottom case and upper case. Polycarbonate in terminal cove	Enclosure Material
1 25 mr	Connecting Capacity Main Circuit

Environmental	
Ambient Air Temperature	Operation -40 70 °C
Degree of Protection	IP20
RoHS Status	Following EU Directive 2002/95/EC August 18, 2005 and amendment
Environmental Information	2CMC484004D0001
Conflict Minerals Reporting Template (CMRT)	9AKK108468A3363

Dimensions	
Width in Number of Modular Spacings	7
Product Net Width	123 mm
Product Net Height	26.5 mm
Product Net Depth / Length	65 mm
Product Net Weight	0.448 kg
Size	97X123X65

Container Information	
Package Level 1 Units	box 1 piece
Package Level 1 Width	98 mm
Package Level 1 Height	68 mm
Package Level 1 Depth / Length	144 mm
Package Level 1 Gross Weight	0.538 kg
Package Level 1 EAN	7392696705226

### Ordering

A43 212-100 3

Minimum Order Quantity	1 piece
Customs Tariff Number	90283019
E-Number (Finland)	6625007
E-Number (Sweden)	0980704
Country of Origin	Italy (IT)

Certificates and Declarations (Document Number)	
Declaration of Conformity - CE	2CMC484003D0001
Environmental Information	2CMC484004D0001
Environmental Product Declaration - EPD	9AKK108467A4138
Instructions and Manuals	2CMC484003M0201
RoHS Information	2CMC484006

Popular Downloads	
Data Sheet, Technical Information	2CMC484001M0201
Instructions and Manuals	2CMC484003M0201
Conflict Minerals Reporting Template (CMRT)	9AKK108468A3363

Classifications	
ETIM 7	EC001506 - Kilowatt-hour meter
ETIM 8	EC001506 - Kilowatt-hour meter
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Consumer
CN8	90283019
eClass	V11.0 : 27142316
Object Classification Code	<u>P</u>

Accessories				
Identifier	Description	Туре	Quantity	Unit Of Measure
2CCG000242R0001	SCU100 Control unit	SCU100	1	piece
2CDG110226R0011	QA/S3.16.1 Energy Analyzer, M-Bus, 16 Devices, MDRC	QA/S3.16.1	1	piece
2CDG110227R0011	QA/S3.64.1 Energy Analyzer, M-Bus, 64 Devices, MDRC	QA/S3.64.1	1	piece
2CDG110228R0011	QA/S4.16.1 Energy Analyzer, Modbus RTU, 16 Devices, MDRC	QA/S4.16.1	1	piece
2CDG110229R0011	QA/S4.64.1 Energy Analyzer, Modbus RTU, 64 Devices, MDRC	QA/S4.64.1	1	piece
2CDG110224R0011	QA/S1.16.1 Energy Analyzer, KNX, 16 Devices, MDRC	QA/S1.16.1	1	piece

## Categories

 $Low\ Voltage\ Products\ and\ Systems\ \rightarrow\ Modular\ DIN\ Rail\ Products\ \rightarrow\ Energy\ Efficiency\ Devices\ \rightarrow\ Energy\ Meters$ 

A43 212-100 4

