



NO.1121070074

检 测 报 告

Test Report

样品名称： 圆柱锂离子电池 ICR 16340 3.7V 650mAh

Name of Sample: Cylindrical lithium-ion battery ICR 16340 3.7V
650mAh

委托单位： 东莞市恒耐力新能源科技有限公司

Consignor: Dongguan HengNaiLi New Energy Technology Co., Ltd

上海化工院检测有限公司

Shanghai Institute of Chemical Industry Testing Co., Ltd.



上海化工院检测有限公司 检测报告

Shanghai Institute of Chemical Industry
Testing Co., Ltd. Test Report

NO. 1121070074

1/10

样品名称 Name of Sample	中文 Chinese	圆柱锂离子电池 ICR 16340 3.7V 650mAh	
	英文 English	Cylindrical lithium-ion battery ICR 16340 3.7V 650mAh	
样品编号 Sample No.	1121070074		
委托单位 Consignor	东莞市恒耐力新能源科技有限公司 Dongguan HengNaiLi New Energy Technology Co., Ltd		
生产单位 Manufacturer	东莞市恒耐力新能源科技有限公司 Dongguan HengNaiLi New Energy Technology Co., Ltd		
检测方法 Test method	联合国《试验和标准手册》 ST/SG/AC.10/11/Rev.7 38.3 UN Manual of Tests and Criteria ST/SG/AC.10/11/Rev.7 Section 38.3		
判定标准 Criterion	联合国《试验和标准手册》 ST/SG/AC.10/11/Rev.7 38.3 UN Manual of Tests and Criteria ST/SG/AC.10/11/Rev.7 Section 38.3		
样品外观 Appearance	蓝色 圆柱型塑料薄膜外壳 Blue Cylinder plastics film shell		
样品接受日期 Accepted Date	2021-07-02	检测起迄日期 Test Date	2021-07-13 ~ 2021-08-11
检测项目 Test Items	高度模拟;热测试;振动;冲击;外短路;挤压;强制放电 Altitude simulation, Thermal test, Vibration, Shock, External short circuit, Crush, Forced discharge		
检测结论 Conclusion	经检测, 该样品符合联合国《试验和标准手册》ST/SG/AC.10/11/Rev.7 38.3标准要求。 The sample has passed the test items of UN Manual of Tests and Criteria ST/SG/AC.10/11/Rev.7 Section 38.3 生效日期(Date): 2021-08-12		
备注 Comment	可充电锂电池芯Rechargeable Lithium Cell./		
委托单位地址 Consignor Address	/		邮政编码 Post Code /

批准
Approver:
职务
Title:

张小平

副总工程师(Vice chief engineer)

审核
Checker:

陈建峰

编制
Compiler:

傅佳



上海化工院检测有限公司

检 测 报 告

Shanghai Institute of Chemical Industry
Testing Co., Ltd. Test Report

NO. 1121070074

2/10

序号 No.	检测项目名称 Name of Test Items	标准要求或标准条款号 Standard requirement or The Clause Number of Standard	检测结果 Test Result	本项结论 Conclusion	备注 Remark
1	高度模拟 Altitude simulation	联合国《试验和标准手册》ST/SG/AC.10/11/Rev.7 38.3 试验T1 UN Manual of Tests and Criteria ST/SG/AC.10/11/Rev.7 Section 38.3 Test T1	见附表 1 See Appendix 1	合格 Passed	/
2	热测试 Thermal test	联合国《试验和标准手册》ST/SG/AC.10/11/Rev.7 38.3 试验T2 UN Manual of Tests and Criteria ST/SG/AC.10/11/Rev.7 Section 38.3 Test T2	见附表 2 See Appendix 2	合格 Passed	/
3	振动 Vibration	联合国《试验和标准手册》ST/SG/AC.10/11/Rev.7 38.3 试验T3 UN Manual of Tests and Criteria ST/SG/AC.10/11/Rev.7 Section 38.3 Test T3	见附表 3 See Appendix 3	合格 Passed	/
4	冲击 Shock	联合国《试验和标准手册》ST/SG/AC.10/11/Rev.7 38.3 试验T4 UN Manual of Tests and Criteria ST/SG/AC.10/11/Rev.7 Section 38.3 Test T4	见附表 4 See Appendix 4	合格 Passed	/
5	外短路 External short circuit	联合国《试验和标准手册》ST/SG/AC.10/11/Rev.7 38.3 试验T5 UN Manual of Tests and Criteria ST/SG/AC.10/11/Rev.7 Section 38.3 Test T.5	见附表 5 See Appendix 5	合格 Passed	/
6	挤压 Crush	联合国《试验和标准手册》ST/SG/AC.10/11/Rev.7 38.3 试验T6 UN Manual of Tests and Criteria ST/SG/AC.10/11/Rev.7 Section 38.3 Test T.6	见附表 6 See Appendix 6	合格 Passed	/
7	强制放电 Forced discharge	联合国《试验和标准手册》ST/SG/AC.10/11/Rev.7 38.3 试验T8 UN Manual of Tests and Criteria ST/SG/AC.10/11/Rev.7 Section 38.3 Test T.8	见附表 7 See Appendix 7	合格 Passed	/
8	以下空白	This space intentionally left blank			
检测环境条件 Test Environment Condition		环境温度:22℃-23℃;环境湿度:/% Ambient temperature:22℃-23℃;Ambient humidity:/%			
分包检验情况 Subcontracted Test Condition		检测项目 Test Item	/		
		分包实验室 Subcontracted Laboratory	名称 Name	/	邮编 Post Code
			地址 Address	/	电话 Tel

Shanghai Institute of Chemical Industry
Testing Co., Ltd. Test Report—Appendix 1

3/10

[illegible]

Shanghai Institute of Chemical Industry
Testing Co., Ltd. Test Report—Appendix 2

4/10

备注: L-泄漏 V-漏气 D-解体 R-破裂 F-起火 O-无泄漏、无漏气、无解体、无破裂、无起火。
Note: L-Leakage V-Venting D-Disassembly R-Rupture F-Fire O-No Leakage, No Venting,
No Disassembly, No Rupture & No Fire.

Shanghai Institute of Chemical Industry
Testing Co., Ltd. Test Report—Appendix 3

5/10

备注: L-泄漏 V-漏气 D-解体 R-破裂 F-起火 O-无泄漏、无漏气、无解体、无破裂、无起火。
Note: L-Leakage V-Venting D-Disassembly R-Rupture F-Fire O-No Leakage, No Venting,
No Disassembly, No Rupture & No Fire.

备注: L-泄漏 V-漏气 D-解体 R-破裂 F-起火 O-无泄漏、无漏气、无解体、无破裂、无起火。
Note: L-Leakage V-Venting D-Disassembly R-Rupture F-Fire O-No Leakage, No Venting,
No Disassembly, No Rupture & No Fire.

检测报告-附表5

NO. 1121070074

7/10

序号 No.	5	检测项目名称 Name of Test Items	外短路 External short circuit
样品编号 Sample No.	样品状态 Sample Status	样品表面最高温度 Max. External Temperature /℃	其他现象 Other Event
001	1CYC完全充电 1CYC Fully charged	131.5	O
002	1CYC完全充电 1CYC Fully charged	129.4	O
003	1CYC完全充电 1CYC Fully charged	128.2	O
004	1CYC完全充电 1CYC Fully charged	129.1	O
005	1CYC完全充电 1CYC Fully charged	130.1	O
006	25CYC完全充电 25CYC Fully charged	125.7	O
007	25CYC完全充电 25CYC Fully charged	126.3	O
008	25CYC完全充电 25CYC Fully charged	129.2	O
009	25CYC完全充电 25CYC Fully charged	127.5	O
010	25CYC完全充电 25CYC Fully charged	128.5	O
以下空白	This space intentionally left blank		

备注：D-解体 R-破裂 F-起火 O-无解体、无起火、无破裂。
Note: D-Disassembly R-Ruptur F-Fire O-No Disassembly,No Fire & No Rupture.



[illegible]

上海化工院检测有限公司
检 测 报 告 - 附表7
Shanghai Institute of Chemical Industry
Testing Co., Ltd. Test Report—Appendix 7

NO. 1121070074

9/10

序号 No.	7	检测项目名称 Name of Test Items	强制放电 Forced discharge
样品编号 Sample No.	样品状态 Sample Status	其他现象 Other Event	
021	1CYC完全放电 1CYC Fully discharged	O	
022	1CYC完全放电 1CYC Fully discharged	O	
023	1CYC完全放电 1CYC Fully discharged	O	
024	1CYC完全放电 1CYC Fully discharged	O	
025	1CYC完全放电 1CYC Fully discharged	O	
026	1CYC完全放电 1CYC Fully discharged	O	
027	1CYC完全放电 1CYC Fully discharged	O	
028	1CYC完全放电 1CYC Fully discharged	O	
029	1CYC完全放电 1CYC Fully discharged	O	
030	1CYC完全放电 1CYC Fully discharged	O	
031	25CYC完全放电 25CYC Fully discharged	O	
032	25CYC完全放电 25CYC Fully discharged	O	
033	25CYC完全放电 25CYC Fully discharged	O	
034	25CYC完全放电 25CYC Fully discharged	O	
035	25CYC完全放电 25CYC Fully discharged	O	
036	25CYC完全放电 25CYC Fully discharged	O	
037	25CYC完全放电 25CYC Fully discharged	O	
038	25CYC完全放电 25CYC Fully discharged	O	
039	25CYC完全放电 25CYC Fully discharged	O	
040	25CYC完全放电 25CYC Fully discharged	O	
备注：D-解体 F-起火 O-无解体、无起火。 Note: D-Disassembly F-Fire O-No Disassembly & No Fire.			



报告结束