




Connectors > Terminal Blocks & Strips > PCB Terminal Blocks



Number of Positions: 16

Terminal Block Connector Type: Plug

Connector System: Wire-to-Board

Centerline (Pitch): 3.5 mm [.138 in]

Number of Rows: 1

Features

Product Type Features

Wire Protection	With
Terminal Block Connector Type	Plug
Connector System	Wire-to-Board
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Stacking Configuration	Side Stackable
Number of Positions	16
Number of Rows	1
Wire Entry Angle	180°
Wire Entry Location	Side

Electrical Characteristics

Operating Voltage	300 VAC
-------------------	---------

Body Features

Primary Product Color	Green
-----------------------	-------



Product Orientation	Right Angle
---------------------	-------------

Contact Features

Contact Mating Area Plating Material	Tin (Sn)
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	11 A

Mechanical Attachment

Screw Plating Material	Nickel
Screw Material	Brass
Thread Size	M2

Housing Features

Housing Material	PA 66
Centerline (Pitch)	3.5 mm[.138 in]

Dimensions

Wire Size	30 – 14 AWG
-----------	-------------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Packaging Features

Packaging Quantity	100
--------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Pb (2% in 27178899646)

Article Safe Usage Statements:
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.




Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 1-796693-9
19 POS TERMI-BLOK PLUG STACK




TE Part # 1-796693-7
17 POS TERMI-BLOK PLUG STACK



TE Part # 1-284514-6
16P TERMI-BLOK HDR DIR POL



TE Part # 1-796693-6
16 POS TERMI-BLOK PLUG STACK




TE Part # 1-284512-6
16 POS TERMI-BLOK HDR 900 POLA

Customers Also Bought




TE Part #1734100-7
Champ050 series, 68pos, Au over PdNi



TE Part #172165-1
2 CIR UNIV M-N-L PLUG NATL



TE Part #3-1437565-0
FSM2JSMATR=ON T/R



TE Part #5-146851-1
B/A REELED DRST HDR ASSY, SN



TE Part #5556416-1
[MJ,TE,8P](#)



TE Part #640445-2
[02P MTA156 HDR ASSY FL/STR SN](#)



TE Part #5787745-1
[USB A R/A STAK ASSY THRU HOLE](#)

Documents

Product Drawings

[16 POS TERMI-BLOK PLUG STAC 3,](#)
English

CAD Files

Customer View Model
[ENG_CVM_1-284506-6_C.2d_dxf.zip](#)
English

3D PDF

English
Customer View Model
[ENG_CVM_1-284506-6_C.3d_igs.zip](#)
English

Customer View Model
[ENG_CVM_1-284506-6_C.3d_stp.zip](#)
English

3D PDF

3D
Customer View Model
[ENG_CVM_CVM_1-284506-6_B.2d_dxf.zip](#)
English

Customer View Model
[ENG_CVM_CVM_1-284506-6_B.3d_igs.zip](#)
English

Customer View Model
[ENG_CVM_CVM_1-284506-6_B.3d_stp.zip](#)
English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[BUCHANAN TERMINAL BLOCKS CATALOG - EUROSTYLE TERMINAL BLOCKS](#)
English
[1-1773458-1_EURO_STYLE_TERMINAL_BLOCKS_QRG](#)
English



Product Specifications

Application Specification

English

Agency Approvals

UL

English