

Safety Light Curtain F3SG-R

F3SG-R



- QR code indication for easy troubleshooting
- Smart-click cable connection for fast set-up




Quick and easy installation

Safety light curtains are a suitable product to help fulfil machinery safety standards, but they can be tricky to set up and maintain. That's why we have re-thought, re-designed, and re-invented our F3SG-R series, with special features and smart designs that help you select, install and maintain the ideal light curtain with a minimum of time and effort. For example, we now use snap-in bayonet coupling for fast set up. Also the new torsion resistant bodies help ensure problem-free alignment. And there's more ...

Additional key features

- Advanced version with versatile muting ideal for flexible manufacturing
- Easy version for simple ON/OFF detection
- 100m of cable for flexible wiring and fast set-up
- Up to 20m sensing distance for straightforward integration
- Optical synchronisation for easy alignment
- IP67 protection for reliability in dusty wash-down environments



The highly rigid construction eliminates the problems of top-tobottom twisting. This enables you to set up the curtain more easily and faster. It also prevents incremental optical axis misalignment due to vibration over time.



QR code for easy troubleshooting

If something is wrong, simply scan the reported QR code with your smart phone and go directly to the troubleshooting webpage. Supported in eight languages: Chinese, English, French, German, Italian, Japanese, Korean and Spanish.



Smartclick® cable connection for fast set-up

No torque-control required: the Smartclick connectors connect cables with just a 1/8th turn of the M12 waterproof connector. This connection reduces the time you need for wiring many devices together.

Family features and benefits

EASY ADVANCED Easy adjustment – even after mounting

Our fixed mounting brackets, which are included as standard, allow you to slide the safety light curtain up and down to make vertical adjustments. While our optional adjustable mounting brackets provide vertical as well as horizontal adjustment of $\pm 15^{\circ}$.



EASY ADVANCED Choice of detection capabilities

- Two versions available: hand protection (30mm) and finger protection (14mm)
- Sensing distances range from 0.3m to 20.0m
- Heights from 160mm to 2,500mm






EASY ADVANCED


Simple 'two-step' beam adjustment

Simply position the safety light curtain in place and watch for the top and bottom LEDs to illuminate when adjustment is completed.



EASY ADVANCED Optional extra protection

You can add extra protection to the optical surface of your F3SG-R Safety Light Curtain with our special cover (F39-HGA and/or F39-HGB) to prevent scratches and other mechanical impacts.



EASY ADVANCED

Built for wash-down and dusty environments

The F3SG-R Safety Light Curtain Series meets IP67 protection rating to be used in wash-down and dusty applications.



EASY ADVANCED Automatic emitter-receiver synchronization

Our two-step optical synchronisation means you do not need to synchronise the wiring between the emitter and receiver. So you save even more time. Also, the resulting flexible wiring reduces disconnection risk and avoids noise sources.



EASY F3SG-RE Easy version for cost-efficiency

We have developed a basic ON/OFF version that's ideal for simple


- Fastest (5ms) response time on the market for the shortest safety light curtain height
- Reduced wiring, thanks to prewired connectors, for fast installation
- Fast, easy troubleshooting via QR codes
- Clear LED ON/OFF indication



Optimising safety throughout your production line with F3SG-RA

ADVANCED Blanking

The F3SG-RA provides floating and fixed blanking functions. Setting of the number of beams can be configured by specifying the number of beams manually using the SD Manager 2 or in Dip-Switch mode by moving an interrupting object in the detection zone using the Push Switch to perform the teach-in task.



ADVANCED Reduced Resolution

With Reduced Resolution the F3SG-RA is able to ignore interrupted beams (1 to 3 floating beams). This changes the detection capability of the safety light curtain and supports more flexible safety, e.g. where objects are moving within the detection zone.



ADVANCED Cascading


Up to three sets of F3SG-R can be series-connected. Cascade connection allows them to be used as one safety light curtain, requiring only one set to be wired to a controller and preventing mutual interference. If any one set of series-connected F3SG-R is blocked, both of the safety outputs turn OFF.


- Number of connections: up to 3 sets
- Total number of beams: up to 255 beams
- Total sum of cable lengths between cascaded segments: 10m max.

ADVANCED Pre-reset


The pre-reset button prevents the restart of a machine while an unseen worker is still inside the cell.

- **A** A local pre-reset pushbutton inside the machine needs to be pressed before the safety system can be reset
- **B** Safety light curtain for easy access, for example by a forklift truck
- **C** Reset pushbutton to acknowledge and start.









Pass the safety light curtain to walk out of the dangerous area



Press the Reset Button outside the dangerous area

Muting with F3SG-RA

ADVANCED

Automated production systems can be protected using fixed guards, but where material goes in and out of a danger zone, muting can aid efficiency without affecting operator safety.

A full range of muting options is available with F3SG-RA Safety Light Curtains using standard Omron accessories.

F3SG-RA provides 3 different muting modes:


- Standard muting mode (T-Shape Muting and X-Shape Muting)
- Exit only muting mode (L-Shape muting)
- Position detection mode (E.g. Robot is stopped in a safe position)

The following settings are available for a beam range to be the muting state.


- Full range muting
- Partial range muting
- Dynamic range muting

Dynamic Muting

When workpieces with various heights are conveyed on the same line, the dynamic muting function automatically sets the appropriate beams, based on the height of the workpiece.




X-Shape Muting



Dynamic Muting used in L-Shape Muting

Smart muting actuator

The Smart Muting Actuator extends the functions of the F3SG-RA in applications where a workpiece is vibrating forward and backward or where the goods on the pallet have small gaps.



Smart Muting Actuator used in T-Shape Muting

Configuration Tool SD Manager2

Minimizing setting and detection errors

The Configuration Tool SD Manager2 visualizes your installation positions and settings, and helps ensure reliable, first-time-right configuration. In addition, you can analyse any stops due to muting error using the data stored in the F3SG-R, this will minimize unexpected machine downtime.



List of features

Feature	Advanced type F3SG-RA	Easy type F3SG-RE	Factory default setting
PNP/NPN Selection	•		PNP output
External Test	•		24 V Active
Interlock	•		Auto Reset Mode
Pre-Reset	•		Disabled
External Device Monitoring (EDM)	•		Disabled
Auxiliary Output			Muting/Override information
Muting			Standard Muting mode
Override			Enabled
Fixed Blanking	•		Disabled
Floating Blanking	•		Disabled
Reduced Resolution			Disabled
Warning Zone			Disabled
Scan Code Selection	•		CodeA
Operating Range Selection	•	0	Short mode
Response Time Adjustment			Standard mode
Lamp	•		Red: Disabled Orange: Disabled Green: Muting/Override information
Designated Beam Output	•		Disabled

- Setting by DIP Switch
- Setting by Configuration Tool
- Setting by Wiring





Advanced type for complex safety solutions

The F3SG-RA advanced safety light curtain provides simplicity in mounting, daily use and maintenance.

- Torsion-resistant for fast and simple alignment
- Smart-click cable connection for fast set-up and proper torque to ensure IP67
- · QR code indication for easy online troubleshooting
- PNP/NPN output selection by DIP switch
- Cascading connection up to 3 segments and up to 255 beams
- Built in blanking, muting and reset functions

Ordering information

Sensors

Application	Туре	Detection capability	Operating range	Protective height	Order code
Finger detection	Type 4 / Type 2	14 mm	0.3 to 10 m	160 to 2,080 mm	F3SGRA14
Hand detection	Type 4 / Type 2	30 mm	0.3 to 20 m	190 to 2,510 mm	F3SGRA30

F3SG-RA_14 models (14 mm detection capability)

Protective	Number of	Order code	
height	beams	Type 4	Type 2
160 mm	15	F3SG-4RA0160-14	F3SG-2RA0160-14
240 mm	23	F3SG-4RA0240-14	F3SG-2RA0240-14
320 mm	31	F3SG-4RA0320-14	F3SG-2RA0320-14
400 mm	39	F3SG-4RA0400-14	F3SG-2RA0400-14
480 mm	47	F3SG-4RA0480-14	F3SG-2RA0480-14
560 mm	55	F3SG-4RA0560-14	F3SG-2RA0560-14
640 mm	62	F3SG-4RA0640-14	F3SG-2RA0640-14
720 mm	71	F3SG-4RA0720-14	F3SG-2RA0720-14
800 mm	79	F3SG-4RA0800-14	F3SG-2RA0800-14
880 mm	87	F3SG-4RA0880-14	F3SG-2RA0880-14
960 mm	95	F3SG-4RA0960-14	F3SG-2RA0960-14
1040 mm	103	F3SG-4RA1040-14	F3SG-2RA1040-14
1120 mm	111	F3SG-4RA1120-14	F3SG-2RA1120-14
1200 mm	119	F3SG-4RA1200-14	F3SG-2RA1200-14
1280 mm	127	F3SG-4RA1280-14	F3SG-2RA1280-14
1360 mm	135	F3SG-4RA1360-14	F3SG-2RA1360-14
1440 mm	143	F3SG-4RA1440-14	F3SG-2RA1440-14
1520 mm	151	F3SG-4RA1520-14	F3SG-2RA1520-14
1600 mm	159	F3SG-4RA1600-14	F3SG-2RA1600-14
1680 mm	167	F3SG-4RA1680-14	F3SG-2RA1680-14
1760 mm	175	F3SG-4RA1760-14	F3SG-2RA1760-14
1840 mm	183	F3SG-4RA1840-14	F3SG-2RA1840-14
1920 mm	191	F3SG-4RA1920-14	F3SG-2RA1920-14
2000 mm	199	F3SG-4RA2000-14	F3SG-2RA2000-14
2080 mm	207	F3SG-4RA2080-14	F3SG-2RA2080-14

F3SG-RA_30 models (30 mm detection capability)

Protective Number of		Order code	
height	beams	Type 4	Type 2
190 mm	8	F3SG-4RA0190-30	F3SG-2RA0190-30
270 mm	12	F3SG-4RA0270-30	F3SG-2RA0270-30
350 mm	16	F3SG-4RA0350-30	F3SG-2RA0350-30
430 mm	20	F3SG-4RA0430-30	F3SG-2RA0430-30
510 mm	24	F3SG-4RA0510-30	F3SG-2RA0510-30
590 mm	28	F3SG-4RA0590-30	F3SG-2RA0590-30
670 mm	32	F3SG-4RA0670-30	F3SG-2RA0670-30
750 mm	36	F3SG-4RA0750-30	F3SG-2RA0750-30
830 mm	40	F3SG-4RA0830-30	F3SG-2RA0830-30
910 mm	44	F3SG-4RA0910-30	F3SG-2RA0910-30
990 mm	48	F3SG-4RA0990-30	F3SG-2RA0990-30
1070 mm	52	F3SG-4RA1070-30	F3SG-2RA1070-30
1150 mm	56	F3SG-4RA1150-30	F3SG-2RA1150-30
1230 mm	60	F3SG-4RA1230-30	F3SG-2RA1230-30
1310 mm	64	F3SG-4RA1310-30	F3SG-2RA1310-30
1390 mm	68	F3SG-4RA1390-30	F3SG-2RA1390-30
1470 mm	72	F3SG-4RA1470-30	F3SG-2RA1470-30
1550 mm	76	F3SG-4RA1550-30	F3SG-2RA1550-30
1630 mm	80	F3SG-4RA1630-30	F3SG-2RA1630-30
1710 mm	84	F3SG-4RA1710-30	F3SG-2RA1710-30
1790 mm	88	F3SG-4RA1790-30	F3SG-2RA1790-30
1870 mm	92	F3SG-4RA1870-30	F3SG-2RA1870-30
1950 mm	96	F3SG-4RA1950-30	F3SG-2RA1950-30
2030 mm	100	F3SG-4RA2030-30	F3SG-2RA2030-30
2110 mm	104	F3SG-4RA2110-30	F3SG-2RA2110-30
2190 mm	108	F3SG-4RA2190-30	F3SG-2RA2190-30
2270 mm	112	F3SG-4RA2270-30	F3SG-2RA2270-30
2350 mm	116	F3SG-4RA2350-30	F3SG-2RA2350-30
2420 mm	120	F3SG-4RA2430-30	F3SG-2RA2430-30
2510 mm	124	F3SG-4RA2510-30	F3SG-2RA2510-30

Accessories (Sold separately)

Single-end connector cable

Appearance	Туре	Specification			Cable length	Order code
	Emitter cable		1 + 24 VDC	Brown	3 m	F39-JG3A-L
	M12 connector 5-Pin	0 0	2 TEST	Black	7m	F39-JG7A-L
	Color: Gray		3 0 VDC	Blue	10 m	F39-JG10A-L
			4 Not used	White	15 m	F39-JG15A-L
4		Female	5 Not used	Yellow	20 m	F39-JG20A-L
00	Receiver cable M12 connector	60	1 Reset	Yellow	3 m	F39-JG3A-D
	8-Pin	(0 ° ° °)	2 + 24 VDC	Brown	7m	F39-JG7A-D
	Color: Black		3 MUTE A	Gray		
			4 MUTEB	Pink	10 m	F39-JG10A-D
		Female	5 OSSD 1	Black		
			6 OSSD 2	White	15 m	F39-JG15A-D
			7 0 VDC	Blue		
			8 AUX(Lamp)	Red	20 m	F39-JG20A-D


Double-end connector cable

Appearance	Туре	Specification		Cable length	Order code
	Emitter cable	Connected to power cable	Connected to single-ended cable, or	0.5 m	F39-JGR5B-L
	M12 connector	or double-ended cable	double-ended cable	1 m	F39-JG1B-L
	5-Pin Color: Gray	① ② 1 Brown 3 Blue	1 Brown 3 Blue	3 m	F39-JG3B-L
	(0.01.010)	(3) 2 Black 4 White	2 Black 4 White	5 m	F39-JG5B-L
		Female 5 Yellow	5 Yellow Male	7m	F39-JG7B-L
				10 m	F39-JG10B-L
				15 m	F39-JG15B-L
				20 m	F39-JG20B-L
	Receiver cable	Connected to power cable or double-ended cable	Connected to single-ended cable, or double-ended cable	0.5 m	F39-JGR5B-D
d	M12 connector	or double-ended cable 2 Brown	2 Brown	1 m	F39-JG1B-D
	8-Pin Color: Black	7 Blue 5 Black 6 White	7 Blue 0 0	3 m	F39-JG3B-D
	COIOT. DIGER	\\ (0) - (4) // - White	6 White	5 m	F39-JG5B-D
			X 10.4	7m	F39-JG7B-D
		Female 3 Gray 4 Pink	8 Red Male 3 Gray 4 Pink	10 m	F39-JG10B-D
		* PINK	9 11115	15 m	F39-JG15B-D
				20 m	F39-JG20B-D

Y-joint Plug/Socket Connector

Appearance	Туре	Specification	Cable length	Order code
	M12 connectors. Used for reduced wiring.	F3SG-RA Emitter Page 1 Page 2 Page 2 Page 3 Page 3 Page 4 Page 3 Page 4 Page	0.5 m	F39-GCNY2

Cascading cable



Mounting brackets

Appearance	Type	Specification	Order code
000	Standard fixed bracket set (Two brackets per set)	Bracket to mount the F3SG-R. Side mounting and backside mounting possible. (Included in the F3SG-R product package *1)	F39-LGF
	Standard adjustable bracket set (Two brackets per set)	Bracket to mount the F3SG-R. Beam alignment after mounting possible. The angle adjustment range is ±15°. Side mounting and backside mounting possible.	F39-LGA

*1 F3SG-_RA____-14: Protective height of 0160 to 1200: 2 sets, protective height of 1280 to 2080: 3 sets F3SG-_RA____-30; Protective height of 0190 to 1230: 2 sets, protective height of 1310 to 2270: 3 sets, protective height of 2350 to 2510: 4 sets

Interface units and configuration tool SD Manager 2

Appearance	Туре	Specification	Order code
		The configuration tool SD Manager 2 is available to download from our website at http://www.ia.omron.com/f3sg-r_tool. To change the settings of the F3SG-RA using SD Manager 2, it is necessary to set the receiver's two DIP switches No. 8 to ON.	-
	Interface unit	F39-GIF interface unit to connect the F3SG-RA receiver to a USB port of the PC	F39-GIF

Lamp

Appearance	Туре	Specification	Order code
L		The lamp unit can be connected to a receiver and turned ON based on the operation of F3SG-RA. The lamp can indicate red, orange, and green colors, to which three different states can be assigned.	F39-LP

Test rod

Appearance	Туре	Specification	Order code
	Test rod 14mm	14 mm diameter	F39-TRD14
	Test rod 30mm	30 mm diameter	F39-TRD30

Spatter protection covers include mounting brackets.

For safety light curtain models of the protective height of 2,000 mm or longer, use two spatter protection covers of different lengths.

Appearance	Safety light curtain model		Order code
	Finger protection	Hand and arm protection	
	F3SGRA0160-14	F3SGRA0190-30	F39-HGA0200
	F3SGRA0240-14	F3SGRA0270-30	F39-HGA0280
	F3SGRA0320-14	F3SGRA0350-30	F39-HGA0360
	F3SGRA0400-14	F3SGRA0430-30	F39-HGA0440
	F3SGRA0480-14	F3SGRA0510-30	F39-HGA0520
	F3SGRA0560-14	F3SGRA0590-30	F39-HGA0600
	F3SGRA0640-14	F3SGRA0670-30	F39-HGA0680
	F3SGRA0720-14	F3SGRA0750-30	F39-HGA0760
	F3SGRA0800-14	F3SGRA0830-30	F39-HGA0840
	F3SGRA0880-14	F3SGRA0910-30	F39-HGA0920
	F3SGRA0960-14	F3SGRA0990-30	F39-HGA1000
	F3SGRA1040-14	F3SGRA1070-30	F39-HGA1080
filmen.	F3SGRA1120-14	F3SGRA1150-30	F39-HGA1160
_	F3SGRA1200-14	F3SGRA1230-30	F39-HGA1240
	F3SGRA1280-14	F3SGRA1310-30	F39-HGA1320
_	F3SGRA1360-14	F3SGRA1390-30	F39-HGA1400
	F3SGRA1440-14	F3SGRA1470-30	F39-HGA1480
_	F3SGRA1520-14	F3SGRA1550-30	F39-HGA1560
-	F3SGRA1600-14	F3SGRA1630-30	F39-HGA1640
_	F3SGRA1680-14	F3SGRA1710-30	F39-HGA1720
_	F3SGRA1760-14	F3SGRA1790-30	F39-HGA1800
_	F3SGRA1840-14	F3SGRA1870-30	F39-HGA1880
_	F3SGRA1920-14	F3SGRA1950-30	F39-HGA1960
_	F3SGRA2000-14	F3SGRA2030-30	F39-HGA1480
			F39-HGA0550
	F3SGRA2080-14	F3SGRA2110-30	F39-HGA1560
			F39-HGA0550
	-	F3SGRA2190-30	F39-HGA1640
			F39-HGA0550
	_	F3SGRA2270-30	F39-HGA1720
			F39-HGA0550
	_	F3SGRA2350-30	F39-HGA1800
			F39-HGA0550
	_	F3SGRA2430-30	F39-HGA1880
			F39-HGA0550
	_	F3SGRA2510-30	F39-HGA1960
			F39-HGA0550

Note: The operating range of the safety light curtain attached with the product is 10% shorter than the rating.

Spare parts

Appearance	Туре	Specification	Order code
	End cap	Housing color: Black For both emitter and receiver (Attached to the F3SG-R. The end cap can be purchased if lost.)	F39-CNM

Specifications


F3SG-RA

Item		F3SG-4RA14 F3SG-2RA14	F3SG-4RA30 F3SG-2RA30		
Type of ESPE (IEC 61496-1)	Type 4	F3SG-4RA14/-30			
	Type 2	F3SG-2RA14/-30			
Detection capability (Opaque objects)		14 mm dia.	30 mm dia.		
Protective height		160 to 2080 mm	190 to 2510 mm		
Operating range (Dip switch option)		0.3 to 3.0 m or 0.3 to 10.0 m	0.3 to 7.0 m or 0.3 to 20.0 m		
Effective aperture angle (EAA)	Type 4	±2.5° max., emitter and receiver at operating range of 3 m or	greater		
(IEC 61496-2)	Type 2	±5.0° max., emitter and receiver at operating range of 3 m or	greater		
Light source	-	Infrared LEDs, Wavelength: 870 nm			
Power supply voltage (Vs)		SELV/PELV 24 VDC ±20% (ripple p-p 10% max.)			
Safety outputs (OSSD)		2 PNP or NPN transistor outputs (PNP or NPN selectable by DI	2 PNP or NPN transistor outputs (PNP or NPN selectable by DIP switch), load current of 300 mA max.		
Cascade connection		Number of cascaded segments: 3 max., total number of beams: 255 max. Total sum of cable lengths between sensors: 10 m max.			
Test function		Self-test (at power-on, and during operation), External test (light emission stop function by test input)			
Safety-related functions		Interlock, pre-reset, external device monitoring (EDM), fixed blanking/floating blanking, reduced resolution, muting/override, scan code selection, PNP/NPN selection, response time adjustment			
Response time		ON to OFF (normal mode): 8 to 18 ms max., OFF to ON: 40 to 90 ms max.			
Ambient temperature	Operating	−10 to 55°C (non-icing)			
	Storage	-25 to 70°C			
Ambient humidity	Operating	35% to 85% (non-condensing)			
	Storage	35% to 95%			
Degree of protection (IEC 60529)		IP65 and IP67			
Material		Housing: Aluminum, Cap: PBT, Front window: PMMA, Cable: Oil resistant PVC, Mounting bracket: ZDC2, FE plate: SUS			
Performance level (PL)/	Type 4	PLe/Category 4 (EN ISO 13849-1:2008)			
Safety category Type 2		PLc/Category 2 (EN ISO 13849-1:2008)			
PFHd		$\leq 9.9 \times 10^{-8} \text{ (IEC 61508)}$			
Proof test interval T _M		Every 20 years (IEC 61508)			

Note: For more information, please check the user manual Z352-E1

Connections (Basic wiring diagram)

Standalone F3SG-RA using PNP outputs





Safety light curtain

C C CUL US

Easy type for simple ON/OFF detection applications

The F3SG-RE easy safety light provides simplicity in mounting, daily use and maintenance.

- Torsion-resistant for fast and simple alignment
- Smart-click cable connection for fast set-up and proper torque to ensure IP67
- · QR code indication for easy online troubleshooting

Ordering information

Sensors

Application	Туре	Detection capability	Operating range	Protective height	Order code
Finger detection	Type 4 / Type 2	14 mm	0.3 to 10 m	160 to 2,080 mm	F3SGRE14
Hand detection	Type 4 / Type 2	30 mm	0.3 to 20 m	190 to 2,510 mm	F3SGRE30

F3SG-RE_P14 models (PNP and 14 mm detection capability)

Protective	Number of	Order code				
height	beams	Type 4	Type 2			
160 mm	15	F3SG-4RE0160P14	F3SG-2RE0160P14			
240 mm	23	F3SG-4RE0240P14	F3SG-2RE0240P14			
320 mm	31	F3SG-4RE0320P14	F3SG-2RE0320P14			
400 mm	39	F3SG-4RE0400P14	F3SG-2RE0400P14			
480 mm	47	F3SG-4RE0480P14	F3SG-2RE0480P14			
560 mm	55	F3SG-4RE0560P14	F3SG-2RE0560P14			
640 mm	62	F3SG-4RE0640P14	F3SG-2RE0640P14			
720 mm	71	F3SG-4RE0720P14	F3SG-2RE0720P14			
800 mm	79	F3SG-4RE0800P14	F3SG-2RE0800P14			
880 mm	87	F3SG-4RE0880P14	F3SG-2RE0880P14			
960 mm	95	F3SG-4RE0960P14	F3SG-2RE0960P14			
1040 mm	103	F3SG-4RE1040P14	F3SG-2RE1040P14			
1120 mm	111	F3SG-4RE1120P14	F3SG-2RE1120P14			
1200 mm	119	F3SG-4RE1200P14	F3SG-2RE1200P14			
1280 mm	127	F3SG-4RE1280P14	F3SG-2RE1280P14			
1360 mm	135	F3SG-4RE1360P14	F3SG-2RE1360P14			
1440 mm	143	F3SG-4RE1440P14	F3SG-2RE1440P14			
1520 mm	151	F3SG-4RE1520P14	F3SG-2RE1520P14			
1600 mm	159	F3SG-4RE1600P14	F3SG-2RE1600P14			
1680 mm	167	F3SG-4RE1680P14	F3SG-2RE1680P14			
1760 mm	175	F3SG-4RE1760P14	F3SG-2RE1760P14			
1840 mm	183	F3SG-4RE1840P14	F3SG-2RE1840P14			
1920 mm	191	F3SG-4RE1920P14	F3SG-2RE1920P14			
2000 mm	199	F3SG-4RE2000P14	F3SG-2RE2000P14			
2080 mm	207	F3SG-4RE2080P14	F3SG-2RE2080P14			

F3SG-RE_P30 models (PNP and 30 mm detection capability)

Protective Number of		Order code				
height	beams	Type 4	Type 2			
190 mm	8	F3SG-4RE0190P30	F3SG-2RE0190P30			
270 mm	12	F3SG-4RE0270P30	F3SG-2RE0270P30			
350 mm	16	F3SG-4RE0350P30	F3SG-2RE0350P30			
430 mm	20	F3SG-4RE0430P30	F3SG-2RE0430P30			
510 mm	24	F3SG-4RE0510P30	F3SG-2RE0510P30			
590 mm	28	F3SG-4RE0590P30	F3SG-2RE0590P30			
670 mm	32	F3SG-4RE0670P30	F3SG-2RE0670P30			
750 mm	36	F3SG-4RE0750P30	F3SG-2RE0750P30			
830 mm	40	F3SG-4RE0830P30	F3SG-2RE0830P30			
910 mm	44	F3SG-4RE0910P30	F3SG-2RE0910P30			
990 mm	48	F3SG-4RE0990P30	F3SG-2RE0990P30			
1070 mm	52	F3SG-4RE1070P30	F3SG-2RE1070P30			
1150 mm	56	F3SG-4RE1150P30	F3SG-2RE1150P30			
1230 mm	60	F3SG-4RE1230P30	F3SG-2RE1230P30			
1310 mm	64	F3SG-4RE1310P30	F3SG-2RE1310P30			
1390 mm	68	F3SG-4RE1390P30	F3SG-2RE1390P30			
1470 mm	72	F3SG-4RE1470P30	F3SG-2RE1470P30			
1550 mm	76	F3SG-4RE1550P30	F3SG-2RE1550P30			
1630 mm	80	F3SG-4RE1630P30	F3SG-2RE1630P30			
1710 mm	84	F3SG-4RE1710P30	F3SG-2RE1710P30			
1790 mm	88	F3SG-4RE1790P30	F3SG-2RE1790P30			
1870 mm	92	F3SG-4RE1870P30	F3SG-2RE1870P30			
1950 mm	96	F3SG-4RE1950P30	F3SG-2RE1950P30			
2030 mm	100	F3SG-4RE2030P30	F3SG-2RE2030P30			
2110 mm	104	F3SG-4RE2110P30	F3SG-2RE2110P30			
2190 mm	108	F3SG-4RE2190P30	F3SG-2RE2190P30			
2270 mm	112	F3SG-4RE2270P30	F3SG-2RE2270P30			
2350 mm	116	F3SG-4RE2350P30 F3SG-2RE2350P30				
2420 mm	120	F3SG-4RE2430P30	F3SG-2RE2430P30			
2510 mm	124	F3SG-4RE2510P30	F3SG-2RE2510P30			

Note: Optional NPN models are available for the F3SG-RE easy types. Please contact your OMRON representative.


Accessories (Sold separately)

Single-end connector cable


F3SG-RE

Appearance	Туре	Specification					Cable length	Order code
	Emitter/receiver cable		PIN	Emitter	Receiver	Color	1 m	XS5F-D421-C80-F
	M12 connector	(0 0)	1	+24 VDC	+24 VDC		2m	XS5F-D421-D80-F
	4-Pin Color: Gray		2	Range setting	OSSD 2		3 m	XS5F-D421-E80-F
	Color: Gray	O O	3	0 VDC	0 VDC	Blue	5 m	XS5F-D421-G80-F
₽		Female	4	Not used	OSSD 1	Black		XS5F-D421-J80-F

Double-end connector cable



Y-joint Plug/Socket Connector



Mounting brackets

Appearance	Туре	Specification	Order code
3,0	Standard fixed bracket set (Two brackets per set)	Bracket to mount the F3SG-R. Side mounting and backside mounting possible. (Included in the F3SG-R product package *1)	F39-LGF
	Standard adjustable bracket set (Two brackets per set)	Bracket to mount the F3SG-R. Beam alignment after mounting possible. The angle adjustment range is $\pm 15^\circ$. Side mounting and backside mounting possible.	F39-LGA

F3SG_RE____-14: Protective height of 0160 to 1200: 2 sets, Protective height of 1280 to 2080: 3 sets F3SG_RE___-30: Protective height of 0190 to 1230: 2 sets, Protective height of 1310 to 2270: 3 sets, Protective height of 2350 to 2510: 4 sets

Test rod

Appearance	Туре	Specification	Order code
	Test rod 14mm	14 mm diameter	F39-TRD14
	Test rod 30mm	30 mm diameter	F39-TRD30





Spatter protection cover (Two covers per set, for emitter and receiver)

Spatter protection covers include mounting brackets.
For safety light curtain models of the protective height of 2,000 mm or longer, use two spatter protection covers of different lengths.

ppearance	Safety light curtain model		Order code
	Finger protection	Hand and arm protection	
	F3SGRE0160-14	F3SGRE0190-30	F39-HGB0180
	F3SGRE0240-14	F3SGRE0270-30	F39-HGB0260
	F3SGRE0320-14	F3SGRE0350-30	F39-HGB0340
	F3SGRE0400-14	F3SGRE0430-30	F39-HGB0420
	F3SGRE0480-14	F3SGRE0510-30	F39-HGB0500
	F3SGRE0560-14	F3SGRE0590-30	F39-HGB0580
	F3SGRE0640-14	F3SGRE0670-30	F39-HGB0660
	F3SGRE0720-14	F3SGRE0750-30	F39-HGB0740
	F3SGRE0800-14	F3SGRE0830-30	F39-HGB0820
	F3SGRE0880-14	F3SGRE0910-30	F39-HGB0900
	F3SGRE0960-14	F3SGRE0990-30	F39-HGB0980
	F3SGRE1040-14	F3SGRE1070-30	F39-HGB1060
film and	F3SGRE1120-14	F3SGRE1150-30	F39-HGB1140
_	F3SGRE1200-14	F3SGRE1230-30	F39-HGB1220
-	F3SGRE1280-14	F3SGRE1310-30	F39-HGB1300
	F3SGRE1360-14	F3SGRE1390-30	F39-HGB1380
	F3SGRE1440-14	F3SGRE1470-30	F39-HGB1460
	F3SGRE1520-14	F3SGRE1550-30	F39-HGB1540
	F3SGRE1600-14	F3SGRE1630-30	F39-HGB1620
	F3SGRE1680-14	F3SGRE1710-30	F39-HGB1700
	F3SGRE1760-14	F3SGRE1790-30	F39-HGB1780
	F3SGRE1840-14	F3SGRE1870-30	F39-HGB1860
	F3SGRE1920-14	F3SGRE1950-30	F39-HGB1940
	F3SGRE2000-14	F3SGRE2030-30	F39-HGB1460
-			F39-HGA0550
	F3SGRE2080-14	F3SGRE2110-30	F39-HGB1540
			F39-HGA0550
	_	F3SGRE2190-30	F39-HGB1620
			F39-HGA0550
	_	F3SGRE2270-30	F39-HGB1700
			F39-HGA0550
	-	F3SGRE2350-30	F39-HGB1780
			F39-HGA0550
	_	F3SGRE2430-30	F39-HGB1860
			F39-HGA0550
	_	F3SGRE2510-30	F39-HGB1940
			F39-HGA0550


Specifications

F3SG-RE

Item		F3SG-4RE14 F3SG-2RE14	F3SG-4RE30 F3SG-2RE30			
Type of ESPE (IEC 61496-1)	Type 4	F3SG-4RE14/30				
	Type 2	F3SG-2RE14/30				
Detection capability (Opaque obje	ects)	14 mm dia.	30-mm dia.			
Protective height		160 to 2080 mm	190 to 2510 mm			
Operating range (Wiring connection	on option)	0.3 to 3.0 m or 0.3 to 10.0 m	0.3 to 7.0 m or 0.3 to 20.0 m			
Effective aperture angle (EAA)	Type 4	±2.5° max., emitter and receiver at operating ran	ge of 3 m or greater			
(IEC 61496-2)	Type 2	±5.0° max., emitter and receiver at operating range of 3 m or greater				
Light source		Infrared LEDs, Wavelength: 870 nm				
Power supply voltage (Vs)		SELV/PELV 24 VDC±20% (ripple p-p 10% max.)				
Safety outputs (OSSD)		F3SGREP: 2 PNP transistor outputs, load current of 300 mA max. F3SGREN: 2 NPN transistor outputs, load current of 300 mA max.				
Test function		Self-test (at power-on, and during operation)				
Response time		ON to OFF (normal mode): 5 to 15ms, OFF to ON: 25 to 75ms				
Ambient temperature	Operating	−10 to 55°C (non-icing)				
	Storage	−25 to 70°C				
Ambient humidity	Operating	35% to 85% (non-condensing)				
	Storage	35% to 95%				
Degree of protection (IEC 60529)	-	IP65 and IP67				
Material		Housing: Aluminum, Cap: PBT, Front window: PMMA, Cable: Oil resistant PVC, Mounting bracket: ZDC2, FE plate: SUS				
Performance level (PL)/	Type 4	PLe/Category 4 (EN ISO 13849-1:2008)				
Safety category	Type 2	PLc/Category 2 (EN ISO 13849-1:2008)				
PFHd		≤ 9.9 × 10 ⁻⁸ (IEC 61508)	, , , , , , , , , , , , , , , , , , ,			
Proof test interval T _M		Every 20 years (IEC 61508)	Every 20 years (IEC 61508)			

Note: For more information, please check the user manual Z352-E1

Connections (Basic wiring diagram)



^{*1} Refer to user's manual Z352-E1 for more information.
*2 The safety controller and the F3SG-R must share the power supply or be connected to the common terminal of the power supply.

Smart muting actuator for muting applications

The F3W-MA smart muting actuator is an integrated sensor system utilizing multiplebeam sensor technology to configure muting systems in combination with the safety light curtain.

- Point-to-point detection mode for workpieces with constant shape
- Chattering/void space prevention mode to prevent impact of small object holes

Ordering information

Application	Туре	Specification	Order code
	Smart muting actuator for small objects detection	100 mm beam gap between muting trigger beams	F3W-MA0100P
THE CONTRACT THE SEASON SEASON	Smart muting actuator for objects detection	300 mm beam gap between muting trigger beams	F3W-MA0300P

Accessories (Sold separately)

Single-end connector cable

ppearance	Туре	Specification			Cable length	Order code
	Emitter cable		1 + 24 VDC	Brown	3 m	F39-JG3A-L
	M12 connector 5-Pin	0 0	2 TEST	Black	7m	F39-JG7A-L
	Color: Gray		3 0 VDC	Blue	10 m	F39-JG10A-L
			4 Not used	White	15 m	F39-JG15A-L
		Female	5 Not used	Yellow	20 m	F39-JG20A-L
	Receiver cable M12 connector	60	1 Reset	Yellow	3 m	F39-JG3A-D
	8-Pin	(0 ₀ 0)	2 + 24 VDC	Brown	7m	F39-JG7A-D
	Color: Black		3 MUTE A	Gray		
		6	4 MUTE B	Pink	10 m	F39-JG10A-D
		Female	5 OSSD 1	Black		
			6 OSSD 2	White	15 m	F39-JG15A-D
			7 0 VDC	Blue		
			8 AUX(Lamp)	Red	20 m	F39-JG20A-D

Double-end connector cable

Appearance	Туре	Specification		Cable length	Order code
	Emitter cable M12 connector 5-Pin Color: Gray	Connected to power cable or double-ended cable of double-ended cable 1 Brown 3 Blue 2 Black 4 White 5 Yellow	Connected to single-ended cable, or double-ended cable. 1 Brown 3 Blue 2 Black 4 White 5 Yestow Male	0.5 m	F39-JGR5B-L
				1 m	F39-JG1B-L
				3 m	F39-JG3B-L
				5 m	F39-JG5B-L
				7 m	F39-JG7B-L
				10 m	F39-JG10B-L
				15 m	F39-JG15B-L
				20 m	F39-JG20B-L
	Receiver cable M12 connector 8-Pin Color: Black	Connected to power cable or double-ended cable, or double-ended cable, or double-ended cable or double-ended cable, or double-ended cable.	0.5 m	F39-JGR5B-D	
			2 Brown 7 Blue 5 Black 6 White 1 Yellow 8 Red 3 Gray Male	1 m	F39-JG1B-D
				3 m	F39-JG3B-D
				5 m	F39-JG5B-D
				7m	F39-JG7B-D
				10 m	F39-JG10B-D
				15 m	F39-JG15B-D
				20 m	F39-JG20B-D

4-joint plug/socket connector

Appearance	Туре	Specification	Order code
	4 joint connector for receivers	Muting 4-joint connector for connection of F3W-MA and F3SG-RA receivers	F39-GCN4-D
		Muting 4-joint connector for connection of F3W-MA and F3SG-RA transmitters	F39-GCN4-L

Mounting brackets

Appearance	Туре	Specification	Order code
300		Bracket to mount the F3SG-R. Side mounting and backside mounting possible.	F39-LGF
	(Two brackets per set)	Bracket to mount the F3SG-R. Beam alignment after mounting possible. The angle adjustment range is ±15°. Side mounting and backside mounting possible.	F39-LGA

Specifications

Item		F3W-MA0300P	F3W-MA0100P	
Beam gap between muting trigger beams		300 mm	100 mm	
Operating range (Dip switch option)		0.3 to 7.0 m or 0.3 to 20.0 m		
Light source		Infrared LEDs, Wavelength: 870 nm		
Power supply voltage (Vs)		SELV/PELV 24 VDC ±20% (ripple p-p 10% max.)		
Functions		Scan code selection, operation mode selection (Point to point detection/chattering and void space prevention), Off-delay, muting enable. muting trigger beam allocation, operating range selection		
Ambient temperature Operating -10 to 55°C (non-icing)				
	Storage	−25 to 70°C		
Ambient humidity Operatin		35% to 85% (non-condensing)		
	Storage	35% to 95%		
Degree of protection (IEC 60529)		IP65 and IP67		
Material		Housing: Aluminum, Cap: PBT, Front window: PMMA, Cable: Oil resistant PVC, Mounting bracket: ZDC2, FE plate: SUS		

Note: For more information, please check the user manual Z355-E1



Omron at a glance

Listed in Top 2000 largest companies of the globe Omron Corporation NASDAQ: OMRNY Top ranking in Dow Jones Sustainability Index Thomson Reuters Top 100 Global Innovators







200,000 products ranging input, logic and output

Sensing, Control Systems, Visualization, Drives, Robots, Safety, Quality Control & Inspection, Control and Switching Components

7%

Investment in Research & Development

Innovation track record of 80 years

Top 150 global patent assignee 1,200 employees dedicated to R&D 11,000 + issued and pending patents

37,000
Employees worldwide

210
Locations worldwide

22
Countries in EMEA

Working for the benefit of society

Automotive 15%

Components 13%

Social Systems 11%

Healthcare 11%

Environmental 10%

Close to your needs

Technical training & seminars, technical support,
Automation Technology Centers, online community
(MyOmron), online catalogues and technical documentation,
customer service & sales support, inter-operability labs
(Tsunagi), safety services, repairs.



LITE Cost effective for standard industrial environment

PRO Extra performance and and extended product mix

PROplus For advanced and unique applications



Would you like to know more?

OMRON UNITED KINGDOM

- **2** +44 (0) 1908 258 258
- industrial.omron.co.uk
- linkedin.com/company/omron

Sales & Support Offices

Austria

Tel: +43 (0) 2236 377 800 industrial.omron.at

Belgium

Tel: +32 (0) 2 466 24 80 industrial.omron.be

Czech Republic

Tel: +420 234 602 602 industrial.omron.cz

Denmark

Tel: +45 43 44 00 11 industrial.omron.dk

Finland

Tel: +358 (0) 207 464 200 industrial.omron.fi

France

Tel: +33 (0) 1 56 63 70 00 industrial.omron.fr

Germany

Tel: +49 (0) 2173 680 00 industrial.omron.de

Hungary

Tel: +36 1 399 30 50 industrial.omron.hu

Italy

Tel: +39 02 326 81 industrial.omron.it

Netherlands

Tel: +31 (0) 23 568 11 00 industrial.omron.nl

Norway

Tel: +47 (0) 22 65 75 00 industrial.omron.no

Poland

Tel: +48 22 458 66 66 industrial.omron.pl

Portugal

Tel: +351 21 942 94 00 industrial.omron.pt

Russia

Tel: +7 495 648 94 50 industrial.omron.ru

South Africa

Tel: +27 (0)11 579 2600 industrial.omron.co.za

Spain

Tel: +34 902 100 221 industrial.omron.es

Sweden

Tel: +46 (0) 8 632 35 00 industrial.omron.se

Switzerland

Tel: +41 (0) 41 748 13 13 industrial.omron.ch

Turkey

Tel: +90 212 467 30 00 industrial.omron.com.tr

More Omron representatives

industrial.omron.eu