

Eaton 266016

Catalog Number: 266016

Eaton Moeller series NZM - Molded Case Circuit Breaker. Switch-disconnector 4p 250A BG2



General specifications

Product Name	Catalog Number
Eaton Moeller series NZM switch-disconnector	266016
	EAN
	4015082660161
Product Length/Depth	Product Height
142 mm	185 mm
Product Width	Product Weight
140 mm	2.442 kg
Compliances	Certifications
RoHS conform	IEC/EN 60947
	IEC

Product specifications

Type

Switch-disconnector

Special features

Main switch characteristics including positive drive to IEC/EN 60204 and VDE 0113.

Isolating characteristics to IEC/EN 60947-3 and VDE 0660.

Busbar tag shroud to VDE 0160 Part 100.

Rated current = rated uninterrupted current: 250 A

The rated short-time withstand current for PN2/N2 in conjunction with earth-fault release NZM2-4-XFI...Icw = 1.5 kA

Application

Use in unearthed supply systems at 690 V

Amperage Rating

250 A

Voltage rating

690 V - 690 V

Circuit breaker frame type

N2

Features

Version as main switch

Version as maintenance-/service switch

Motor drive optional

Version as emergency stop installation

10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

Resources

Brochures

[eaton-digital-nzm-brochure-br013003en-en-us.pdf](#)

[eaton-feerum-the-whole-grain-solution-success-story-en-us.pdf](#)

Catalogs

[eaton-digital-nzm-catalog-ca013003en-en-us.pdf](#)

Declarations of conformity

[DA-DC-03_N2](#)

Drawings

[eaton-circuit-breaker-nzm-mccb-dimensions-035.eps](#)

[eaton-circuit-breaker-switch-nzm-mccb-dimensions-017.eps](#)

eCAD model

[DA-CE-ETN.N2-4-250](#)

Installation videos

[Introduction of the new digital circuit breaker NZM](#)

[The new digital NZM Range](#)

mCAD model

[DA-CD-nzm2_4p](#)

[DA-CS-nzm2_4p](#)

Technical data sheets

[eaton-nzm-technical-information-sheet](#)

10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

10.4 Clearances and creepage distances

Meets the product standard's requirements.

10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

Pollution degree

3

Mounting Method

Built-in device fixed built-in technique

Fixed

Distribution board installation

Intermediate mounting

Ground mounting

Climatic proofing

Damp heat, constant, to IEC 60068-2-78

Damp heat, cyclic, to IEC 60068-2-30

Equipment heat dissipation, current-dependent

48 W

Isolation

300 V AC (between the auxiliary contacts)

500 V AC (between auxiliary contacts and main contacts)

Rated short-time withstand current (Icw)

3.5 kA

Degree of protection

IP20 (basic protection type, in the area of the HMI devices)

Other

Direction of incoming supply

As required

Electrical connection type of main circuit

Screw connection

Ambient operating temperature - max

70 °C

Ambient operating temperature - min

-25 °C

Ambient storage temperature - max

70 °C

Ambient storage temperature - min

-40 °C

Number of auxiliary contacts (change-over contacts)

0

Number of auxiliary contacts (normally closed contacts)

0

Number of auxiliary contacts (normally open contacts)

0

Protection against direct contact

Finger and back-of-hand proof to DIN EN 50274/VDE 0106 part

110

Rated insulation voltage (Ui)

690 V

Rated operating frequency

50 Hz

Rated operating power at AC-23, 400 V

132 kW

Rated operating power at AC-3, 400 V

0 kW

Switch positions

I, +, 0

Lifespan, mechanical

20000 operations

Overvoltage category

III

Rated operational current

250 A (415 V AC-22/23A, making and breaking capacity)

250 A (690 V AC-22/23A, making and breaking capacity)

Degree of protection (IP), front side

IP40 (with insulating surround)

IP20

IP66 (with door coupling rotary handle)

Degree of protection (terminations)

IP00 (terminations, phase isolator and band terminal)

IP10 (tunnel terminal)

Number of poles

Four-pole

Terminal capacity (copper strip)

Max. 10 segments of 24 mm x 0.8 mm at rear-side connection
(punched)

Min. 2 segments of 16 mm x 0.8 mm at rear-side connection
(punched)

Min. 2 segments of 9 mm x 0.8 mm at box terminal

Max. 10 segments of 16 mm x 0.8 mm at box terminal

Max. 8 segments of 15.5 mm x 0.8 mm (2x) at box terminal

Handle color

Black

Lifespan, electrical

7500 operations at 400 V AC-1

4000 operations at 690 V AC-3

5000 operations at 690 V AC-1

6000 operations at 400 V AC-3

6000 operations at 415 V AC-3

7500 operations at 415 V AC-1

Functions

Disconnectors/main switches

Interlockable

Voltage release optional

Shock resistance

20 g (half-sinusoidal shock 20 ms)

Number of switches

1

Rated conditional short-circuit current (I_q)

0 kA

Rated conditional short-circuit current with back-up fuse

80 kA at 690 V

PN2(N2)-160...250: 250 AgGgL

100 kA at 400/415 V

Rated conditional short-circuit current with downstream fuse

PN2(N2)-160...250: 250 AgGgL

100 kA at 400/415 V

80 kA at 690 V

Rated operating voltage (U_e) at AC - max

690 V

Rated operational current for specified heat dissipation (I_n)

250 A

Rated permanent current at AC-21, 400 V

0 A

Rated permanent current at AC-23, 400 V

0 A

Rated short-time withstand current (t = 0.3 s)

3.5 kA

Rated short-time withstand current (t = 1 s)

3.5 kA

Switching power at 400 V

0 kW

Handle type

Rocker lever

Number of operations per hour - max

120

Rated short-circuit making capacity I_{cm} at 690 V, 50/60 Hz

5.5 kA

Rated impulse withstand voltage (U_{imp}) at auxiliary contacts

6000 V

Rated impulse withstand voltage (U_{imp}) at main contacts

8000 V

Standard terminals

Screw terminal

Optional terminals

Box terminal. Connection on rear. Tunnel terminal

Short-circuit protective device fuses - max

250 A gL

Terminal capacity (copper busbar)

M8 at rear-side screw connection

Max. 24 mm x 8 mm direct at switch rear-side connection

Min. 16 mm x 5 mm direct at switch rear-side connection

Terminal capacity (copper solid conductor/cable)

10 mm² - 16 mm² (1x) at box terminal

16 mm² (1x) at tunnel terminal

10 mm² - 16 mm² (1x) direct at switch rear-side connection

6 mm² - 16 mm² (2x) at box terminal

6 mm² - 16 mm² (2x) direct at switch rear-side connection

Terminal capacity (aluminum solid conductor/cable)

10 mm² - 16 mm² (2x) direct at switch rear-side connection

10 mm² - 16 mm² (1x) direct at switch rear-side connection

16 mm² (1x) at tunnel terminal

Terminal capacity (copper stranded conductor/cable)

25 mm² - 185 mm² (1x) at box terminal

25 mm² - 185 mm² (1x) at 1-hole tunnel terminal
25 mm² - 70 mm² (2x) direct at switch rear-side connection
25 mm² - 70 mm² (2x) at box terminal
25 mm² - 185 mm² (1x) direct at switch rear-side connection

[Terminal capacity \(aluminum stranded conductor/cable\)](#)

25 mm² - 185 mm² (1x) at 1-hole tunnel terminal



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia