



## **Solid Grommet, Black, PE, 1.6mm Max Panel, 30.5m L,PK1**

GES62F-A-C0

The GES62F-A-C0 Polyethylene Slotted Grommet Edging protects and prevents wires and cables from chafing against sharp edges of panel walls and knockouts. Slotted edging is recommended for use on irregularly shaped and round panel holes. The material is highly flexible, while the adhesive lining ensures the product will stay in place. Packaged on a 100' (30.5m) reel for easy handling and dispensing. Polyethylene. Designed for 0.036"-0.062" (0.9 mm-1.6 mm) thick panels. Color Black. 1 per package.

### **Specifications**

Note	Designed for straight edges
Product Type	Solid Grommet Edging
Color	Black
Material	Polyethylene
Maximum Compatible Panel Thickness (In.)	0.06
Maximum Compatible Panel Thickness (mm)	1.6
Minimum Compatible Panel Thickness (In.)	0.036
Minimum Compatible Panel Thickness (mm)	0.9
Maximum Operating Temperature (°C)	50
Maximum Operating Temperature (°F)	122
Minimum Operating Temperature (°C)	-40
Minimum Operating Temperature (°F)	-40
Overall Length (ft.)	100
Overall Length (m)	30.48
Overall Width (In.)	0.13
Overall Width (mm)	3.3
Overall Height (In.)	0.16
Overall Height (mm)	4.1
Resistance Properties	Weather-Resistant
Standards Met	RoHS Compliant
Application	To Protect and Prevent Wires and Cables from Chafing Against Sharp Edges of Panel Walls and Knockouts.
Part Features	Provides protection for cables being installed where there might be sharp edges with irregular shaped and round panel holes.

**Packaging Detail**

UPC	07498362706
Std. Pkg. Qty.	1
Std. Pkg. Volume (cf)	0.1339
Std. Ctn. Qty.	0
Std. Ctn. Volume (cf)	0.0000