

# RF-12P2N8A90DU - Coupler connector



1607255

<https://www.phoenixcontact.com/gb/products/1607255>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Coupler connector, straight, Screw locking mechanism, M23, number of positions: 12, contact connection type: Pin, shielded: yes, degree of protection: IP67, cable diameter range: 5 mm ... 13.2 mm, number of positions: 12, connection method: Crimp connection, series: RF, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1242253

## Commercial data

Item number	1607255
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	ABRAGG
Product key	ABRAGG
Catalog page	Page 78 (PC-2011)
GTIN	4046356174817
Weight per piece (including packing)	97.97 g
Weight per piece (excluding packing)	93.697 g
Customs tariff number	85366990
Country of origin	DE

# RF-12P2N8A90DU - Coupler connector



1607255

<https://www.phoenixcontact.com/gb/products/1607255>

## Technical data

### Notes

Order information:	Order crimp contacts Ø 1 mm separately
--------------------	--

### Product properties

Product type	Circular connector (cable-side)
Series	RF
Application	Feedback, signal
	Signal
Number of positions	12
Connection profile	12
Shielded	yes
Coding	N
Thread type	M23

### Material specifications

Seal material	FPM
Housing material	Metal
Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Insulator material	PA 6.6
Gasket and O-ring material	FPM

### Connection data

Conductor connection	
Connection method	Crimp connection

### Electrical properties

Contact	
Contact diameter	1 mm
Max. current	8 A
Nominal voltage $U_N$	48 V AC 74 V DC
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	1.5 kV

### Connector

Type	straight
Direction of rotation	Counter direction

### Cable/line

External cable diameter	5 mm ... 13.2 mm
-------------------------	------------------

# RF-12P2N8A90DU - Coupler connector



1607255

<https://www.phoenixcontact.com/gb/products/1607255>

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-40 °C ... 125 °C
Altitude	2000 m

# RF-12P2N8A90DU - Coupler connector




1607255

<https://www.phoenixcontact.com/gb/products/1607255>


## Drawings

Dimensional drawing



RF-12(17)...N8A90DU

Dimensional drawing




Dimensional drawing

# RF-12P2N8A90DU - Coupler connector

1607255

<https://www.phoenixcontact.com/gb/products/1607255>

Schematic diagram



Connector pin assignment

# RF-12P2N8A90DU - Coupler connector




1607255

<https://www.phoenixcontact.com/gb/products/1607255>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1607255>

	<b>cUL Recognized</b> Approval ID: E153698-20090723			
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
	48 V	5 A	20	-

	<b>UL Recognized</b> Approval ID: E153698-20090723			
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
	48 V	5 A	20	-

# RF-12P2N8A90DU - Coupler connector



1607255

<https://www.phoenixcontact.com/gb/products/1607255>

## Classifications

### ECLASS

ECLASS-13.0	27440116
-------------	----------

### ETIM

ETIM 9.0	EC002635
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# RF-12P2N8A90DU - Coupler connector



1607255

<https://www.phoenixcontact.com/gb/products/1607255>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	cc4b3a3f-30f9-45bc-9e06-828530548fdf

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)