





Specifications

| Ge | ne | ra |
|----|----|----|
| | | |

| General | | |
|--|--|--|
| Product Type | Crimp-to-Wire Contact | |
| Number of contacts (per housing) | 40-72 | |
| Mating half | Mates with most 2.54 mm (0.1 in.) Centerline Products with 0.64 mm (0.025in.) Square or Round Pins | |
| Dimensional | | |
| Size (Wire) | 22 to 26 AWG | |
| Height (Crimp) | 0.81 - 0.86 mm (0.032 - 0.034 in.) | |
| Size Insulation OD (Discrete contact) | 0.91 mm (0.036 in.) to 2.62 mm (0.103 in.) | |
| Size Insulation OD (Latch housing application) | 0.91 mm (0.036 in.) to 1.52 mm (0.06 in.) | |
| Thickness (Spring) | 0.089 mm (0.0035 in.) | |
| Electrical | | |
| Current rating | 3A Continuous | |
| Resistance (Contact) | 15 M-ohms max. | |
| Resistance (Insulation) | 5000 M-ohms | |
| Voltage rating | 1000V rms | |
| Mechanical | | |
| Insertion force | 2.35N (240 gf) | |
| Withdrawal Force | 0.45N (45 gf) | |
| Spring force | Standard | |
| Physical | | |
| Material (Contact) | Copper Alloy | |
| Plating (Contact area) | 0.38 μm (15 μin.) Gold | |
| Humidity Range | 10% to 95% | |
| Underplating | 1.27 μm (50 μin.) Nickel | |
| Material (Spring) | Copper Alloy | |
| Temperature (Range) | -65°C to +125°C | |
| Approvals / Certifications | | |
| Approvals / Certifications | UL and CSA Approved | |
| Other Features | Databating Hand Crimping Tools Part Number HT 0005 | |
| Accessory | Ratcheting Hand Crimping Tool: Part Number HT-0095 | |
| Packaging (Type) | Box | |
| Comments | PV™ Contact Removal Tool: Part Number HT-0080 | |





