

M12 male 0° / M12 female 0° A-cod.




PUR AWG24+22 shielded vt UL/CSA+drag ch. 0.15m




Art.No.: 7000-40531-8030015

Weight: 0.038


Country of origin: CZ

Model designation: MSBL0-A-U803_0.15

Link to Product**Illustration**



Product may differ from Image



Side 1	
Family construction form	M12
No. of poles	5
Coding	A
Gender	male
Mounting method	inserted, screwed
Thread	M12 x 1
Tightening torque	0.6 Nm
Width across flats	SW13
Cable outlet	straight
Material	PUR
Degree of protection (EN IEC 60529)	IP67, IP66K, IP65
Side 2	
Family construction form	M12

No. of poles	5
Coding	A
Gender	female
Mounting method	inserted, screwed
Thread	M12 x 1
Tightening torque	0.6 Nm
Width across flats	SW13
Cable outlet	straight
Material	PUR
Degree of protection (EN IEC 60529)	IP67, IP66K, IP65

Commercial data

URL Webshop	https://shop.murrelektronik.com/7000-40531-8030015
GTIN	4048879613408
ECLASS-6.0	27279218
ECLASS-6.1	27060307
ECLASS-7.0	27060307
ECLASS-7.1	27060307
ECLASS-8.0	27060307
ECLASS-8.1	27060307
ECLASS-9.0	27060307
ECLASS-9.1	27060307
ECLASS-10.0.1	27060307
ECLASS-10.1	27060307
ECLASS-11.0	27060307
ECLASS-11.1	27060307
ECLASS-12.0	27060307
ECLASS-13.0	27060307
ECLASS-14.0	27060307
ETIM-5.0	EC001855
ETIM-6.0	EC001855
ETIM-7.0	EC001855
ETIM-8.0	EC001855
EAN	4048879613408

Electrical data | Supply

Operating voltage AC max.	60 V
Operating voltage DC max.	60 V
Current operating per contact max.	4 A
Operating voltage AC (UL-listed)	30 V
Operating voltage DC (UL-listed)	30 V

Diagnostics

Status indication LED	no
-----------------------	----

Installation | Connection

Mounting set	M12 x 1
--------------	---------

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP67, IP66K, IP65
Additional condition protection degree	inserted, screwed
Pollution Degree	3
Rated surge voltage	1.5 kV
Material group (IEC 60664-1)	I

Mechanical data

Contour for corrugated hose	without
-----------------------------	---------

Mechanical data | Material data

Material screw connection	Zinc die-casting
Coating of fitting	nickel plated
Locking material	Zinc die-casting
Coating locking	Nickeled
Material gasket	FKM
Mechanical data Mounting data	
Mounting method	inserted, screwed, Shaking protection
Environmental characteristics Climatic	
Operating temperature min.	-30 °C
Operating temperature max.	85 °C
Additional condition temperature range	depending on cable quality
Important installation notes	
Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.
Conformity	
Product standard	DIN EN 61076-2-101 (M12)
Installation Cable	
Function cable	Hybrid, Data, Power
Amount stranding	2
Stranding	Wires
Amount stranding (type 2)	1
Stranding (type 2)	Stranded joints
Cable shielding (type)	copper braid, tinned
Cable shielding (coverage)	65 %
Banding	Foil
Drain wire (cross-section)	22 AWG
Wire arrangement	(, white, blue,), black, red
Cable weight	63.12 g/m
Drain wire (cross-section)	22 AWG
Material wire insulation (type 2)	PE
Outer diameter wire insulation (type 2)	2.1 mm
Tolerance outer diameter wire insulation (type 2)	± 0.05 mm
Shore hardness wire insulation (type 2)	65
Ingredient freeness wire insulation (type 2)	CFC-free, halogen-free, lead-free
Amount wires (type 2)	2
Amount strands wire (type 2)	19
Diameter of single wires (type 2)	36 AWG
Conductor crosssection wire (type 2)	24 AWG
Material conductor wire (type 2)	copper stranded wire, tinned
Material wire insulation (type 3)	PE
Outer diameter wire insulation (type 3)	1.5 mm
Tolerance outer diameter wire insulation (type 3)	± 0.05 mm
Shore hardness wire insulation (type 3)	65
Ingredient freeness wire insulation (type 3)	CFC-free, halogen-free, lead-free
Amount wires (type 3)	2
Amount strands wire (type 3)	19
Diameter of single wires (type 3)	22 AWG
Wire conductor cross section (type 3)	22 AWG
Material conductor wire (type 3)	copper stranded wire, tinned
Outer-diameter (jacket)	6.9 mm

Tolerance outer diameter (sheath)	± 5 %
Material jacket	PUR
Shore hardness jacket	89
Freedom from ingredients (jacket)	CFC-free, halogen-free, lead-free
Conductor resistance (wire type 2)	78 Ω/km @ 20 °C
Conductor resistance (wire type 3)	54 Ω/km @ 20 °C
Electric capacitance	40,000 pF/km
Isolation resistance	5,000 MΩ × km
Nominal voltage AC max.	300 V
Withstand voltage (wire - wire)	2 kV @ 60 s
Withstand voltage (wire - shield)	2 kV @ 60 s
AC withstand voltage power (wire - wire)	2 kV @ 60 s
AC withstand voltage power (wire - shield)	2 kV @ 60 s
Current load capacity (standard)	to DIN VDE 0298-4
Current load capacity min. Wire (type 2)	3 A
Current carrying capacity min. wire (type 3)	6 A
Characteristic impedance	120 Ω 10 %
Min. operating temperature (static)	-40 °C
Max. operating temperature (fixed)	80 °C
Operating temperature min. (dynamic)	-30 °C
Operating temperature max. (dynamic)	70 °C
Bending radius (fixed)	6 × Outer diameter
Bending radius (dynamic)	10 × Outer diameter
No. of bending cycles (C-track)	1 Mio. @ 25 °C
Traversing distance (C-track)	5 m @ 25 °C
Travel speed (C-track)	3 m/s @ 25 °C
Acceleration (C-track)	5 m/s² @ 25 °C