
solenoid valve **VZWF-B-L-M22C-N12-135-E-3AP4-10-R1**Part number: 1492376

FESTO

force pilot operated, NPT1/2" connection.





Data sheet

Feature	Value
Design structure	Diaphragm valve
-	forced
Type of actuation	electrical
Sealing principle	soft
Assembly position	Magnet standing
Mounting type	Line installation
Process valve connection	1/2 NPT
Electrical connection	Plug
	Cubic design
	to EN 175301-803
	Plug pattern type A to EN 175301-803
Nominal size	13.5 mm
Valve function	2/2 closed, monostable
Manual override	None
Flow direction	non reversible
Medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Mediani	Inert gases
	Mineral oil
	Water
	Neutral fluids
	Other media on request
Nominal pressure of process valve	40
Differential pressure	0 bar
Characteristic coil data	230 V AC: 50/60 Hz, pick-up power 18 VA, holding power 15 VA
Permissible voltage fluctuation	+/- 10 %
Medium pressure	0 10 bar
Max. viscosity	22 mm2/s
Medium temperature	-10 80 °C
·	-10 35 °C
Ambient temperature	
Leak rate in accordance with EN 12266-1	A 25 m 2 /h
Flow rate Kv	2.5 m3/h
Standard nominal flow rate	2,660 l/min
Switching time on	130 ms
Switching time off	180 ms
Materials note	Contains PWIS substances
	Conforms to RoHS
Material housing	Stainless steel casting
Material number for housing	1.4581
Material seals	EPDM
Material screws	High alloy steel, non-corrosive
Material number, screw	1.4301
Product weight	1,000 g
CE mark (see declaration of conformity)	to EU directive low-voltage devices
Protection class	IP65
Corrosion resistance classification CRC	3 - High corrosion stress