



ITEM. 06865

SIP SUB 3040 WATER PUMP

POWERFUL SUBMERSIBLE WATER PUMP FOR DOMESTIC & LIGHT COMMERCIAL USE



**COMES WITH
A 2-YEAR
STANDARD
WARRANTY***

FIND OUT MORE AT
SIP-GROUP.COM/WARRANTY



PRODUCT OVERVIEW

The **SIP SUB 3040 Water Pump** is ideal for draining clean water from a flooded cellar, basement, small water or collection tank, work site, well or hot tub. Clean water is considered to be free from large particle contamination. Water pumps can help prevent costly damage to property or work areas from recurring rainwater or groundwater. This pump can also be used for a variety of garden maintenance purposes and is suited for intermittent use.

FEATURES & BENEFITS

- ✓ **POWERFUL BRUSHLESS INDUCTION MOTOR (400w/0.5hp)**
Draws water at a max. flow rate of 9,000ltr/hr through an impeller at the pump base. The heavy-duty wound motor is durable and lightweight.
- ✓ **FITTED FLOAT SWITCH**
Ensures the pump functions unaided when the activation depth (360mm) is reached. This prevents the pump from running dry and overheating when in use.
- ✓ **MAX. 6MTR PUMPING HEAD**
Discharges water flow to a max. height of 6mtr through hose or pipe connected to pump outlet. This ensures the intended area or item is drained quickly.
- ✓ **PARTICLE CAPACITY**
Suitable for draining water with particles to max. diameter of 3mm.
- ✓ **LIGHTWEIGHT, COMPACT DESIGN**
Includes a carry handle for portability and lowering into water (7mtr max. operating depth). A mounted power cable hook provides added safety.

For over 50 years, SIP Industrial Products Limited has been a flagship supplier of high-quality equipment and machinery to the ever-growing engineering, construction, automotive, and agricultural marketplaces.



ITEM. 06865

SIP SUB 3040 WATER PUMP

OTHER FEATURES

HIGH-GRADE CARBON STEEL PUMP SHAFT

High-tensile strength compound for long life use.

POWER CABLE

Fitted with a 9mtr length cable for greater versatility.

APPLICATIONS & USES

Quickly drains flooded areas.

Effective for a variety of garden maintenance purposes.

Suitable for domestic or light commercial use.

Intended for intermittent use.

TECHNICAL INFORMATION

ITEM NO.	06865
Input Supply	230v 50Hz
Motor Power	400w (0.5hp)
Flow Rate	9,000ltr/hr
Outlet	25mm Ø - 40mm Ø 1" BSP
Max. Pumping Head	6mtr
Max. Operating Depth	7mtr
Max. Particle Diameter	Ø 3mm
Max. Water Temperature	35°C
Body Type	Plastic
Pump Type	Clean Water
Cable Length	9mtr
Protection	IPX8
Net Weight	3.50kg
Gross Weight	4.50kg
Product Dimensions	300(H) x 250(W) x 180mm(D)
Packaged Dimensions	440(H) x 350(W) x 300mm(D)