

DIAL TORQUE WRENCHES - NM/IN-LBS, FT-LBS

- › 2-10 Nm thru 50-250 Nm / 18-90 in-lbs. thru 35-175 ft-lbs
- › Accurate to $\pm 4\%$ of torque reading in both directions at 20% to 100% of full scale.
- › Industrial all steel or aluminum torque transfer components.
- › High alloy torsion drive design — accuracy not effected by hand position.
- › Dual scale (Metric/English) with clockwise and counterclockwise operation — fewer wrenches needed to complete job.
- › Memory needles are standard on all wrenches except electric light models.
- › Easy-to-read, high contrast scale.
- › Laser marked serial number for traceability.
- › N.I.S.T. (National Institute of Standards and Technology) traceable CW certification supplied with each wrench.



Product #	Drive Size (in)	Torque Range (ft-lbs)	Torque Range (in-lbs)	Torque Range (Nm)	Increments (Nm)	Overall Length (in)	Weight (lbs)
J6169NMF	1/4	–	18-90	2-10	0.2	10	1.30
J6177NMF	3/8	–	50-250	6-30	0.5	10	1.50
J6113NMF	3/8	10-50	–	14-70	2	14-7/8	2.10
J6121NMF	1/2	35-175	–	50-250	5	21-1/2	4.00